## KYCON





**AUDIO JACKS: STX-3150 Series** 

3.5mm Jack Slim Design with Switch PCB Mount

#### **Product Features**

Audio Applications for Computers and Multimedia
Can Be Used To Activate Speakers, an Equalizer or to
Configure the Audio Signal
Up to One Double-Pole Single-Throw Switch
Spring Loaded Contacts for High Contact Reliability
Narrow Body Uses Minimal Board Space
CSA/NRTL Certified File No. LR78160

## Performance Specifications

## **Materials and Finish**

#### Housing

PBT Thermoplastic, UL94V-0 Rated, Black Color

## **Bushing**

Brass. Nickel Plated

## **Terminals and Contacts**

Phosphor Bronze, Silver Plated

## **Coil Springs**

Spring Steel

# **Mechanical Characteristics**

## **Insertion Force**

0.3kg - 3.0kg

### **Extraction Force**

0.3kg - 3.0kg

### **Durability**

5000 Mating Cycles

#### **Electrical Characteristics**

### Insulation Resistance

100 Megohms Min. at 500V DC

#### **Contact Resistance**

30 milliohms Max.

# **Dielectric Withstanding Voltage**


500V AC RMS for 1 Minute

## **Operating Temperature**

-25°C to + 80°C

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

#### **Generated Part Number**



# **Series**

STX-3150 - 3.5mm Jack Slim Design with Switch PCB Mount

## **Number of Pins**

3 - Pin

5 - Pin

## **Threading Option**


C - Threaded Barrel

N - Non-Threaded Barrel

Contact Kycon for other Options

## STX-3150 Series

Dimensions in mm



## STX-3150-5N

