

# GSX-223

# Ultra-miniature SM Crystal

- Ultra-miniature for maximum space saving
- Ideal for wireless & mobile applications
- Metal lid can be grounded to minimise EMI
- Seam sealed for excellent long-term stability



# CONFIGURABLE OPTIONS


Parameter	Option Code
Frequency	
Calibration tolerance	
Any	
±10ppm	1
±15ppm	Р
±30ppm	3
Temperature stability	
Any	
±10ppm	1
±15ppm	Р
±20ppm	2
±30ppm	3
Operating temperature range	
Any	
-10 to +60°C	1
-20 to +70°C	2
-30 to +80°C	3
-40 to +85°C	4
Circuit condition	
Any	
6pF	Т
8pF	М
9pF	Ν
10pF	А
12pF	В
16pF	D
Series resonant	S
Oscillation mode	
Fundamental	F




## **SPECIFICATIONS**

Frequency range	16.0 ~ 96.0MHz		
Dimensions	2.05 x 1.65 x 0.50mm		
Storage temperature	-40 to +85°C		
range			
Equivalent series	150Ω max (16.0 ~ 23.99MHz)		
resistance	100Ω max (24.0 ~ 35.99MHz)		
	60Ω max (36.0 ~ 54.0MHz)		
	50Ω max (60.0MHz)		
	30Ω max (76.8MHz)		
	20Ω max (96.0MHz)		
Ageing	±1ppm max first year		
Test drive level	10µW typ, 100µW max		
Soldering condition	260°C, 10 sec x2 max		
Net mass	5.63mg		


#### **PACKAGE DRAWING**





0.70

(typ)



PAD	CONNECTION	
1	Crystal	
2	Ground & lid	
3	Crystal	
4	Ground & lid	

Dimensions in mm



MARKING

FREQUENCY

T DC

## **ORDERING INFORMATION**

To request a quotation for the GSX-223 please use the configurable options form to choose the options you require and then submit your configured product to our team. Our expert advisers are always happy to help with your requirements and can be contacted on +44 1460 256 100 or at sales@golledge.com.

Following product selection you will be issued with a seven character Golledge part number. Your Golledge part number is the internationally accepted Golledge manufacturing part number (MPN) that should be used for all project documentation, including bills of materials (BoMs) and purchase orders.

If you have any queries regarding any of our documentation our dedicated sales team will be happy to help.

Marking type: Laser

DC = Date code


# **APPLICATIONS**

Our crystals and oscillators are regularly supplied for use with industry-leading ICs, from world-leading manufacturers including:

Analogue Devices Atmel (Microchip Technology Inc.) Broadcom Dialog Semiconductor PLC Intel Nordic Semiconductor NXP Semiconductors Qualcomm (and CSR) Silicon Labs STMicroelectronics Texas Instruments (TI) Xilinx and more...

If you'd like more information about chipset compatibility please get in touch with our team here.


#### SOLDERING PROFILE



Lead free solderability limits: 260°C ±5°C x 10s ±5s x 2.



## **TAPE & REEL SPECIFICATION**



Dimensions in mm

## CONSTRUCTION

Ceramic body with gold-plated pads Metal lid, seam sealed

#### **HANDLING & STORAGE**



Human Body Model (HBM) 1A (250V to <500V)

	_	
 		•
	r 4	
	. •	

Moisture Sensitivity Level (MSL): 1 (or not applicable)

#### COMPLIANCE

Please refer to our **DOCUMENTS** section for more information.



Lead-free (< 0.1% by weight )



RoHS compliant with no exemptions.



REACH compliant.



Free of conflict minerals.



Free from halogens.



Free from ozone-depleting substances.