



SPECIFICATIONS:

LOW CONTACT RESISTANCE	<.01 OHMS
ROTATIONAL LIFE	>1000 REVOLUTIONS
TORQUE	1.0 TO 5.0 IN. OZ.
CONCENTRICITY	WITHIN .002 T.I.R.

APPLICATION:

FOR HIGH Q VARIABLE REACTANCE TUNING OF MICROWAVE CAVITIES, FILTERS AND OTHER RESONANT STRUCTURES.

CAPACITIVE TUNING ELEMENT (U.S. PATENT RE. 30,406)



MANUFACTURING CORPORATION

Rockaway Valley Road, Boonton, N.J. 07005 (201) 334-2676

ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION

DRN. -14	APP. <i>[Signature]</i>	SCALE ≈ 3IN = 1IN.
DATE 29 JUN 81	DATE 29 JUN 81	.X X ± .015 .X X X ± .005
DRG. NO. 6927-0		REV. T 29 JUN 81