

Dwg. Number	Customer P/N	Times P/N	Length(L) in 'mm'
IE-00407-01	-	MGS160-KMKM-0.5M	500 +10/-0
IE-00407-02	-	MGS160-KMKM-1.0M	1000 +20/-0
IE-00407-03	-	MGS160-KMKM-1.5M	1500 +30/-0
IE-00407-04	-	MGS160-KMKM-2.0M	2000 +40/-0

1.0 Scope

This drawing documents the construction and performance of Maxgain 160 cable assemblies manufactured by Times Microwave systems.

2.0 Cable Information

- 2.1 Cable to be MAXGAIN 160
- 2.2 Jacket color to be Blue
- 2.3 Jacket material to be FEP
- 2.4 Nominal cable impedance to be 50 ohms
- 2.5 Cable diameter to be 4.04mm [0.159"] (Nominal).

3.0 Connector Information

3.1 Forward Connector

Type 2.92mm (M) Straight Connector (SP029) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated

3.2 After Connector Type 2.92mm (M) Straight Connector (SP029) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated

Unless otherwise spec- ified, dimensions are in MM. Tolerances are applicable when spec- ified.						TIMES MICROWAVE SYSTEMS			
	Drawn	YA	10/19/22			www.timesmicrowave.com			
These drawings and specifications contain proprietary information	Checked			MG160 CABLE ASSEMBLY (Space Assemblies)					
which is the property of	Approved					blies)			
Times Microwave	Apploved			Size	CAGE C	CAGE CODE		Drawing No.:	
Systems.				A	6899	99	IE-00407-XX		
				Scale:	NA	Rev. ((A)	Sheet: 1 of 3	

	THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE	E SAME AS SHEET	1
REV	DESCRIPTION	DATE	BY
А	INITIAL RELEASE	10/19/22	YA
	4.0 Electrical Performance	-	

erformance

- 4.1 Frequency range: DC 40GHz
- 4.2 Insertion loss & VSWR: As per below table,

Dwg. Number	Max. Insertion Loss in dB	Max. VSWR			
Dwg. Number	@ 40GHz	@ 40GHz			
IE-00407-01	1.98	1.40			
IE-00407-02	3.41	1.40			
IE-00407-03	4.81	1.40			
IE-00407-04	6.27	1.40			

5.0 Mechanical Performance

- 5.1 Overall Length to be specified length.
- 5.2 Minimum Bend radius is 19mm [0.750"].

6.0 Environmental Performance

- 6.1 Installation Temperature Range (-55°C to +150°C)
- 6.2 Storage Temperature Range (-55°C to +150°C)
- 6.3 Operating Temperature Range (-55°C to +150°C)

7.0 Marking

- 7.1 Markers are to be black text on White Color Marker Sleeve.
- 7.2 Marker Configuration to be:

1.2		Juration	10 00.						
	Dwg. Numb	er	Marking details			Marker Numbers	Mar Posi	-	
	IE-00407-0		mes Microwa MGS160-KN \$\$\$\$	IKM-0.5N		1	In cente cable		
	IE-00407-0		MGS160-KN					er of the assy.	
	IE-00407-0		mes Microwa MGS160-KN \$\$\$\$	IKM-1.5N		1 & 2	At both	n ends.	
	IE-00407-0		mes Microwa MGS160-KN \$\$\$\$	IKM-2.0N	e Systems (M-2.0M 1 & 2			n ends.	
	\$\$\$\$\$ = 5-dig Register to be					guration.			
Unless otherwise spec- ified, dimensions are in MM. Tolerances are applicable when spec-				TIMES MICROWAVE SYSTEMS					
ified.	Drawn	YA	10/19/22	2 www.timesmicrowave.com					
These drawings and specifications contain proprietary information	Checked					MG160 CABLE ASSEMBLY (Space Assemblies)			
which is the property of Times Microwave Systems.	Approved			Size A		E CODE 8999	Drawing	,	
				Scale:	NA	Rev. (A)	Sheet: 2 of 3	

	THE RE	VISION STAT	TUS OF	ALL SHEET	S OF TH	IIS DRAWI	NG IS TH	HE SAME A	S SHEET '	1
REV			DE	SCRIPTION				DA	TE	BY
А	INITIAL RE	LEASE						10/1	9/22	YA
3	8.3 8.4 	ass 100,000 o rials per AST ecified: Tolera Tole ±10 ±15	M E595. ance will rance mm mm mm							
fied, dimen MM. Tolera applicable v fied.	vhen spec-	Ap	oprova YA	als 10/19/22		Ī	_	MICROW ww.timesmi	_	
	ns contain information	Checked				M		ABLE AS		,
which is the property of Times Microwave Systems.	icrowave	Approved			Size A	Size CAGE CO		0		
					Scale:	NA	Rev. ((A)	Sheet:	3 of 3