	THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS T	HE SAME AS SHEET	1
REV	DESCRIPTION	DATE	BY
А	INITIAL RELEASE	10/28/22	YA
FORWARD	Length (L)		AFIER
2 L			

Dwg. Number	Customer P/N	Times P/N	Length(L) in 'inch'
IE-00419-01	-	IBPS047-KMKM-4.0IN	4 +0.20/-0
IE-00419-02	-	IBPS047-KMKM-6.0IN	6 +0.20/-0
IE-00419-03	-	IBPS047-KMKM-8.0IN	8 +0.20/-0
IE-00419-04	-	IBPS047-KMKM-10.0IN	10 +0.20/-0
IE-00419-05	-	IBPS047-KMKM-12.0IN	12 +0.24/-0

#### 1.0 Scope

This drawing documents the construction and performance of PT- 047 cable assemblies manufactured by Times Microwave systems.

#### 2.0 Cable Information

- 2.1 Cable to be PT-047
- 2.2 Jacket color to be Blue
- 2.3 Jacket material to be FEP
- 2.4 Nominal cable impedance to be 50 ohms
- 2.5 Cable diameter to be 0.062" [1.58mm] (Nominal).

## 3.0 Connector Information

- 3.1 Forward Connector Type K (M) Straight Connector (SP107) Connector Body – Stainless Steel, Gold Plated Center Contact – Beryllium Copper, Gold Plated
- 3.2 After Connector

Type K (M) Straight Connector (SP107) Connector Body – Stainless Steel, Gold Plated Center Contact – Beryllium Copper, Gold Plated

Unless otherwise spec- ified, dimensions are in INCH. Tolerances are applicable when spec-	Aŗ	oprova	als		TIMES MICROWAVE SYSTEMS			
ified.	Drawn	YA	10/28/22	www.timesmicrowave.		crowave.com		
These drawings and specifications contain proprietary information	Checked			PT-047 CABLE ASSEMBLY (Space Assemblies)				
which is the property of	Approved							
Times Microwave	Appioved			Size	Size CAGE CODE A 68999		Drawing No.: IE-00419-XX	
Systems.				A				
				Scale:	NA	Rev. (	A)	Sheet: 1 of 2

THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE SAME AS SHEET 1							
REV	V DESCRIPTION DATE B						
А	INITIAL RELEASE	10/28/22	YA				
	<b>4.0 Electrical Performance</b> 4.1 Frequency range: DC – 40GHz						

4.2 Insertion loss & VSWR: As per below table,

Dwg. Number	Max. Insertion Loss in dB	Max. VSWR		
Dwg. Number	@ 40GHz	@ 40GHz		
IE-00419-01	1.45	1.40		
IE-00419-02	1.94	1.40		
IE-00419-03	2.43	1.40		
IE-00419-04	2.92	1.40		
IE-00419-05	3.43	1.40		

#### 5.0 Mechanical Performance

- 5.1 Overall Length to be specified length.
- 5.2 Minimum Bend radius is 0.25" [6.5mm].

# 6.0 Environmental Performance

- 6.1 Installation Temperature Range (-65°C to +150°C)
- 6.2 Storage Temperature Range (-65°C to +150°C)
- 6.3 Operating Temperature Range (-65°C to +150°C)

### 7.0 NOTES

- 7.1 All Dimensions are in INCH.
- 7.2 Assemblies built in Class 100,000 clean room.
- 7.3 Low outgassing materials per ASTM E595.
- 7.4 Unless Otherwise Specified: Tolerance will be,

Linear Dimension	Tolerance
<20 INCH	±0.4 INCH
20-79 INCH	±0.6 INCH
>79 INCH	±0.8 INCH

\*\*Tolerances are not accumulative.

Unless otherwise spec ified, dimensions are ir INCH. Tolerances are applicable when spec-				TIMES MICROWAVE SYSTEMS					
ified.	Drawn	YA	10/28/22			www.timesmicrowave.com			
These drawings and specifications contain proprietary information	Checked			PT-047 CABLE ASSEMBLY (Space Assemblies)					
which is the property of	Approved								
Times Microwave	, pproved			Size	CAGE CODE   Drawin		Drawing	3 No.:	
Systems.				A	68999		IE	IE-00419-XX	
				-					
				Scale:	NA	Rev. (	(A)	Sheet: 2 of 2	