# PARTICLES PLUS\*

# 5501-30 Remote Airborne Particle Counter

# 0.1CFM (2.83 LPM)

- Industry's highest concentration of 15,000,000 particles/ft<sup>3</sup> @ 10% coincidence loss
- · Ideal for use in research, industrial health and safety, indoor air quality, and cleanroom applications
- · The most comprehensive internal self-diagnostics of any remote particle counter
- Remote diagnostics allow for remote service investigation through the Internet
- Supports MODBUS TCP, RTU and ASCII communication over Ethernet, or (optional) RS-485/RS-232
- Internet of Things (IoT) communication allows for network or cloud-based data options



The Particles Plus® 5501-30 Remote Particle Counter measures 0.5 to 75.0 µm and are the most feature advanced remote particle counters available.

Integration is easy into a building automation and cleanroom management system via Ethernet, or (optional) Wireless 802.11 b/g, RS485 or RS232. Integrated web server displays instrument screen through any browser.

The 5501-30 remote particle counter displays and reports 6 user-selectable particle size channels, as well as (optional) temperature and humidity, flow and sensor status, date of last calibration, serial number, laser on-time, and date of manufacture for easy maintenance and warranty management. Storing up to 45,000 time-stamped particle count and environmental data records provides data redundancy on every instrument. Particles Plus® counters can be monitored remotely via web browser, or controlled and monitored using IMS Software.

All Particles Plus® counters meet ISO 21501-4 and JIS B9921. The 5501-30 ensures compliance with an on-board pulse height analyzer.

### **Features and Benefits**

- 5501-30: Measures 0.5 μm to 75 μm
- 0.1 CFM (2.83 LPM) flow rate
- Long life laser diode technology
- · Measures up to 6 channels of simultaneous data
- Approximates mas concentration in µg/m³ with density/refractive index corections
- · Large easy-to-use icon driven colour touch screen display
- · (Optional) Temperature and relative humidity probe
- Internalvacuum pump
- Stores up to 45,000 sample records, 1,000 sample locations and 50 recipes
- · Annotation function alows user to save 32 character notations to a sample record
- · Easy configuration and transferable from instrument to instrument
- · Connect using Ethernet, USB or (optional) Wireles 802.11b/g, RS485 or RS232
- Static or dynamic IP address (DHCP)
- · Remote diagnostics allows for remote service investigation through the internet
- Versatile mounting options
- · Internal audible alarm
- User-selectable channel sizes
- · Complies with ISO 21501-4 and JIS B9921 standards
- · Easy to clean and wipe down with minimal particle traps
- Seamless integration into a facitilty monitoring system
- · Light weight stainles steel enclosure
- · 2 year limited waranty. Extended waranties available

## **Specifications**

 Model
 5501-30

 Size Range
 0.5 to 75.0 μm

Size Channels Factory calibrated at 0.5, 1.0, 2.5, 5.0, 10.0, 30.0 µm variable binning

Counting Efficiency 50% @ 0.5 µm; 100% for particles >0.75 µm per JIS

Concentration Limits 15,000,000 particles/ft<sup>3</sup> @ 10% coincidence (per ISO 21501-4),

30,000,000 particles/ft3 @ 10% coincidence (as tested and validated1)

Flow rates 0.1 CFM (2.83 LPM)
Light Source Long life laser diode

Zero Count <1 count / 60 minutes (<1 particles / 6 ft³)

Count Modes Real-Time Meter and graph, cumulative/differential count/m³ and count/ft³, and mass concentration (PM)

Count Alarms 1 to 9,999,999 counts
Calibration NIST traceable

Display 4.3" (10.9 cm) WQVGA (480×272) color touch screen

Printer (Optional) External thermal printer available

Vacuum Source Internal pump with automatic flow control

Airflow Internally monitored Filtered Exhaust Internal HEPA filter

Number of Channels 6

Custom Size Channels Calibration for custom size channels available

Audible Alarm Adjustable built-in alarm

Reports ISO 14644-1, EU GMP Annex 1, FS 209E

Communication Modes Ethernet and USB (Optional) Wireless 802.11 b/g, RS485 or RS232.

Environmental Sensor (Optional) Temperature 32° to 122°F (0° to 50°C) ±1°F (0.5°C) and relative humidity probe 15-90% ±2% Alarms on counts for all particle sizes, low battery, sensor failure, environmental sensors and flow

Standards ISO 21501-4 and JIS B9921

Calibration Recommended minimum once per year

External Surface Stainless steel

Dimensions (L x W x H) 5.2" x 2.3" x 8.9" (13.3 cm x 5.8 cm x 22.6 cm) includes barb fittings

Weight 2.6 lb (1.18 kg)

Accessories Operating manual on USB flash drive, isokinetic probe, temperature relative humidity sensor, purge filter,

battery, data download software, USB cable, power supply & cable

Optional Accessories Printed manual, spare battery, external battery charger, external printer and isokinetic probes

Buffer Memory 45,000 sample records (rotating buffer) including particle count data, environmental data, locations and

times. Scrollable on screen or printout

Sample Locations Up to 1,000 locations 20 characters long

Sample Time 1 second to 99 hours

Power 110 to 240 VAC 50/60 Hz universal in-line power supply Operating Conditions 41° to 104°F (5° to 40°C) / 20% to 95% non-condensing Storage Conditions 32° to 122°F (0° to 50°C) / Up to 98% non-condensing

Warranty 2 Years. Extended warranties available.


 $\underline{\hbox{1-Validated by independent analysis see paper available at www.particlesplus.com/aac2022\_paper}\\$ 




Audible and Visual Alarm Management



Icon Driven Menus for Ease-of-Use



Control and Manage Remotely with IMS



PAT. https://particlepatents.com/ Additional Patents Pending.
Particles Plus, Inc. reserves the right to change specifications without notice.
Contact hello@particlesplus.com or your local distributor for more details.
Particles Plus and the Particles Plus logo are trademarks of Particles Plus, Inc. @2022 Particles Plus, Inc. All rights reserved.





