Notification Number:		20230320002.0	Notification Da	ate:	March 21, 2023
Title: Datasheet for DS90UB953-Q1, DS90UB935-Q1, DS90UB953A-Q1, and TSER953		and TSER953			
Customer Contact: No		Notification Manager		Dept:	Quality Services
Change Type: Electrical Specification					

Change Type: Electrical Specification

Description of Change:

Texas Instruments Incorporated is announcing an information only notification.

The product datasheet(s) is being updated as summarized below.

The following change history provides further details.



DS90UB953-Q1

SNLS552D - SEPTEMBER 2017 - REVISED MARCH 2023

C	nanges from Revision C (October 2020) to Revision D (March 2023)	Page
•	Typical power consumption bullet on front page updated to match electrical characteristics table	
•	IDD_TOTAL typical value changed to 160 mA	
•	Changed I2C terminology to "Controller" and "Target"	
•	Removed extra arrow from DPHY Receiver to Clock Gen blocks in Functional Block Diagram	
•	Added description for non-continuous clock lane mode	
•	Added description for deserializer SENSOR_STS registers	18
•	Updated script example for voltage monitoring	
•	Updated description for reading GPIO status when set as output and added GPIO Configuration table.	21
•	Added information for enabling Forward Channel GPIO using FC_GPIO_EN	21
•	Updated GPIO Output Control section description for enabling register 0x0E	
•	Added typical latency to Forward Channel GPIO table	22
•	Updated Clocking Mode table with additional modes, frequency clarifications, and CSI-2 bandwidth	
	clarifications	22
•	Corrected effect of setting M value in register 0x06	35
•	Updated description to refer to "DVP_DT_MATCH_EN" in register 0x11	
•	Changed 0x17[7:4] default value from 0x0 to 0x3	39
•	Added max and min readings to Voltage Sensor Thresholds description in Register 0x19	
•	Updated SENSOR_V1_THRESH description to match SENSOR_V0_THRESH in register 0x1A	40
•	Changed "GPIO0 Sensor" to "Internal Temperature Sensor" in register 0x57	
•	Changed "FPD3_RX_ID" to "FPD3_TX_ID" in registers 0xF0-0xF5	
•	Changed PoC network impedance recommendation from 2 kΩ to 1 kΩ	
•	Updated PoC description	
•	Removed IL and RL values from Suggested Characteristics for Single-Ended PCB Traces With Attach	ed PoC
	Networks Table	
•	Changed FB1-FB3 requirement to DCR < 500 mΩ	
•	Added note for setting watchdog timer for system initialization	
•	Corrected PDB capacitor from 1-µF to 10-µF	



С	hanges from Revision A (October 2020) to Revision B (March 2023)	Page
•	Typical power consumption bullet on front page updated to match electrical characteristics table	1
•	Fixed typo - missing max ambient temp on front page	1
•	Added note for supply noise frequency range	6
•	Changed I2C terminology to "Controller" and "Target"	14
•	Removed extra arrow from DPHY Receiver to Clock Gen blocks in Functional Block Diagram	
•	Added description for non-continuous clock lane mode	
•	Added description for descrializer SENSOR_STS registers	17
•	Updated script example for voltage monitoring	
•	Updated description for reading GPIO status when set as output and added GPIO Configuration table.	20
•	Added information for enabling Forward Channel GPIO using FC_GPIO_EN	
•	Updated GPIO Output Control section description for enabling register 0x0E	20
•	Added typical latency to Forward Channel GPIO table	21
•	Updated Clocking Mode table with additional modes, frequency clarifications, and CSI-2 bandwidth	
	clarifications	
•	Added "set for 4 Gbps line rate" in register 0x05	
•	Corrected effect of setting M value in register 0x06	
•	Updated description to refer to "DVP_DT_MATCH_EN" in register 0x11	37
•	Changed 0x17[7:4] default value from 0x0 to 0x3	
•	Added max and min readings to Voltage Sensor Thresholds description in Register 0x19	
•	Updated SENSOR_V1_THRESH description to match SENSOR_V0_THRESH in register 0x1A	
•	Changed "GPIO0 Sensor" to "Internal Temperature Sensor" in register 0x57	
•	Changed "FPD3_RX_ID" to "FPD3_TX_ID" in registers 0xF0-0xF5	
•	Changed PoC network impedance recommendation from 2 kΩ to 1 kΩ	
•	Updated PoC description	
•	Removed IL and RL values from Suggested Characteristics for Single-Ended PCB Traces With Attache	ed PoC
	Networks Table	
•	Changed FB1-FB3 requirement to DCR < 500 mΩ	
•	Added note for setting watchdog timer for system initialization	
•	Corrected PDB capacitor from 1-µF to 10-µF	68



DS90UB953A-Q1 SNLS643B - MARCH 2019 - REVISED MARCH 2023

C	nanges from Revision A (September 2020) to Revision B (March 2023)	Page
•	Typical power consumption bullet on front page updated to match electrical characteristics table	1
•	Changed I2C terminology to "Controller" and "Target"	13
•	Removed extra arrow from DPHY Receiver to Clock Gen blocks in Functional Block Diagram	
•	Added description for non-continuous clock lane mode	
•	Added description for descrializer SENSOR_STS registers	
•	Updated script example for voltage monitoring.	
•	Updated description for reading GPIO status when set as output and added GPIO Configuration table	
•	Added information for enabling Forward Channel GPIO using FC_GPIO_EN	
•	Updated GPIO Output Control section description for enabling register 0x0E	
•	Added typical latency to Forward Channel GPIO table	20
•	Updated Clocking Mode table with additional modes, frequency clarifications, and CSI-2 bandwidth	
	clarifications	
•	Corrected effect of setting M value in register 0x06	
•	Updated description to refer to "DVP_DT_MATCH_EN" in register 0x11	
•	Changed 0x17[7:4] default value from 0x0 to 0x3	
•	Added max and min readings to Voltage Sensor Thresholds description in Register 0x19	
•	Updated SENSOR_V1_THRESH description to match SENSOR_V0_THRESH in register 0x1A	
•	Changed "GPIO0 Sensor" to "Internal Temperature Sensor" in register 0x57	
•	Changed "FPD3_RX_ID" to "FPD3_TX_ID" in registers 0xF0-0xF5	
•	Changed PoC network impedance recommendation from 2 k Ω to 1 k Ω .	
•	Updated PoC description	
•	Removed IL and RL values from Suggested Characteristics for Single-Ended PCB Traces With Attache	
	Networks Table	
•	Changed FB1-FB3 requirement to DCR < 500 m Ω	
•	Added note for setting watchdog timer for system initialization	
	Corrected PDB capacitor from 1-µF to 10-µF	73

Changes from Revision A (May 2021) to Revision B (March 2023) Typical power consumption bullet on front page updated to match electrical characteristics table......1 Updated description for reading GPIO status when set as output and added GPIO Configuration table........19 Added typical latency to Forward Channel GPIO Typical Timing table......21 Updated Clocking Mode table with additional modes, frequency clarifications, and CSI-2 bandwidth Updated SENSOR V1 THRESH description to match SENSOR V0 THRESH in register 0x1A38 Changed "GPIO0 Sensor" to "Internal Temperature Sensor" in register 0x57.......49 Removed IL and RL values from Suggested Components for a "4G" V3Link PoC Network Table......65 Updated PoC description......65 Changed PDB capacitor value to "> 10 µF"......68 Changed PDB capacitor value from 1-µF to 10-µF.......73

The datasheet number will be changing. Device Family Change From: Change To:

DS90UB953-Q1	SNLS552C	SNLS552D
DS90UB935-Q1	SNLS605A	SNLS605B
DS90UB953A-Q1	SNLS643A	SNLS643B
TSER953	SNLS696A	SNLS696B

These changes may be reviewed at the datasheet links provided.

http://www.ti.com/product/DS90UB953-Q1

http://www.ti.com/product/DS90UB935-Q1

http://www.ti.com/product/DS90UB953A-Q1

http://www.ti.com/product/TSER953

Reason for Change:

To accurately reflect device characteristics.

Anticipated impact on Fit, Form, Function, Quality or Reliability (positive / negative):

No anticipated impact. This is a specification change announcement only. There are no changes to the actual device.

Changes to product identification resulting from this notification:

None.

Product Affected:

DS90UB953TRHBRQ1	DS90UB953TRHBTQ1	DS90UB935TRHBRQ1	DS90UB935TRHBTQ1	
DS90UB953ATRHBRQ1	DS90UB953ATRHBTQ1	TSER953RHBR	TSER953RHBT	

For questions regarding this notice, e-mails can be sent to the regional contacts shown below or your local Field Sales Representative.

Location	E-Mail		
WW Change Management Team	PCN www admin team@list.ti.com		

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property

right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's

provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.