

Harvatek 3.0mm Round LED LAMP with Holder HV-317464/230/SURSUBW-F3.0-U1930

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Data Sheet No.
	***************************************		HV-317464/230/SURSUBW-F3.0-U1930	
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 1/14



DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

LIFE SUPPORT POLICY

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Customer Part No.		Data Sheet No.
	********	******		HV-317464/230/SURSUBW-F3.0-U1930		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 2/14		




Compliance and Certification

ISO9002, QS9000 and ISO14001 Certified RoHS Compliant



Orderable Information






Features:

- Stable Color
- Popular 3.0mm through hole package.
- White Diffused Lens.

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Data Sheet No.
	********	******		HV-317464/230/SURSUBW-F3.0-U1930
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 3/14



Package Dimensions:



Notes:

- 1.All dimensions are millimeters.
- 2. Tolerance is +/-0.25mm unless otherwise noted.
- 3. Specifications are subject to change without notice.

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Customer Part No.		Data Sheet No.
	********	******		HV-317464/230/SURSUBW-F3.0-U1930		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 4/14		



Parameter	Symbol	Rat	ting	Unit
Forward Current	I_{F}	3	0	mA
Operating Temperature	$T_{ m opr}$	-40to	o+85	$^{\circ}$
Storage Temperature	T_{stg}	-40to	o+85	$^{\circ}$ C
Soldering Temperature*1	$T_{ m sol}$	260±5		$^{\circ}$
Dayyan Dissination	D	SUR	75	mW
Power Dissipation	P_d	SUB	100	m w
Reverse Voltage	V_R	:	5	V
Peak Forward Current*2	Ţ	SUR	75	A
Peak Forward Current*2	$ m I_{FP}$	SUB	100	mA

^{*1:}Soldering time \leq 5 seconds. *2:Pulse Width \leq 100 μ s and Duty \leq 1%

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Customer Part No.		Data Sheet No.
	********	******		HV-317464/230/SURSUBW-F3.0-U1930		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 5/14		



Electrical and Optical Characteristic

Parameter	Symbol	Condition	on	Min.	Тур.	Max.	Unit		
Formward Waltage	V_{F}	I _F =20 mA	SUR	/	2.0	2.4	V		
Forward Voltage	VF	I _F =20 mA	SUB	/	3.0	3.6	V		
Reverse Current	I_R	$V_R = 5$	V	/	/	10	μΑ		
Lyminous Intensity	Ţ	I _F =20 mA	SUR	250	700	/	mcd		
Luminous Intensity			I _F =20 mA	IF-20 IIIA	100	500	/	mcd	
Viewing Angle	201/2	I _F =20 mA	SUR/ SUB	/	80	/	deg		
Dominant Wayslan ath	λd	I -20 m A	SUR	/	620	/			
Dominant Wavelength	λα	I _F =20 mA	IF-20 IIIA	7. 20 mm	SUB	/	470	/	nm
Peak Wavelength	λρ	I _F =20 mA	SUR	/	630	/	nm		
reak wavelengin	λρ	1F-20 IIIA	SUB	/	465	/	11111		
Spectrum Radiation	Δλ	I _F =20 mA	SUR	/	20	/	nm		
Bandwidth	Δ Λ	I;─∠U IIIA	SUB	/	25	/	nm		

Notes:

 θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Customer Part No.		Data Sheet No.
	********	*******		HV-317464/230/SURSUBW-F3.0-U1930		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 6/14		



Specifications for Bin Grading:(SUR)

	lv (mcd)				
Grade	Min.	Max.			
Т	250	500			
U	400	800			
V	630	1250			
W	1000	2000			

Notes:

Luminous intensity:+/-15%.

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Customer Part No.		Data Sheet No.
	********	******		HV-317464/230/SURSUBW-F3.0-U1930		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 7/14		



Specifications for Bin Grading:(SUB)

Iv (mcd)				
Grade	Min.	Max.		
R	100	200		
S	160	320		
Т	250	500		
U	400	800		
V	630	1250		

	λd (nm)				
Grade	Min.	Max.			
3	465. 5	468. 5			
4	467.5	470. 5			
5	469.5	472. 5			
6	471.5	474. 5			
7	473. 5	476. 5			

Notes:


1.Luminous intensity:+/-15%.

2.Wavelength: +/-1nm.

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Data Sheet No.
	********	********		HV-317464/230/SURSUBW-F3.0-U1930
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 8/14




Typical Electro-Optical Characteristics Curve(SUR)



Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Data Sheet No.
	********	******		HV-317464/230/SURSUBW-F3.0-U1930
	Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Version of 1.0	Page 9/14



Typical Electrical / Optical Characteristics Curves(SUB)



Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Data Sheet No.
	********	*****		HV-317464/230/SURSUBW-F3.0-U1930
	Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Version of 1.0	Page 10/14




Soldering condition

- 1. Careful attention should be paid during soldering. When soldering, leave more then 2mm from solder joint to Led, and soldering beyond the base of the tie bar is recommended.
- 2. Avoiding applying any stress to the lead frame while the LED are at high temperature particularly when soldering.
- 3. Dip and hand soldering should not be done more than one time.
- 4. After soldering the LED, the epoxy bulb should be protected from mechanical shock or vibration until the LED return to room temperature.
- 5. A rapid-rate process is not recommended for cooling the LED down from the peak temperature.
- 6. Although the recommended soldering conditions are specified in the above table, dip or hand soldering at the lowest possible temperature is desirable for the LED.
- 7. Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.

Recommended soldering conditions

Hai	nd Soldering	Wave Soldering		
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	160°C Max. (120 sec Max.)	
Soldering time 3 sec Max.		Bath temp. & time	260 Max., 5 sec Max	
Distance	2mm Min.(From solder joint to	Distance	2mm Min. (From solder joint	
Distance	Led)	Distance	to Led)	



Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Customer Part No.		Data Sheet No.
	********	******		HV-317464/230/SURSUBW-F3.0-U1930		
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 11/14		



Reliability test items and conditions:

The reliability of products shall be satisfied with items listed below.

Confidence level: 97%

LTPD:3%

No	Item	Test Conditions	Test Hours/Cycle	Sample Size	Failure Judgment Criteria	Ac/Er
1	Solder Heat	TEMP:230°C±5 °C	10 SEC	76 PCS		0/1
2	Temperature Cycle	H:+100°C 15min ∫ 5min L:-40°C 15min	300 CYCLES	76 PCS		0/1
3	Thermal Shock	H:+100°C 5min ∫ 10sec L:-10°C 5min	300 CYCLES	76 PCS	$Iv \leq Ivt*0.5$ or	0/1
4	High Temperature Storage	TEMP:100°C	1000 HRS	76 PCS	Vf≧U or Vf≦L	0/1
5	Low Temperature Storage	TEMP:-40°C	1000 HRS	76 PCS	VI=L	0/1
6	DC Operating Life	TEMP:25°C IF=20mA	1000 HRS	76 PCS		0/1
7	High Temperature / High Humidity	85°C/85%RH	1000 HRS	76 PCS		0/1

Note: Ivt: To test Iv value of the chip before the reliability test.

Iv: The test value of the chip that has completed the reliability test


U: Upper Specification Limit

L: Lower Specification Limit

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Data Sheet No.
	********	********		HV-317464/230/SURSUBW-F3.0-U1930
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Aug.14. 2021	Version of 1.0	Page 12/14



Packing Specification:



500PCS/Bag

2000PCS/In-Carton

20000PCS/Out-Carton



CPN:

RoHs

P/N:

HV-317464/230/SURSUBW-F3.0-U1930

CAT:

QTY: HUE:

LOT NO: REF:

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Data Sheet No.
	********	*******		HV-317464/230/SURSUBW-F3.0-U1930
	Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Version of 1.0	Page 13/14



Revision History

Revision	Page	Version No.	Revision Date
Initial Release		1.0	08-14-2021

Official Product	HV-317464/230/SURSUBW-F3.0-U1930	Customer Part No.		Data Sheet No.
	********	******		HV-317464/230/SURSUBW-F3.0-U1930
	Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Version of 1.0	Page 14/14