

Date: - 9th April 2020

Data Sheet Issue:- A1

Rectifier Diode Types W2865HA680 to W2865HA720

Absolute Maximum Ratings

	VOLTAGE RATINGS	MAXIMUM LIMITS	UNITS
V_{RRM}	Repetitive peak reverse voltage, (note 1)	6800-7200	V
V _{RSM}	Non-repetitive peak reverse voltage, (note 1)	6900-7300	V

	OTHER RATINGS	MAXIMUM LIMITS	UNITS
I _{F(AV)M}	Maximum average forward current, T _{sink} =55°C, (note 2)	2862	Α
I _{F(AV)M}	Maximum average forward current. T _{sink} =100°C, (note 2)	1938	Α
I _{F(AV)M}	Maximum average forward current. T _{sink} =100°C, (note 3)	1035	Α
I _{F(RMS)M}	Nominal RMS forward current, T _{sink} =25°C, (note 2)	5480	Α
I _{F(d.c.)}	D.C. forward current, T _{sink} =25°C, (note 4)	4825	Α
I _{FSM}	Peak non-repetitive surge t _p =10ms, V _{rm} =60%V _{RRM} , (note 5)	32.4	kA
I _{FSM2}	Peak non-repetitive surge t _p =10ms, V _{rm} ≤10V, (note 5)	36	kA
l ² t	I ² t capacity for fusing t _p =10ms, V _{rm} =60%V _{RRM} , (note 5)	5.25×10 ⁶	A ² s
l ² t	I²t capacity for fusing t _p =10ms, V _{rm} ≤10V, (note 5)	6.48×10 ⁶	A ² s
T _{j op}	Operating temperature range	-40 to +150	°C
T _{stg}	Storage temperature range	-55 to +150	°C

Notes:-

- 1) De-rating factor of 0.13% per $^{\circ}$ C is applicable for T_{j} below 25 $^{\circ}$ C.
- 2) Double side cooled, single phase; 50Hz, 180° half-sinewave.
- 3) Cathode side cooled, single phase; 50Hz, 180° half-sinewave.
- 4) Double side cooled.
- 5) Half-sinewave, 150°C T_j initial.



Characteristics

	PARAMETER	MIN.	TYP.	MAX.	TEST CONDITIONS (Note 1)	UNITS
V _{FM}	Maximum peak forward voltage	-	-	2.54	I _{FM} =5000A	V
V_{FM}	Maximum peak forward voltage	-	-	4.04	I _{FM} =10000A	V
V _{T0}	Threshold voltage	-	-	0.982		V
r _T	Slope resistance	-	-	0.308		mΩ
I _{RRM}	Peak reverse current	-	-	100	Rated V _{RRM}	mA
Qrr	Recovered charge	-	12800	13500		μC
Qra	Recovered charge, 50% Chord	-	6300	-	 I _{TM} =2000A, t _p =1000μs, di/dt=10A/μs,	μC
I _{rm}	Reverse recovery current	-	240	-	V _r =100V	Α
trr	Reverse recovery time, 50% chord	-	53	-		μs
		-	-	0.0105	Double side cooled	K/W
RthJK	Thermal resistance, junction to heatsink	-	-	0.0173	Anode side cooled	K/W
		-	-	0.0273	Cathode side cooled	K/W
F	Mounting force	32	-	40	Note 2	kN
W_t	Weight		1.2			kg

- Unless otherwise indicated T_j=150°C.
 For other clamp forces, please consult factory.



Notes on Ratings and Characteristics

1.0 Voltage Grade Table

Voltage Grade	V _{RRM} V	V _{RSM} V	V _R DC V
68	6800	6700	4050
72	7200	7100	4300

2.0 Extension of Voltage Grades

This report is applicable to other voltage grades when supply has been agreed by Sales/Production.

3.0 De-rating Factor

A blocking voltage de-rating factor of 0.13%/°C is applicable to this device for T_j below 25°C.

4.0 Snubber Components

When selecting snubber components, care must be taken not to use excessively large values of snubber capacitor or excessively small values of snubber resistor. Such excessive component values may lead to device damage due to the large resultant values of snubber discharge current. If required, please consult the factory for assistance.

5.0 Computer Modelling Parameters

5.1 Device Dissipation Calculations

$$I_{AV} = \frac{-V_0 + \sqrt{{V_0}^2 + 4 \cdot ff^2 \cdot r_{\scriptscriptstyle S} \cdot W_{AV}}}{2 \cdot ff^2 \cdot r_{\scriptscriptstyle S}} \qquad \text{and:} \qquad W_{AV} = \frac{\Delta T}{R_{th}} \\ \Delta T = T_{j \max} - T_{\scriptscriptstyle K}$$

Where $V_{T0}=0.982V$, $r_{T}=0.308m\Omega$,

 R_{th} = Supplementary thermal impedance, see table below and

ff = Form factor, see table below.

Supplementary Thermal Impedance						
Conduction Angle	6 phase (60°)	3 phase (120°)	½ wave (180°)	d.c.		
Square wave Double Side Cooled	0.0120	0.0116	0.0112	0.0105		
Square wave Cathode Side Cooled	0.0288	0.0284	0.0280	0.0273		
Sine wave Double Side Cooled	0.0117	0.0112	0.0107			
Sine wave Cathode Side Cooled	0.0285	0.0281	0.0276			

Form Factors						
Conduction Angle 6 phase (60°) 3 phase (120°) ½ wave (180°) d.c.						
Square wave	2.449	1.732	1.414	1		
Sine wave	2.778	1.879	1.57			



5.2 Calculating V_F using ABCD Coefficients

The on-state characteristic I_F vs. V_F, on page 6 is represented in two ways;

- (i) the well established V_{T0} and r_T tangent used for rating purposes and
- (ii) a set of constants A, B, C, D, forming the coefficients of the representative equation for V_F in terms of I_F given below:

$$V_F = A + B \cdot \ln(I_F) + C \cdot I_F + D \cdot \sqrt{I_F}$$

The constants, derived by curve fitting software, are given below for both hot and cold characteristics. The resulting values for V_F agree with the true device characteristic over a current range, which is limited to that plotted.

25°C Coefficients		150°C Coefficients	
Α	0.4948654	Α	0.27883
В	0.06879860	В	0.074496
С	1.688076 ×10 ⁻⁴	С	2.6277 ×10 ⁻⁴
D	1.710350 ×10 ⁻³	D	4.4583 ×10 ⁻³

5.3 D.C. Thermal Impedance Calculation

$$r_{t} = \sum_{p=1}^{p=n} r_{p} \cdot \left(1 - e^{\frac{-t}{\tau_{p}}}\right)$$

Where p = 1 to n, n is the number of terms in the series and:

t = Duration of heating pulse in seconds.

 r_t = Thermal resistance at time t.

 r_p = Amplitude of p_{th} term.

 τ_p = Time Constant of r_{th} term.

The coefficients for this device are shown in the tables below:

D.C. Double Side Cooled							
Term	1	2	3	4			
r_p	4.833386×10 ⁻³	2.428484×10 ⁻³	2.556565×10 ⁻³	6.778151×10 ⁻⁴			
$ au_{\mathcal{P}}$	0.9049929	0.3059693	0.07882910	5.760647×10 ⁻³			

D.C. Anode Side Cooled						
Term	1	2	3	4	5	
r_p	9.389648×10 ⁻³	3.552906×10 ⁻³	2.867635×10 ⁻³	6.065886×10 ⁻⁴	1.081806×10 ⁻³	
$ au_p$	6.032949	0.5244182	0.1316295	0.05328786	9.747228×10 ⁻³	

	D.C. Cathode Side Cooled							
Term 1 2 3 4								
r_p	0.02178216	3.548018×10 ⁻³	1.319715×10 ⁻³	7.056416×10 ⁻⁴				
$ au_{ m p}$	5.035878	0.1905190	0.05133230	6.802442×10 ⁻³				



6.0 Reverse recovery ratings

(i) Q_{ra} is based on 50% I_{rm} chord as shown in Fig. 1




Fig. 1

(ii) Q_{rr} is based on a 150 μs integration time i.e.

$$Q_{rr} = \int_{0}^{150\,\mu s} i_{rr}.dt$$

(iii)
$$K Factor = \frac{t_1}{t_2}$$



Curves

Figure 1 – Forward characteristics of Limit device




Figure 2 – Transient thermal impedance






Figure 3 - Maximum Surge Rating











Figure 5 – Recovered charge, Qra (50% chord)






Figure 7 – Maximum recovery time, t_{rr} (50% chord)






Figure 8 – Forward current vs. Power dissipation – Double Side Cooled




Figure 10 – Forward current vs. Power dissipation – Cathode Side Cooled




Figure 9 – Forward current vs. Heatsink temperature – Double Side Cooled






Figure 11 – Forward current vs. Heatsink temperature – Cathode Side Cooled





Outline Drawing & Ordering Information



ORDERII	NG INFORMATION	(Please quote 10 digit code as below)		
W2865	HA	**	0	
Fixed Type Code	Fixed Outline Code	Voltage code V _{RRM} /100 68-72	Fixed code	

Order code: W2865HA720 - 7200V V_{RRM}, 26mm clamp height capsule.

IXYS Semiconductor GmbH

Edisonstraße 15 D-68623 Lampertheim Tel: +49 6206 503-0 Fax: +49 6206 503-627

E-mail: marcom@ixys.de

IXYS Corporation

1590 Buckeye Drive Milpitas CA 95035 7418 USA Tel: +1 (408) 547 9000 Fax: +1 (408) 496 0670

E-mail: sales@ixys.net

A Littelfuse Technology

www.littelfuse.com

www.ixysuk.com

www.ixys.com

IXYS UK Westcode Ltd

Langley Park Way, Langley Park, Chippenham, Wiltshire, SN15 1GE. Tel: +44 (0)1249 455500 Fax: +44 (0)1249 659448

E-mail: sales@ixysuk.com

IXYS Long Beach Inc 2500 Mira Mar Avenue

Long Beach CA 90815 USA Tel: +1 (562) 296 6584 Fax: +1 (562) 296 6585

Email: service@ixyslongbeach.com

The information contained herein is confidential and is protected by Copyright. The information may not be used or disclosed except with the written permission of and in the manner permitted by the proprietors IXYS UK Westcode Ltd.

In the interest of product improvement, IXYS UK Westcode Ltd. reserves the right to change specifications at any time without

Devices with a suffix code (2-letter, 3-letter or letter/digit/letter combination) added to their generic code are not necessarily subject to the conditions and limits contained in this report.

©IXYS UK Westcode Ltd.





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.