

Features

- ESD/Surge Protection for 1 Line with Bidirectional.
- Provide transient protection for each line to IEC 61000-4-2 (ESD) ±30kV (air/contact)
 IEC 61000-4-4 (EFT) 80A (5/50ns)
 IEC 61000-4-5 (Lightning) 25A (8/20µs)
- Suitable for, 12V and below, operating voltage applications
- Small package saves board space
- Protect one I/O line or one power line
- Fast turn-on and Low clamping voltage
- Solid-state silicon-avalanche and active circuit triggering technology
- Green part

Applications

- RS232, RS485 Interfaces
- Power line protection
- Security system
- Network
- Power manager system
- Notebooks, desktops, and servers
- Microprocessor-based equipment
- Peripherals

Description

AZ4212-01G is a design which includes a bidirectional ESD rated clamping cell to protect one power line, or one control line, or one low speed data line in an electronic systems. The AZ4212-01G has been specifically designed to protect sensitive components which are connected to power and control lines from over-voltage damage and latch-up caused by


Electrostatic Discharging (ESD), Electrical Fast Transients (EFT), Lightning, and Cable Discharge Event (CDE).

AZ4212-01G is a unique design which includes proprietary clamping cell in a single package.

During transient conditions, the proprietary clamping cell prevents over-voltage on the power line or control/data lines, protecting any downstream components.

AZ4212-01G may be used to meet the ESD immunity requirements of IEC 61000-4-2, Level 4 (±15kV air, ±8kV contact discharge).

Circuit Diagram / Pin Configuration





SPECIFICATIONS


ABSOLUTE MAXIMUM RATINGS			
PARAMETER	SYMBOL	RATING	UNITS
Peak Pulse Current (tp =8/20μs)	I _{PP}	25	А
Operating Supply Voltage	V_{DC}	±13.2	V
ESD per IEC 61000-4-2 (Air)	V _{ESD-1}	±30	kV
ESD per IEC 61000-4-2 (Contact)	V _{ESD-2}	±30	
Lead Soldering Temperature	T _{SOL}	260 (10 sec.)	℃
Operating Temperature	T _{OP}	-55 to +85	℃
Storage Temperature	T _{STO}	-55 to +150	$^{\circ}$


ELECTRICAL CHARACTERISTICS						
PARAMETER	SYMBOL	CONDITIONS	MINI	TYP	MAX	UNITS
Reverse Stand-Off Voltage	V_{RWM}	T=25 ℃.	-12		12	V
Reverse Leakage Current	I _{Leak}	V _{RWM} = ±12V, T=25 °C			1	μΑ
Reverse Breakdown Voltage	V_{BV}	I _{BV} = 1mA, T=25 °C	13.7		18	V
Surge Clamping Voltage	Va	I _{PP} =5A, tp=8/20μs, T=25 °C		16.5		V
	▼ CL-surge	I _{PP} =25A, tp=8/20μs, T=25 °C		21.5		V
ESD Clamping Voltage (Note 1)	$V_{\sf clamp}$	IEC 61000-4-2 +8kV (I _{TLP} =16A), T=25 °C, Contact mode		17		V
ESD Dynamic Turn-on Resistance	R _{dynamic}	IEC 61000-4-2 0~+8kV, T=25 °C, Contact mode		0.14		Ω
Channel Input Capacitance	C _{IN}	$V_R = 0V, f = 1MHz, T=25 ^{\circ}C$		60	75	pF


Note 1: ESD Clamping Voltage was measured by Transmission Line Pulsing (TLP) System. TLP conditions: Z_0 = 50 Ω , t_p = 100ns, t_r = 2ns.



Typical Characteristics









Applications Information

The AZ4212-01G is designed to protect one line against System ESD/EFT/Lightning pulses by clamping it to an acceptable reference. It provides bi-directional protection.

The usage of the AZ4212-01G is shown in Fig. 1. Protected line, such as data line, control line, or power line, is connected at pin 1. The pin 2 is connected to a ground plane on the board. In order to minimize parasitic inductance in the board traces, all path lengths connected to the pins of AZ4212-01G should be kept as short as possible.

In order to obtain enough suppression of ESD induced transient, good circuit board is critical. Thus, the following guidelines are recommended:

- Minimize the path length between the protected lines and the AZ4212-01G.
- Place the AZ4212-01G near the input terminals or connectors to restrict transient coupling.
- The ESD current return path to ground should be kept as short as possible.
- Use ground planes whenever possible.
- NEVER route critical signals near board edges and near the lines which the ESD transient easily injects to.




Fig. 2 shows another simplified example of using AZ4212-01G to protect the control line, low

speed data line, and power line from ESD transient stress.





Fig. 2




Mechanical Details SOD-123



PACKAGE DIMENSIONS

Symbol	Millim	neters	Inches		
	MIN.	MAX.	MIN.	MAX.	
Α	1.050	1.250	0.041	0.049	
A 1	0.000	0.100	0.000	0.004	
A2	1.050	1.150	0.041	0.045	
b	0.450	0.650	0.018	0.026	
С	0.080	0.150	0.003	0.006	
D	1.500	1.700	0.059	0.067	
Е	2.600	2.800	0.102	0.110	
E1	3.550	3.850	0.140	0.152	
L	0.500	REF	0.020 REF		
L1	0.250	0.450	0.010	0.018	
θ	0 °	8°	0 °	8°	


LAND LAYOUT



Notes:

This LAND LAYOUT is for reference purposes only. Please consult your manufacturing partners to ensure your company's PCB design guidelines are met.

MARKING CODE



Part Number	Marking Code
AZ4212-01G (Green part)	CX

Note. Green means Pb-free, RoHS, and Halogen free compliant.

Ordering Information

PN#	Material	Type	Reel size	MOQ	MOQ/internal box	MOQ/carton
AZ4212-01G.R7G	Green	T/R	7 inch	3,000/reel	4 reel= 12,000/box	6 box =72,000/carton

Revision History

Revision	Modification Description			
Revision 2014/11/27	Preliminary Release.			
Revision 2015/03/26	Formal Release.			