LEGION[®]900 Greater Connectivity to LPWAN IoT Networks

The **LEGION 900** antenna is a low profile 3dBi omni-directional high performance antenna for the 900MHz ISM band. This antenna is designed to accommodate outdoor communications including LoRa protocol for Internet of Things (IoT). Designed specifically for outdoor connection to LoRa or Sigfox IoT remote stations that require reliable connectivity back to modems and gateways.

- Long Product Life Low Profile Design The LEGION 900 antenna stands only 0.62" inches tall.
- High performance, efficiency and High Omni directionality in a small form factor, outperforming competing solutions
- Robust and UV resistant enclosure

ANTENNAPLUS

- · Alternative mounting options available on request
- Available in black or white







Full Outdoor Installation Ready

Compact and Robust UV Resistant Housing



ţ Ļ

Low loss cable accessories

Customizable Cables and Connectors to Connect to Any Modem



Fast custom turnaround time

Standard Configurations

AP-LPWAN-A-S2-BL-15	Adhesive Mount, SMA on LPWAN, Black, 15ft coax
AP-LPWAN-Q-S2-BL-15	Threaded Bolt Mount, SMA on LPWAN, Black, 15ft coax

Also available in color white, customizable cable lengths up to 35 feet, and other connector variations.



Adhesive Mount

Bolt Mount



Electrical Data			
Frequency Range	F1=890-950 MHz		
VSWR	1.5:1 or less at resonant point		
Peak Gain: Isotropic	3.0 dBi		
Radiation Pattern	OMNI Directional Hemispherical		
Polarization	Vertical		
Mechanical Specifications			
Radome	Glass Filled Polypropylene		
Cable Data			
Single-Band Antenna	15 feet (4.5 m) (Adhesive Mount)		
	SMA is standard or Contact factory for connector.		
Mounting Data			
Dimensions	Diameter	4.2" (106.6 mm)	
	Height	0.62" (15.8 mm)	



3D Antenna Patterns

