

Customer Specification PART NO. SPC-800

Construction

1) Tubing Type	Adhesive Lined Heat Shrinkable Tubing
2) Tubing Material	Irr Polyolefin w/ Heavy Wall Thermoplastic Bonding Layer
3) Minimum Supplied ID(In)	0.800
4) Maximum Recovered ID(In)	0.200
5) Nominal Recovered Wall Thickness(In)	0.060
6) Minimum Recovered Adhesive Wall Thickness(In)	0.050
7) Color(s)	BLACK

Applicable Specifications

1) Other	AMS-DTL-23053/15, Class 1	

Environmental

1) EU Directive 2011/65/EU(RoHS2):	
	All materials used in the manufacture of this part are in compliance with European Directive 2011/65/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for RoHS C of C.
2) REACH Regulation (EC 1907/2006):	
	This product does not contain Substances of Very High Concern (SVHC) listed on the Europear Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.
3) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

Properties

I) Temperature Range	-55 to 110°C		
2) Shrink Ratio	Approximately 3:1		
3) Minimum Shrink Temperature	120°C		
4) Tensile Strength	2400psi, Min	ASTM D638	
5) Elongation	475%, Min	ASTM D638	
6) Low Temperature Flex(-55°C)	no cracking	AMS-DTL-23053	
7) Cold Impact(-55°C)	no cracking	ASTM D746	
8) Heat Resistance(175°C,168hrs)	100% Elongation, Min	ASTM D638	
9) Heat Shock(225°C,4hrs)	no cracking	AMS-DTL-23053	
10) Secant Modulus	1.4x10 ⁵ psi, Min	ASTM D882	
11) Longitudinal Change	+1%/-10%	AMS-DTL-23053	
12) Specific Gravity	1.28, Max	ASTM D792	
13) Shelf Life	25 Years @ 18 to 35°C		
Electrical Properties			
1) Dielectric Strength	500 V/mil, Min	ASTM D876	
2) Volume Resistivity	1x10 ¹⁵ ohm-cm, Min	ASTM D876	
Chemical Properties			
1) Water Absorption	0.02%, Max	ASTM D570	
2) Corrosion(175°C,16hrs)	no corrosion	AMS-DTL-23053	
3) Fungus Resistance	Pass	AMS-DTL-23053	
4) Halogen Free	No		
5) Lead Free	Yes		

Other

Packaging

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207 Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY

Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. ©2013 ALPHA WIRE - all rights reserved.