
Top Shelf Acoustics

Specification Part Number: TM141030





Revision	Date	Comments
A	January 18, 2017	Initial Release

www.topshelfacoustics.com Please contact Top Shelf Acoustics for sales inquiries or integration assistance of your microphone at sales@tsacoustics.com or Miranda Ullrich at (P) 317.512.4569 Copyright © Top Shelf Acoustics, LLC. All rights reserved.

1


1. ELECTRICAL SPECIFICATIONS

Standard Conditions		Basic Test Conditions	
Temperature	5 to 35°C	Temperature	20 ± 2°C
Humidity	45 to 85%	Humidity	63 to 67%
Air Pressure	86 to 106kPa	Air Pressure	86 to 106kPa


r			
Parameter		SPEC	Unit
	Directional Characteristic	Omni-Directional	_
	Sensitivity	-40 ±2	dB
	Impedance	1.5(Max)	kΩ
S/N Ratio (A weighted network)		60(Min)	dB
Maximum Input Sound Pressure Level		115	dB
Standard Operating Voltage		5.0	Vdc
Operating Voltage Range		1.0~10	Vdc
Decrease Voltage Characteristics (Vs=2.0 to 1.5V dc)		-3(Max)	dB
Current Consumption		500	μA
Standard Test Circuit		See Fig. 1	—
Frequency Response Characteristic		See Fig. 2	—
Memo Standard test condition		RL=1.5kΩ, Vs=5 (@f=1kHz, Pin=1Pa, 0 L=50cm)	



2. STANDARD TEST CIRCUIT



3. TYPICAL FREQUENCY RESPONSE IN ANECHOIC CHAMBER



www.topshelfacoustics.com Please contact Top Shelf Acoustics for sales inquiries or integration assistance of your microphone at sales@tsacoustics.com or Miranda Ullrich at (P) 317.512.4569 Copyright © Top Shelf Acoustics, LLC. All rights reserved.

4. RELIABILITY

	ltem	Test conditions	Evaluation standard
1	Hi-Temp.Test	The microphone unit must be subjected to +70℃ for 100 hours and exposed to room temperature for 3 hours.	
2	Low-Temp.Test	The microphone unit must be subjected to -40℃ for 100 hours and exposed to room temperature for 3 hours.	
3	Humidity &Heat Test	The microphone unit must be subjected to +55℃, 90% RH-for 100 hours and exposed to room temp for 3 hours.	
4	Thermal Shock Test	The microphone unit must be subjected to following condition [+70 $^{\circ}$ C 0.5H \rightarrow room temp 1H \rightarrow -40 $^{\circ}$ C 0.5H \rightarrow room temp 1H]at 10 cycles and exposed to room temp for 3 hours.	After any of the tests, the sensitivity of the microphone unit shall not change more than $\pm 3 {\rm dB}$ from initial value and
5	Vibration Test	The microphone unit must be subjected to a procedure that it is vibrating for two hours from each of the three directions(x y z) with a frequency of 10-55Hz and a 1.52mm-high amplitude.	shall keep its initial operation and appearance.
6	Drop Test	The microphone unit must be subjected to a procedure that it is dropped on a slippery marble floor for 5 times from a 1.0-meter- height without package.	
7	Storage Temperature	-40℃~+70℃ R.H. less than 90%	
8	Operating Temperature	-35℃~+70℃ R.H. less than 90%	

All the soldering procedures upon microphones must be completed in a heat sink device. The temperature of the soldering iron must be limited to 360°C±10°C and the soldering time should not exceed 3 seconds.

Operators, the soldering fixture and the soldering iron must be statically grounded under each soldering process.