CompactDAQ Sound and Vibration Measurement Bundle

Modular Data Acquisition Bundles For Sound and Vibration

Use NI DAQ sound and vibration bundle for:

- Quick sound and vibration logging
- System-level validation
- Frequency testing
- Measurement and acoustic characterization



Popular Features

Sensor Compatibility

Smart TEDS sensor compatibility with internal signal conditioning

Rugged

-40° to 70° C Temp range 50g shock

Coupling

Software-selectable AC/DC coupling and IEPE signal conditioning with AC coupling



Hardware Bundle for Sound and Vibration Sensors

Spend less time configuring your test bundle and more time testing your products with NI's temperature measurement bundles based on CompactDAQ hardware.

	cDAQ-SV1100 P/N: 865665-01	cDAQ-SV1101 P/N: 865664-01	cDAQ-SV4202 P/N: 868017-01					
What's in the Box?								
Chassis	cDAQ-9171	cDAQ-9171	cDAQ-9174					
Module(s)	NI 9231 (x1)	NI 9234 (x1)	NI 9234 (x2)					
Accessories	 USB cable (A to B) with captive screw 	 USB cable (A to B) with captive screw 	 USB cable (A to B) with captive screw Desktop Mounting Kit AC/DC power supply* *IEC power cord sold separately 					
Specifications (chassis)								
Slots		4						
Power Required	USB 2.0 B	9-31 VDC						
Dimensions (unloaded)	131.4 mm × 88.6 (5.17 in. × 3.49	159.5 mm × 88.1 mm × 58.9 mm (6.28 in. × 3.47 in. × 2.3 in.)						
Operating Temp	-40° to 70° C							
Operating shock/vib	50 g shock and 5 g vibration							
Specifications (module)								
Connectivity	Coaxial Jack	BNC	BNC					
Channels	8	4	8 (total)					
Sample Rate	51.2 kS/s	51.2 kS/s/ch	51.2 kS/s/ch					
Isolation	Channel-Earth							
Resolution	24-bit							



Replacement and Upgrade Options for Sound and Vibration Sensors

Need more channels or a different sample rate? NI offers more Sound and Vibration Modules for your sound and vibration test needs.

Sound and Vibration Modules

System Need	Connectivity	Ch	Sample Rate	Isolation	Model/PN
Lowest Module Cost	BNC	3	12.8 kS/s/ch Simultaneous	60 VDC Channel-Earth	NI-9230
Lowest cost/channel	10-32 Coaxial	8	51.2 kS/s/ch Simultaneous	None	NI-9231*
Fastest Sample Rate	BNC	3	102.4 S/s/ch Simultaneous	60 VDC Channel-Earth	NI-9232
General Use	BNC	4	51.2 kS/s/ch	None	NI-9234*

*In the Sound and Vibration Measurement Bundles

Other Popular Measurement Types

Measurement	Connectivity	Ch	Sample Rate	Isolation	Model/PN
Thermocouple	Spring terminal	16	74 S/s Multiplexed	Channel- Earth	NI-9213
Voltage Input	Spring Terminal	4	250 kS/s Multiplexed	Channel- Earth	NI-9205
Load, Pressure, Strain	RJ-50 (accessories sold separately)	4	50 kS/s/ch Simultaneous	Channel- Earth	NI-9237
Voltage, current, strain, thermocouple, RTD, 1/4 1/2 full bridge	Spring terminal	4	100 S/sec Simultaneous	Channel- Channel	NI-9219

CompactDAQ Chassis

Need more than four modules or a different connectivity?

Select the chassis that meets your needs. All hardware use the same software driver.

- Ethernet: 1, 4, and 8-Slot chassis
- USB: 1, 4, 8, 14-Slot chassis
- Wi-Fi: 1-Slot chassis



Contact your NI product expert to get help solving your test challenges.

Improve Test Performance with NI Software

Build an Automated Test System with LabVIEW

- Acquire data from NI hardware, 3rd party instruments, and many industry-standard protocols
- Create interactive UIs for test monitoring and control.
- Process with standard math, probability, and statistical functions.
- Integrate code written in Python, C/C++, .NET, and MathWorks MATLAB® software.
- Save data to .csv, .tdms, or any custom-defined binary file.


Perform Quick Tests with FlexLogger No-Code Software

- Configure quick tests with alarms, test properties, and real-time data displays
- Simplify sensor measurement with sensor-specific templates
- Log test results to .tdms or .csv files
- Add calculations for simple math, filtering, Boolean logic, and more
- Review data with an included interactive TDMS file viewer

Develop with Your Preferred Programming Language

- Python
- C, C+, C#
- .NET
- MATLAB® (Contact MathWorks® for the Data Acquisition Toolbox)

*MATLAB is a registered trademark of The MathWorks, Inc.



""FlexLogger makes it easier to troubleshoot and verify that the raw data from different sensors are correct before I start my test. This helps shorten test development by saving time typically wasted on redoing configurations."

> - Andy Tarman, Lab Test Engineer CNH Industrial

Test Workflow

NI's recommended, and affordable, collection of software for engineers working on research, validation, and production test applications.



Includes: LabVIEW, FlexLogger, DIAdem, and G Web Development Software

