


Specification Part Number: TM141059

<u>Description: Uni-Directional (Cardioid) Electret Condenser Microphone</u> (Size: 9.7mm x 5mm) RoHS Compliant



Revision	Date	Comments
A	March 1, 2023	Initial Release




1. ELECTRICAL SPECIFICATIONS

Standard Conditions		Basic Test Conditions	
Temperature	5 to 35°C	Temperature	20 ± 2°C
Humidity	45 to 85%	Humidity	63 to 67%
Air Pressure	86 to 106kPa	Air Pressure	86 to 106kPa


	Parameter	SPEC	Unit
Directional Characteristic		Uni-directional	dB
Sensitivity		-47±3	dB
Impedance		1 (Max)	kΩ
S/N Ratio (A weighted network)		65 (Typ)	dB
Maxir	num Input Sound Pressure Level	110 THD≤1%	dB
Standard Operating Voltage		4.5	Vdc
Operating Voltage Range		1.0~10.0	Vdc
Decrease Voltage Characteristics (Vs=2.0 to 1.5V dc)		-3(Max)	dB
Current Consumption		500 (Max)	μΑ
Standard Test Circuit		See Fig. 1	_
Frequency Response Characteristic		See Fig. 2	_
		RL= 2.7kΩ, Vs=4 (@f=1kHz, Pin=1Pa, 0 L=50cm)	




2. STANDARD TEST CIRCUIT



3. TYPICAL FREQUENCY RESPONSE IN ANECHOIC CHAMBER







4. RELIABILITY

	Item	Test conditions	Evaluation standard
1	Hi-Temp.Test	The microphone unit must be subjected to +85℃ for 100 hours and exposed to room temperature for 3 hours.	
2	Low-Temp.Test	The microphone unit must be subjected to -40℃ for 100 hours and exposed to room temperature for 3 hours.	
3	Humidity &Heat Test	The microphone unit must be subjected to +55℃, 85% RH-for 100 hours and exposed to room temp for 3 hours.	
4	Thermal Shock Test	The microphone unit must be subjected to following condition [+80 $^{\circ}$ C 0.5H \rightarrow room temp 1H \rightarrow -40 $^{\circ}$ C 0.5H \rightarrow room temp 1H]at 10 cycles.	
5	Vibration Test	The microphone unit must be subjected to a procedure that it is vibrating for two hours from each of the three directions(x y z) with a frequency of 10-55Hz and a 1.52mm-high amplitude.	After any of the tests, the sensitivity of the microphone unit shall not change more than ± 3 dB from initial value and shall keep its initial operation and appearance.
6	Drop Test	The microphone unit must be subjected to a procedure that it is dropped on a slippery marble floor for 5 times from each axis for a total of 5 times from a 1.0-meter-height without packaging.	
7	Storage Temperature	-35℃~+60℃ R.H .less than 90%	
8	Operating Temperature	-35℃~+60℃ R.H. less than 90%	
9	ESD Protection	The test microphone must be discharged between each ESD exposure without ground(contact:±6KV,air:±8KV)	

NOTES:

All the soldering procedures upon microphones must be completed in a heat sink device. The temperature of the soldering iron must be limited to 360°C±20°C and the soldering time should not exceed 3 seconds.

Operators, the soldering fixture and the soldering iron must be statically grounded under each soldering process.