

Specification Part Number: TM141049


Description: RF Immune Bi-Direction! Noise Cancelling

Electret Condenser Microphone (Size: 9.7mm x 5.2mm)

RoHS Compliant

Pin Material: Cu / Plating Au

Case Material: Al and Mg Alloys



Revision	Date	Comments
Α	August 8, 2021	Initial Release



1. ELECTRICAL SPECIFICATIONS


Standard Conditions		Basic Test Conditions	
Ordinary Temperature	5 to 35°C	Temperature	20 ± 2°C
Ordinary Humidity	45 to 85%	Humidity	63 to 67%
Ordinary air pressure	86 to 106kPa	Ordinary air pressure	86 to 106kPa

	Parameter	SPEC	Unit
	Directional Noise Cancelling		-
	Sensitivity		dB
	Impedance	2.2(Max)	kΩ
S/I	S/N Ratio (A weighted network) 56(typ)		dB
Maximum Input Sound Pressure Level 110(Max)		dB	
,	Standard Operating Voltage 2		Vdc
Operating Voltage Range 1.0~10		Vdc	
Decrease Voltage Characteristics (Vs=2.0 to 1.5V dc)		-3(Max)	dB
Current Consumption 500(Max)		μΑ	
	Standard Test Circuit See Fig. 1 -		_
Fred	Frequency Response Characteristic See Fig. 2 —		_
Memo	Memo Standard test condition RL=2.2kΩ, Vs=2V dc (@f=1kHz, Pin=1Pa, 0dB=1V, L=50cm)		



2. STANDARD TEST CIRCUIT


Fig.1





3. TYPICAL FREQUENCY RESPONSE IN ANECHOIC CHAMBER

Fig.2



4. RELIABILITY

	Item	Test conditions	Evaluation standard
1	Hi-Temp. Test	The microphone unit must be subjected to +80℃ for 100 Hours and exposed to room temperature for 3 Hours.	
2	Low-Temp. Test	The microphone unit must be subjected to -40°C for 100 Hours and exposed to room temperature for 3 Hours.	After any of the tests, the sensitivity of the microphone unit shall not change
3	Humidity & Heat Test	The microphone unit must be subjected to +55℃, 85% RH-for 100 Hours and exposed to room temp for 3 Hours.	more than ± 3 dB from initial value and shall keep its initial operation and appearance.
4	Thermal Shocking Test	The microphone unit must be subjected to following condition [+80°C 0.5H → room temp 1H→ -40°C 0.5H →room temp 1H] at 10cycle.	



5	Vibration Test	The microphone unit must be subjected to a procedure that it is vibrating for two hours from each of the 3 directions(x y z) with a frequency of 10-55Hz and a 1.52mm-high amplitude.
6	Drop Test	The microphone unit must be subjected to a procedure that it is dropped on a slippery marble floor for 5 times from each axis for a total of 15 times from a 1.0-meter-height without packaging.
7	Storage Temperature	-35℃~+60℃
8	Operating Temperature	-35℃~+60℃
9	ESD Protection	The test microphone must be discharged between each ESD exposure without ground(contact :±6KV,air:±8KV)

NOTES:

All the soldering procedures upon microphones must be completed in a heat sink device. The temperature of the soldering iron must be limited to 360°C±20°C and the soldering time should not exceed 3 seconds.

Operators, the soldering fixture and the soldering iron must be statically grounded under each soldering process.