

GLF73912/ GLF73915 Ultra-Efficient I_QSmart[™] Battery Protection IC

DESCRIPTION

The EV011-GLF73912/ GLF73915 evaluation board features the GLF73912/ GLF73915 that is an IoSmartTM ultra-efficient, full battery protection IC with an accurate over charge voltage, over discharge voltage, shipping mode, over charge current, and short circuit protection for lithium-Ion/Polymer battery safety.

The over charge and discharge voltage protections keep a rechargeable battery working within the desired safe operating condition. When the battery is charged past the over voltage detection level, the GLF73912/ GLF73915 charging switch opens in a preset delay time. As the battery voltage decreases below the over discharge detection voltage level, the GLF73915 discharging switch is turned off immediately to cut off the battery power rail, consuming an ultralow leakage current (I_{SD}) to save the battery. In addition, when the load current reaches the I_{SC} short circuit protection level, the GLF73912/ GLF73915 is turned off and will maintain the off state to avoid any serious damage to system. The short circuit delay time avoids any false trigger which might open the switch.

The GLF73915 provides a shipping mode pin to prevent smart devices with a non-removable battery from discharging during the shipping period. When a charged battery cell is connected the GLF73912/ GLF73915 remains in the off state and consumes an ultra-low leakage current (I_{SD}) until the V_{ON} voltage is applied to VOUT pin. Note that the GLF73912/ GLF73915 is activated only by a V_{ON} voltage from a charger output.

FEATURES

- Over Charge Detection, Voc: 4.35 VBAT
- Over Discharge Detection, VoD: 2.80 VBAT
- Ioc. Over Charge Current Detection
- Load Short Circuit Protection with Delay Time to avoid a false trigger
- Activated by Applying V_{ON} to the **VOUT Pin from Charger**
- 1.5 A Continuous Charging Current Capability from VOUT to VBAT Pin
- Low R_{ON}: 57 m Ω Typ. @ 3.6 V_{BAT}
- **Quiescent Current:** $I_Q = 940 \text{ nA Typ.} @ 3.6 V_{BAT}$
- **Shutdown Current**
 - \circ I_{SD} = 7 nA Typ. @ V_{BAT} < V_{OD}
 - I_{SD} = 8 nA Typ. @ V_{BAT} = 3.6 V, Shipping
 - \circ I_{SD} = 9 nA Typ. @ V_{BAT} = 4.2 V, Shipping Mode
- Latch-off at Over Discharge Detection and Short Circuit Protection. Apply V_{ON} to VOUT pin to turn on
- Shipping Mode Implementation: GLF73915
- 0 V Battery Minimum Voltage for Charging
- Reverse Polarity Connection Protection
- Patent Pending Circuit Architecture
- HBM: 8 kV, CDM: 2 kV
- 0.97 mm x 0.97 mm x 0.55 mm Chip Scale Package 4 Bumps, 0.5 mm Pitch



PRODUCT TABLE

Eval Board Ordering Info: EV011-GLF73912/ GLF73915

Part Number	Top Mark	RON (Typ) V _{BAT} =3.6 V	Over Charge Detection, VOC	Over Discharge Detection, VOD	Over Charge Current, IOC	Short Circuit Current, ISC	V _{BAT} =0 V Charging	Shipping Mode
GLF73915	CN	57 mΩ	4.35 V	2.80 V	350 mA	0.5 A	Available	Available
GLF73912	NC	57 mΩ	4.35 V	2.80 V	350 mA	0.5 A	Available	N/A