Q QueLighting



QLSP14RGB_B (2121 PLCC 4 LED)





Product Outline:

This is the small TOP LED with 3 color (Red/Green/Blue) combined in one package. This special package is ideal for customer's application in traffic signal and sign boards on production promotion. With special binning technology, Quelighting is able to provide special binning for customer's needs

Features:

- 3 colors(Red/Green/Blue) LED Package
- High brightness output @ 20mA,
- Package Dimension = 2.1mm x 2.1mm x 1.0mm
- RoHS compliant
- Custom Bin available upon special request
- View angel >120°

Application:

- Architecture Lighting
- Sign board backlighting
- Emergency vehicle lighting
- Traffic signal lighting
- Automotive lighting

Compliance and Certification:







Mechanical Property:





(Dimension)






* All

dimensions are in millimeters, * Tolerances are ± 0.10mm.

Recommended Solder footprint:



Reference Soldering Pad

- * All dimensions are measured in mm
- * The LEDs is designed to be reflow soldered on to a PCB. IF dip soldered that QL cannot guarantee its reliability.
- * Reflow soldering must not be performed more than twice.





Characteristics

■ Absolute Maximum Ratings

(Ta=25°C)

Parameter	Symbol	Rating	Unit
DC Forward Current RGB	3 I _f 20		mA
	Pd (R)	90	
Power Dissipation	Pd (G)	100	mW
	Pd (B)	100	
Pulse Forward Current (RGB)	I _{fp}	100	mA
Storage Temperature	T _{st}	-40 ~ +100	೦ೆ
Operation Temperature	Тор	-40 ~ +85	$^{\circ}$
Soldering Temperature	T _{sol}	260 < 10 sec	$^{\circ}$

⁽¹⁾ Proper current rating must be observed to maintain junction temperature below maximum at all time



⁽²⁾ IFP Condition: Duty 1/10, Pulse within 10msec



■ Electrical / Optical Characteristic @20mA

(Ta=25 °C)

Electrical / Optical Characteristic @zoniA (1)							
Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit	
		R	700		1000		
Luminous Intensity	lv	G	1800		2200	mcd	
		В	400		600		
		R	2.0		2.4		
Forward Voltage	Vf	G	2.9		3.3	V	
		В	3.0		3.4		
Reverse Voltage	V _R				5	V	
Reverse Current	I _R				5	μA	
		R	620		625		
Dominant Wavelength	$\lambda_{ m d}$	G	520		525	nm	
		В	465		470		
View Angle	θ			120		deg	

⁽¹⁾ Tolerance of measurement (luminous intensity): ±15%


⁽²⁾ Tolerance of Forward Voltage: ±0.05V

⁽³⁾ Tolerance of Peak emission wavelength: ±1.0nm



■ Color Bin Code:

A. F.								_									
色区	Bin	MinIv	MaxIv	x1	y1	x2	y2	x 3	y3	z4	y4	MinVF	MaxVF	MinVF	MaxVF	MinVF	MaxVF
A1	1	2500	2800	0. 2467	0. 2551	0. 2486	0.2676	0. 2625	0.2655	0.2606	0. 253	2. 1	2.2	2. 9	3.0	2.9	3.0
	2	2500	2800	0. 2467	0.2551	0. 2486	0.2676	0. 2625	0.2655	0.2606	0. 253	2. 1	2.2	2. 9	3.0	3. 0	3. 1
A2	3	2500	2800	0. 2486	0.2676	0. 2504	0.2801	0. 2643	0. 278	0.2625	0. 2655	2. 1	2.2	2. 9	3.0	2.9	3.0
82	4	2500	2800	0. 2486	0.2676	0. 2504	0.2801	0. 2643	0. 278	0. 2625	0. 2655	2. 1	2.2	2. 9	3.0	3. 0	3. 1
	5	2500	2800	0. 2504	0.2801	0. 2523	0.2926	0. 2662	0.2905	0.2643	0. 278	2. 1	2.2	2. 9	3.0	2. 9	3.0
A3	6	2500	2800	0. 2504	0.2801	0. 2523	0.2926	0. 2662	0.2905	0.2643	0. 278	2. 1	2.2	2. 9	3.0	3.0	3. 1
	7	2500	2800	0. 2523	0. 2926	0. 2542	0.3051	0. 2681	0. 303	0.2662	0. 2905	2. 1	2.2	2. 9	3.0	2. 9	3.0
A4	8	2500	2800	0. 2523	0. 2926	0. 2542	0.3051	0. 2681	0.303	0.2662	0. 2905	2. 1	2.2	2. 9	3.0	3. 0	3. 1
	9	2500	2800	0. 2542	0.3051	0. 2561	0.3176	0. 27	0.3155	0.2681	0.303	2. 1	2.2	2. 9	3.0	2.9	3.0
A5	10	2500	2800	0. 2542	0.3051	0. 2561	0.3176	0. 27	0.3155	0.2681	0.303	2. 1	2.2	2. 9	3.0	3.0	3.1
	11	2500	2800	0. 2606	0.253	0. 2625	0.2655	0. 2764	0.2634	0. 2745	0. 2509	2. 1	2.2	2. 9	3.0	2. 9	3.0
B1	12	2500	2800	0. 2606	0.253	0. 2625	0.2655	0. 2764	0.2634	0. 2745	0. 2509	2. 1	2.2	2. 9			
	13	2500	2800	0. 2625	0. 2655	0. 2643	0.278	0. 2782	0.2759	0.2764	0. 2634	2. 1	2.2	2. 9			
B2	14	2500	2800	0. 2625	0. 2655	0. 2643	0.278	0. 2782	0.2759	0.2764	0. 2634	2. 1	2.2	2. 9			
	15	2500	2800	0. 2643	0.278	0. 2662	0.2905	0. 2801	0. 2884	0.2782	0. 2759	2. 1	2.2	2. 9	3.0	2. 9	
В3	16	2500	2800	0. 2643	0.278	0. 2662	0.2905	0. 2801	0. 2884	0.2782	0. 2759	2.1	2.2	2.9	3.0	3. 0	
	17	2500	2800	0. 2662	0. 2905	0. 2681	0.303	0.282	0.3009	0.2801	0. 2884	2. 1	2.2	2. 9	3.0	2.9	3.0
B4	18	2500	2800	0. 2662	0. 2905	0. 2681	0.303	0.282	0.3009	0.2801	0. 2884	2. 1	2. 2	2. 9	3.0	3. 0	3. 1
B5	19	2500	2800	0. 2681	0.303	0.27	0.3155	0. 2839	0.3134	0.282	0. 3009	2. 1	2.2	2. 9	3.0	2.9	3.0
20	20	2500	2800	0. 2681	0.303	0.27	0.3155	0. 2839	0.3134	0.282	0. 3009	2. 1	2.2	2. 9	3.0	3. 0	3. 1
C1	21	2500	2800	0. 2745	0.2509	0. 2764	0.2634	0. 2903	0.2613	0.2884	0. 2488	2. 1	2.2	2. 9	3.0	2. 9	3.0
	22	2500	2800	0. 2745	0.2509	0. 2764	0.2634	0. 2903	0.2613	0.2884	0. 2488	2. 1	2.2	2. 9	3.0	3.0	3. 1
C2	23	2500	2800	0. 2764	0.2634	0. 2782	0.2759	0. 2921	0.2738	0.2903	0.2613	2. 1	2.2	2. 9	3.0	2.9	3.0
	24	2500	2800	0. 2764	0.2634	0. 2782	0.2759	0. 2921	0.2738	0.2903	0.2613	2. 1	2.2	2. 9	3.0	3. 0	3. 1
сз	25	2500	2800	0. 2782	0.2759	0. 2801	0.2884	0.294	0.2863	0.2921	0. 2738	2. 1	2.2	2. 9	3.0	2.9	3.0
	26	2500	2800	0. 2782	0.2759	0. 2801	0.2884	0.294	0.2863	0.2921	0. 2738	2. 1	2.2	2. 9	3.0	3.0	3. 1
C4	27	2500	2800	0. 2801	0.2884	0. 282	0.3009	0. 2959	0.2988	0.294	0. 2863	2. 1	2. 2	2. 9	3.0	2.9	3.0
	28	2500	2800	0. 2801	0.2884	0. 282	0.3009	0. 2959	0.2988	0.294	0. 2863	2. 1	2.2	2. 9	3.0	3.0	3.1
C5	29	2500	2800	0. 282	0.3009	0. 2839	0.3134	0. 2978	0.3113	0.2959	0. 2988	2. 1	2.2	2. 9	3.0	2.9	3.0
	30	2500	2800	0. 282	0.3009	0. 2839	0.3134	0.2978	0.3113	0.2959	0. 2988	2. 1	2.2	2. 9	3.0	3. 0	3. 1





*Tolerance = +/- 10%








■ Characteristic Curves


















■ Reliability test:

No	Item	Condition	Time/Cycle	Sample size
1	Steady State Operating Life of Room Temperature	25 [°] C Operating	1000 Hrs	20 pcs
2	Steady State Operating Life of Low Temperature -40°C	-40°C Operating	1000 Hrs	20 pcs
3	Steady State Operating Life of Low Temperature 60°C	60℃ Operating	1000 Hrs	20 pcs
4	Steady State Operating Life of Low Temperature $85^{\circ}\!\mathbb{C}$	85℃ Operating	1000 Hrs	20 pcs
5	Low temperature storage -40°C	-40°C Storage	1000 Hrs	20 pcs
6	High temperature storage 100°C	100°C Storage	1000 Hrs	20 pcs
7	Steady State Operating Life of High Humidity Heat 60°C 90%	60°C/90% Operating	1000 Hrs	20 pcs
8	Steady State Pulse Operating Life Condition	25°C10Hz duty=1/10 Operating	200 Cycle	20 pcs
9	Resistance to soldering heat on PCB (JEDEC MSL3)	pre-store@60℃, 60%RH for 52hrs Tsld max.=260 10sec	3 Times	20 pcs
10	Heat Cycle Test (JEDEC MRC)	25℃ ~65℃ ~-10℃ , 90%RH, 24hr/1cycle	10 Cycle	20 pcs
11	Thermal shock	-40°C/ 20minr~ 5minr~100°C /20min	100 Cycle	20 pcs

■ Judgment Criteria:

ltem	Symbol	Test Condition	Judgment Criteria
Forward Voltage	Vf	20 mA	△Vf< 10%






■ Solder Profile:

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):







- 1. We recommend the reflow temperature 245°C (+/-5°C). The maximum soldering temperature should be limited to 260°C.
- Don't cause stress to the epoxy resin while it is exposed to high temperature.
- 3. Number of reflow process shall be 2 times or less.





■ Taping & Packing:






Unit: mm



Reel Dimension



Unit: mm



■ Labeling

QueLighting

Quantity: XXXX

Quelighting P/N: XXXXXX

Lot number: XXXXX

lv Bin: XX Color Bin: XX Vf Bin: XX Date Code: XXXX

■ Ordering Information:

Part #	Multiple Quantities	Quantity per Reel
QLSP14RGB_B PLCC 4	Sampling stage	4,000 pcs
	MP stage	10,000 pcs





■ Revision History:

Revision Date:	Changes:	Version #:				
04-20-2021	Initial release	1.0				
5-12-2021	Added 4k reel	1.1				
5/10/2022	Revise bin structure	1.2				
7/12/2022	Added 10k reel for MP	1.3				
2/16/2023	Revised solder foot print.	1.4				