Miniature Waterproof Shielded Connectors

LF Series



Mated dimensions (Example: LF07) 8.9 mm max. (3 pos.) 36.4 Receptacle / Plug Fig. 1

■Features

1. Ease of shielded termination and connector assembly

All components are self-aligning and do not require complex assembly tooling. The shield of the cable is connected with the metal housing of the connector using simple shielding clamp, supplied with the connector. (Fig. 2)

2. Water and dust protected

The LF series is a rugged, waterproof connector series that is IP67 and IP68 rated in the mated condition.

IP67: Left in water at a depth of 1 m for 30 minutes IP68: Left in water at a depth of 2 m for 14 days

3. Simplified assembly procedure

No use of screws makes wiring and mounting easier.

4. Bayonet lock


Short turn bayonet lock assures secure vibration resistant mating of the connectors. (Fig. 3)


5. Acquired safety standard

4 pos. is 10A and meets safety standards (TÜV) Also 3- and 4-pos. have acquired the UL standard.

6. High current rating capacity

No. of contacts	Current rating
3	5A max.
4	10A max.
6, 12 and 20	2A max.
11	10A max.
11	2A max.





■Product Specifications

	Voltage rating	125V AC, 175V DC (3 pos.) 125V AC, 125V DC (4 pos.) 30V AC, 42V DC (6 pos., 12pos., 20pos.) 125V AC, 125V DC (11 pos. A to D) 30V AC, 42V DC (11 pos. 1 to 7)
Ratings	Current rating	5A max. (3 pos.) 10A max. (4 pos.) 2A max. (6 pos. , 12pos. , 20pos.) 10A(11 pos. A to D), 2A(11 pos. 1 to 7)
	Operating temperature range	–25°C to +85°C
	Storage temperature range	-10℃ to +60℃

Item	Specifications	Conditions
1.Contact resistance	15mΩ max. (3, 6, 12, 20 pos.) 5mΩ max. (4 pos.) 5mΩ max. (A to D), 15mΩ max. (1 to 7)(11 pos.)	1A DC
2.Insulation resistance	1000MΩ min.	500V DC (3, 4 pos.) 100V DC (6, 12, 20 pos.) 500V DC (A to D), 100V DC (1 to 7)(11pos.)
3.Withstanding voltage	No flashover or insulation breakdown.	1250V AC/one minute (3, 4 pos.) 300V AC/one minute (6, 12, 20 pos.) 1250V AC(A to D),300V AC(1 to 7) / one minute(11pos.)
4.Vibration	No electrical discontinuity for 10μ s max.	10 → 55 → 10Hz /cycle, single amplitude of 0.75mm five minutes / cycle, three directions, 10 cycles for each direction.
5.Shock	No electrical discontinuity for 10 μ s max	Acceleration of 490m/s², duration of 11ms, three directions, three times for each direction.
6.Durability (Mating/un-mating)	30mΩ max. (3, 6, 12, 20 pos.) 10mΩ max. (4 pos.) 10mΩ max. (A to D), 30mΩ max.(1 to 7)(11pos.)	1000 cycles
7.Temperature cycle	Insulation resistance: 100MΩ min.	Temperature: -55°C → Room temperature → +85°C → Room temperature Time: $30 \rightarrow 2$ to $3 \rightarrow 30 \rightarrow 2$ to 3 (minutes) 5 cycles
8.Humidity	Insulation resistance: $10M\Omega$ min. (at high humidity condition) Insulation resistance: $100M\Omega$ min. (at dry condition)	96 hours at temperature of 40°C and humidity of 90% to 95%.
9.Water / dust protection	When mated with corresponding connector.	Complete dust protection. No water penetration when submerged for 48 hours at the depth of 1.8 meter.

■Materials / Finish

Components	Material	Finish / Color	Remarks
Body / back shell	Zinc alloy	Nickel plated	
Insulator	PPS	Black	UL94V-0
Contacts	Copper alloy	Selective Gold plated	
Packing	Chloroprene rubber	Black	
Tightening collar	PPS	Brown	UL94V-0


■Product Number Structure



A 0	1.5
Series name	:LF
Shell size	07
	10
	13
Waterproof	W : Waterproof type
4 Lock Mechanism	B : Bayonet lock
6 Connector type	P : Plug
	R : Receptacle
	J: Jack
	(*:Form change zoning symbols in an identical class)
No. of contacts	: 3, 4, 6, 11, 12, 20
Contact type	P : Male contact
	S : Female contact

■Plugs






U	nit	:	mm

						•
Part No.	HRS No.	No. of contacts	φA	В	φC	Weight
LF07WBP-3S	136-0003-7	3				
LF07WBP-3P	136-0004-0	3	10.0	05.0	5	11
LF07WBP-6S	136-0001-1	6	12.3	35.8	5	11g
LF07WBP-6P	136-0002-4	0				
LF10WBP-4S	136-0005-2	4	14.8	41.8		
LF10WBP-4P	136-0006-5	4			7.3	17g
LF10WBP-12S	136-0007-8	12			7.3	
LF10WBP-12P	136-0008-0	12				16g
LF13WBP-20S	136-0009-3	20		51.9		
LF13WBP-20P	136-0010-2	11	17.9		8.7	200
LF13WBP-11S	136-0011-5		17.9		0.7	29g
LF13WBP-11P	136-0012-8					

●Lock ease type





(Representative example.)


Unit: mm

Part No.	HRS No.	No. of contacts	φA	В	φC	Weight
LF07WBPD-6S	136-0020-6	6	14.3	35.8	5	12g
LF10WBPD-4S	136-0014-3	4	100	41.8	7.3	
LF10WBPD-4P	136-0017-1] 4				100
LF10WBPD-12S	136-0015-6	12	16.8	41.0	7.3	19g
LF10WBPD-12P	136-0018-4	12				

■Receptacles

●Front panel mount type · Solder Type






(Representative example.)

Unit: mm

Part No.	HRS No.	No. of contacts	φA	φB	С	D	Е	F	Weight	
LF07WBR-3P	136-1003-2	3			10.55					
LF07WBR-3S	136-1004-5	3	10.3	13	16.55	7.65	M9×0.75	11	10	
LF07WBR-6P	136-1001-7	6	10.3	13	15.05	7.65	WI9∧U.75	''	4g	
LF07WBR-6S	136-1002-0	0			15.25					
LF10WBR-4P	136-1005-8	4	12.8	15.3	19.05	7.75	M11×0.75	13		
LF10WBR-4S	136-1006-0	4							6g	
LF10WBR-12P	136-1007-3	10	12	12.0	15.5	47.05	7.75	WITT \ 0.75	13	5g
LF10WBR-12S	136-1008-6	12			17.25				6g	
LF13WBR-20P	136-1009-9	20			47.05				9g	
LF13WBR-20S	136-1010-8	20	15.9	18.3	17.25	7.75	M14×0.75	17	10g	
LF13WBR-11P	136-1011-0	11	15.9	10.3	10.05	7.75	W114\0.75	'/	9g	
LF13WBR-11S	136-1012-3	11			19.05				10g	

● Front panel mount type · Through hole Type






(Representative example.)

Unit: mm Part No. HRS No. No. of contacts φΑ φΒ С D Ε Weight LF13WBR-20SD 136-1017-7 20 15.9 18.3 17.5 7.75 M14×0.75 17 9g

■ Receptacles • Rear panel mount type · Solder Type






(Representative example.)

Unit: mm

Part No.	HRS No.	No. of contacts	φA	φB	С	D	Е	Weight
LF10WBRB-4P	136-1118-4	4			19.05			
LF10WBRB-12P	136-1013-6	10	12.8	18.3	17.25	17	M14×0.75	10g
LF10WBRB-12S	136-1014-9	12			17.25			
LF13WBRB-20S	136-1018-0	20	15.9	21.5	19.25	20	M17×0.75	160
LF13WBRB-11S	136-1019-2	11	15.9	21.5	19.25	20	IVI 1 / ~ U. / 5	16g

●Rear panel mount type · Through hole Type






(Representative example.)

Unit: mm

Part No.	HRS No.	No. of contacts	φA	φB	С	D	Е	Weight
LF10WBRB-12PD	136-1015-1	10	12.8	18.3	175	17	M14×0.75	00
LF10WBRB-12SD	136-1016-4	12	12.0	10.3	17.5	17	W14×0.75	9g

■Jacks





(Representative example.)


Unit: mm

Part No.	HRS No.	No. of contacts	φA	ϕ B	С	ϕ D	Weight
LF07WBJ-3P	136-2003-8	3					
LF07WBJ-3S	136-2004-0	3	10.3	11.5	36.3	5	11g
LF07WBJ-6P	136-2001-2	6	10.3	11.5	30.3	5	119
LF07WBJ-6S	136-2002-5	O					
LF10WBJ-4P	136-2005-3	4	12.8	13.8	42.4		
LF10WBJ-4S	136-2006-6	4				7.3	160
LF10WBJ-12P	136-2007-9	12				7.3	16g
LF10WBJ-12S	136-2008-1	12					
LF13WBJ-20P	136-2009-4	20					29g
LF13WBJ-20S	136-2010-3	20	15.9	16.9	52.4	8.7	30g
LF13WBJ-11P	136-2011-6		15.9	16.9		0.7	29g
LF13WBJ-11S	136-2012-9	11					30g

■CAP

●For Receptacles





(Representative example.)

- 1	Init	٠	mn

Part No.	HRS No.	Applicable connector	φA	В	Weight
		LF07WBR-6P			
LF07WBR-C	136-3008-7	LF07WBR-6S	12.3		4.00
LI O7 WOIT O	130-3006-7	LF07WBR-3P	12.3		4g
		LF07WBR-3S			
		LF10WBR-4P			
		LF10WBR-4S			
		LF10WBR-12P			5g
		LF10WBR-12S		8.8	
LF10WBR-C	136-3001-8	LF10WBRB-4P	14.8		
		LF10WBRB-12P			
		LF10WBRB-12S			
		LF10WBRB-12PD			
		LF10WBRB-12SD			
		LF13WBR-20P			
	R-C 136-3003-3	LF13WBR-20S			7g
		LF13WBR-11P			
LF13WBR-C		LF13WBR-11S	17.9		
		LF13WBR-20SD			
		LF13WBRB-20S			
		LF13WBRB-11S			

◆Applicable tools



Unit: mm

Description	Part No.	HRS No.	LF series Applicable cable dia.
Manual cable clamp crimp	HR10A-TC-02	150-0041-2	5 (Note)
	LF-TC-01	150-0234-6	7.3 · 8.7

Note: Applicable cable dia. is only 5mm for LF series.

◆Solder termination fixture




Part No.	HRS No.	Applicable connectors
LF07BP-T01	150-0232-0	LF07WBP-**
LF07BJ-T01	150-0233-3	LF07WBJ-**
LF10BP-T01	150-0235-9	LF10WBP-**
LF10BJ-T01	150-0236-1	LF10WBJ-**
LF13BP-T01	150-0237-4	LF13WBP-**
LF13BJ-T01	150-0238-7	LF13WBJ-**



Note: It is applicable regard less of given alphabets or Numbers shown at *.

♦ Panel Cutout



U					
Shell size	Α	В	Weight		
LF07WBR-**	φ9.05	8.1			
LF10WBR-**	φ11.05	10.2	0.7 to 0		
LF13WBR-**	φ14.05	13.1	0.7 to 2		
LF10WBRB-**		13.1			
LF13WBRB-**	φ17.05	16.1	0.7 to 4.8		

● Contact position arrangement and specifications

Shell size	LF07		LF10			LF	13	
Contact arrangement	3 1	6 1 5 2 4 3	4 1 3 2	9 1 8 (b) 2 7 (2) (1) 3 6 (5) 4	(B) (A) (1) (2) (5) (6)	© © 3 4)7	2345 67890 10896 6089	
No. of contacts	3	6	4	12	1	1	20	
Withstanding voltage	1250V AC	300V AC	0V AC 1250V AC	300V AC	4	7	AC300V	
withstanding voitage	1250V AC	300 V AC	1230V AO 300V AO		AC1250V	AC300V	A0300V	
Current rating	5A	2A	10A	2A	4	7	2A	
Current fatting	SA	ZA	IUA	ZA	10A 2A		ZA	
Insulation resistance	1000ΜΩ					·		
Contact resistance	15mΩ		50	450	4	7	450	
Contact resistance			5mΩ	15mΩ	5mΩ	15mΩ	15mΩ	
Colder not inner diameter	4 4 6	0.0	1.7	0.0000	4	7	0.0000	
Solder pot inner diameter	1.15mm 0.8mm		1.7mm	0.8mm	<i>φ</i> 1.7	<i>φ</i> 0.8	0.8mm	


Note 1: The contact configuration as viewed from the female contact connector mating side.


Note 2 : The ▼ symbol indicates polarizing key position.


Note 3: Withstanding voltages are test voltage values.


Termination and Assembly InstructionsThe connectors are delivered with pre-assembed condition and the disassembly as shown №.1.

No.	Illustration	Operation
1	Solder termination fixture Plug Locking collar Insertion direction	Plug disassembly 1 Insert the plug into securely held solder termination fixture as shown. Fixture Part No. Applicable connector
	Body / insulator assembly Backshell	Loosen the backshell turning it counter clockwise and remove it from the body/ insulator assembly.
	Solder termination fixture Jack Insertion direction	Jack Disassembly 1 Insert the jack into the securely held solder termination fixture as shown. Fixture Part No. Applicable connector
	Body / insulator assembly Backshell	2 Loosen the backshell turning it counterclockwise.
2	Threaded section Tightening collar	Connector Assembly (Manufactured by Henkel Japan, Ltd,) primer to the threaded sections of the backshell and the tightening collar. Completely dry the coated surfaces. Notes (1) Drying time at room temperature is approximately 30 to 70 seconds. (2) Ensure sufficient ventilation of the area at time of drying. (3) Take necessary steps to protect the coated surfaces from contamination.
	2 Backshell Strain relief collar Tightening collar Cable preparation end Gasket Cable	Thread the tightening collar, strain relief collar, seal bushing and the backshell over the cable as illustrated. Notes Threading the components may not be possible after the cable-end finishing process.









◆Cable Specifications (Reference)

I	No. of contact	3 pos.	4 pos.	6 pos.	12 pos.	20 pos.	11 μ	oos.
Conductor	Material	Tin plated soft copper wire						
	Size (mm)	<i>ϕ</i> 0.18	φ0.26	<i>ϕ</i> 0.16	<i>ϕ</i> 0.16	φ0.16	<i>φ</i> 0.26	<i>φ</i> 0.16
	Construction	20 /φ0.18 mm dia.	20 /\phi 0.26 mm dia.	7 /\phi 0.16 mm dia.	7 /\phi 0.16 mm dia.	7 /\phi 0.16 mm dia.	26 /ø0.26 mm dia.	7 /ø0.16 mm dia.
	Size (AWG)	20 AWG	16 AWG	26 AWG	26 AWG	26 AWG	16 AWG	26 AWG
O	Sectional area	0.5	1.25	0.14	0.14	0.14	1.25	0.14
	Diameter (mm)	<i>φ</i> 0.98	φ1.5	<i>φ</i> 0.48	φ0.48	φ0.48	<i>φ</i> 1.5	φ0.48
lator	Diameter (mm)	ϕ 1.5 (Standard)	ϕ 2.1 (Standard)	ϕ 0.88 (Standard)	ϕ 0.9 (Standard)	ϕ 0.9 (Standard)	ϕ 2.1 (Standard)	
Insulator	Thickness (mm)	0.26	0.3	0.2	0.21	0.21	0.3	0.24
٥	Material	Tin plated soft copper wire						
Shield	Density	85%	80% or more	85%	80% or more	80% or more	80% or more	
S	Diameter (mm)	φ3.6	φ5.5	φ3.4	φ4.2	φ5.1	<i>φ</i> 6.7	
Jacket	Diameter (mm)	φ5±0.2	φ7.3±0.2	φ5±0.2	φ7.3±0.2	φ8.7±0.2	φ8.7±0.2	

Remarks: The cable satisfies required specifications for UL specification.

Notes : The cable pull and twisting strength, waterproof tightness and other characteristics may differ, depending on the cable structure, please confirm before the use.



HIROSE ELECTRIC CO.,LTD.

2-6-3,Nakagawa Chuoh,Tsuzuki-Ku,Yokohama-Shi 224-8540,JAPAN TEL: +81-45-620-3526 Fax: +81-45-591-3726 http://www.hirose.com

http://www.hirose-connectors.com