

TMR1348

MicroAmpere High Frequency Response Omnipolar Magnetic Switch Sensor

Description

TMR1348 is an omnipolar magnetic switch integrated the tunneling magnetoresistance (TMR) magnetic sensor and CMOS circuitry, which is able to detect the change of magnetic field and output high and low voltage signals for high accuracy position detection.

Unlike Hall/AMR sensors, TMR sensors with extremely high resistance values allows TMR1348 to achieve the supply current as low as 1.5μ A while operating in the full-time power supply mode, and maintaining high-speed operation with the response frequency at 1 kHz. Therefore, TMR1348 can provide true continuous detection of magnetic field signals, avoiding sampling errors from the traditional time-sharing power supply mode.

TMR1348 allows a wide range of operating supply voltages from 1.8 V to 5.5 V with excellent temperature characteristics, and can meet the requirements of most applications.


SOT23-3



- Tunneling magnetoresistance (TMR) technology
- Low power consumption: supply current 1.5 µA
- High frequency response: typ.1 kHz
- Omnipolar operation
- Wide range supply voltages: 1.8 V to 5.5 V
- Open-drain output
- High sensitivity
- Excellent temperature stability
- High tolerance to external magnetic field interference
- RoHS & REACH compliant
- AEC-Q100 qualified
- MSL1

Applications

- Utility meters: water, gas, and heat meters
- Proximity switches
- Speed sensing
- · Linear and rotation position sensing
- Wake-up switches
- Liquid level sensors







Selection Guide

Part Number	Supply Current	Response Frequency	Operating Ambient Temperature	Operating Point	Release Point	Package	Packing Form
TMR1348S	1.5 µA	1 kHz	-40 °C to 125 °C	±14 Gs	±10 Gs	SOT23-3	Tape & Reel

Note: Please contact MultiDimension Technology local sales for customizing operating and release points.

Catalogue

1. Functional Block Diagram0	3
2. Switching Characteristics0	3
3. Pin Configuration0	3
4. Absolute Maximum Ratings0	4
5. Electrical Specifications0	4
6. Magnetic Specifications0	4
7. Typical Supply Voltage Characteristics0	5
8. Typical Temperature Characteristics0	5
9. Application Information0	6
10. Dimensions0	7



.



1. Functional Block Diagram

TMR1348 series switch chips are composed of TMR sensors and signal processing circuits. The TMR sensor detects external magnetic field, generates an analog voltage signal, and outputs a logical switch level after processing by the circuits as shown in Figure 1.




Figure 1. Block diagram

2. Switching Characteristics

The Figure 2 shows the sensing direction is parallel to the silkscreen surface of the package as shown by the arrow.




Figure 2. Sensing direction

The output is "High", when power is on at zero magnetic field. B is the external magnetic field along the sensing direction, B_{OPS} (B_{OPN}) is the operating point, B_{RPS} (B_{RPN}) is the release point, and hysteresis B_{H} is define as the difference between B_{OPS} and B_{RPS} (B_{OPN} and B_{RPN}).

The sensor outputs a low level, when the magnetic field along the sensing axis exceeds the operate point B_{OPS} (B_{OPN}), and the device outputs a high level, when the magnetic field is reduced below the release point B_{RPS} (B_{RPN}) as shown in Figure 3.




Figure 3. Switching characteristics

3. Pin Configuration




Figure 4. Pin configuration (SOT23-3)

Pin Number	Name	Function
1	V _{cc}	Power supply
2	V _{OUT}	Output
3	GND	Ground





4. Absolute Maximum Ratings

Parameters	Symbol	Min.	Max.	Unit
Supply voltage	V _{cc}	-0.3	7	V
Output current	I _{SINK} [1]	-	20	mA
Magnetic flux density	В	-	4000	Gs
ESD performance (HBM)	V _{ESD}	-	4	kV
Operating ambient temperature	T _A	-40	125	°C
Storage ambient temperature	T _{STG}	-50	150	°C

[1] I_{SINK} is the current flowing through V_{OUT} pin to GND pin.

5. Electrical Specifications

V_{CC} = 3 V, T_{A} = 25 °C, a 0.1 μF capacitor is connected between V_{CC} and GND

Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Supply voltage	V _{cc}	operating	1.8	3.0	5.5	V
Output stress voltage	V _{stress}	-	-	-	5.5	V
Output leak current	I _{leak}	OUT = H	-	-	1	μA
Off resistance of output	R _{OFF}	OUT = H	-	30	-	MΩ
On resistance of output	R _{on}	OUT = L	-	0.75	1	Ω
Output high voltage	V _{OH}	RP	[2]	-	V _{cc}	V
Output low voltage	V _{OL}	OP	0	-	0.2	V
Supply current	I _{cc}	OP/RP	0.5	1.5	2	μA
Response frequency	F	-		0 to 1000		Hz

[2] The min value of V_{OH} depends on the pull-up resistor and the leakage current following through the resistor.

6. Magnetic Specifications

 V_{CC} = 3 V, T_{A} = 25 °C, a 0.1 μF capacitor is connected between V_{CC} and GND

TMR1348S

Parameter	Symbol	Min.	Тур.	Max.	Unit
Operate point	B _{OPS}	10	14	25	Gs
	B _{OPN}	-25	-14	-10	Gs
Release point	B _{RPS}	5	10	20	Gs
	B _{RPN}	-20	-10	-5	Gs
Hysteresis	B _H	2	4	8	Gs





7. Typical Supply Voltage Characteristics




Figure 5. Supply current versus supply voltage (T_A =25°C)




Figure 6. Switch points versus supply voltage ($T_A=25^{\circ}C$)

8. Typical Temperature Characteristics






Figure 7. Supply current versus temperature (V_{CC} = 3 V)









9. Application Information

It is recommended to add a filter capacitor between the sensor power supply and ground (close to the sensor) to reduce external noise. As shown in Figure 9, the typical value is $0.1 \ \mu$ F.




Figure 9. Application circuit diagram

The TMR1348 series sensor chips are not suitable for driving power loads. The general method of use is utilizing the output voltage of V_{OUT} pin as a signal to input the MCU or drive a triode or MOS as shown in Figure 10.




Figure 10. Application diagram for driving power load

Common failure conditions:


- The supply voltage exceeds the limit of absolute maximum ratings
- Absence of matching filter capacitor to power supply when the power supply is unstable, which can cause the product to restart repeatedly
- Using switch output V_{OUT} to control high-power relays, etc., and cause I_{SINK} and I_{SOURCE} exceeding the limit of absolute maximum ratings
- The external magnetic field exceeds the limit of absolute maximum ratings
- Operating in a humid environment for a long time, causing vapor penetration and increased power consumption
- Overheating when soldering
- Over bending of pins





10. Dimensions

SOT23-3 Package









Copyright © 2022 by MultiDimension Technology Co., Ltd.

Information furnished herein by MultiDimension Technology Co., Ltd. (hereinafter MDT) is believed to be accurate and reliable. However, MDT disclaims any and all warranties and liabilities of any kind, with respect to any examples, hints or any performance or use of technical data as described herein and/or any information regarding the application of the product, including without limitation warranties of non-infringement of intellectual property rights of any third party. This document neither conveys nor implies any license under patent or other industrial or intellectual property rights. Customer or any third-party must further determine the suitability of the MDT products for its applications to avoid the applications default of customer or third-party. MDT accept no liability in this respect.

MDT does not assume any liabilities of any indirect, incidental, punitive, special or consequential damages (including without limitation of lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, MDT's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the terms and conditions of commercial sale of MDT.

Absolute maximum ratings are the extreme limits the device will withstand without damage to the MDT product. However, the electrical and mechanical characteristics are not guaranteed as the maximum limits (above recommended operating conditions) are approached. MDT disclaims any and all warranties and liabilities of the MDT product will operate at absolute maximum ratings.

Specifications may change without notice.

Please download latest document from our official website www.dowaytech.com/en.

Recycling

The product(s) in this document need to be handed over to a qualified solid waste management services company for recycling in accordance with relevant regulations on waste classification after the end of the product(s) life.



No.2 Guangdong Road, Zhangjiagang Free Trade Zone, Jiangsu, China Web: www.dowaytech.com/en E-mail: info@dowaytech.com

