No. SPQ-19L28

Nov . 20 , 2019

TO : DIGI-KEY ELECTRONICS

.

## <u>SPECIFICATION</u>

Product name : DIA THERMISTOR NEGATIVE

Part number : DTN-V103J3T-DGS103V

PW-AP-3611E : Specification

Should you have any changes regarding this specifications, please make a contact to our sales department within 14 days after receiving this document.

MITSUBISHI MATERIALS CORPORATION CERAMICS PLANT QUALITY ASSURANCE DEPARTMENT / MANAGER

> Matsumoto J. MATSUMOTO

> > 2270 YOKOZE CHICHIBU SAITAMA PREF. 368-8502. JAPAN

Thermistor Sensor Specification			Drawing No.	PW-AP-36	11E (1st	Edition	) Pa	age	1⁄4
Туре	DTI	N-V103J3T-DGS103V	Date		November 20, 2019				
1. Usa Thi RoH 2. The	<ol> <li>Usage range</li> <li>This specification is applied to thermistor sensor ( DTN-V103J3T-DGS103V ) . RoHS directive pass.</li> <li>Thermistor characteristics</li> </ol>								
	Item	Particu	lar		Sign	Char.	Unit	t	Tol.
2-1 Resist	ance	Resistance at 25°C.			R 2 5	10	kΩ		±5%
2-2	B-value between t1°C and t2 °C		t2 °C	c		3820	К		±3%
B-vaiu	e	$Bt_{1}/t_{2}=In \frac{Rt_{1}}{Rt_{2}} / \left( \frac{1}{t_{1}+273.15} - \frac{1}{t_{2}+273.15} \right)$			$(B_{25/85} = 3792K)$				
2-3 Therma consta (ambie	l time nt nt temp. change)	Where the sensor is screwed up on aluminum block(120L*20W*20T), the block except sensor attached surface is put into 25°C water. From this state when the block is moved into 50°C water, the time required for the temperature of the sensor to change by 63.2% of the difference of temperature.			τ	27	sec.		or less
2-4 Operat temper range	ing ature				Tw	-40~ +150	°C		
2-5 Dissip consta	ation nt	The electric power to increase 1 degree in temperature of sensor at 25°C in still air.			δ	3 approx.	mW/°C	;	
2-6 Maximu permis power	m sible	The power taking temperature of sensor to upper limit of operating temperature range by self-heating at 25°C in still air.			Pmax.	375	mW		
2-7 Withst voltag	anding e	A.C.500V 1 minute or A.C (In water between	.600V 1 seco case and le	nd. ad wire)	No abnormal found				
2-8 Insula resist	tion ance	D.C.500V megger. (In water between case and lead wire)		I. R.	100	MΩ		or more	

Thermistor Sensor Specification	Drawing No.	PW-AP-3611E (1st Edition)	Page	2 ⁄ 4

## 3. Reliability characteristics

Testing item	Testi	Changing ratio after test		
3-1 Heat resistance test	150℃ in air	placed for 1000 hours	$\Delta R_{25} \leq \pm 5\%$ $\Delta B_{25/50} \leq \pm 3\%$	
3-2 Cold resistance test	-40°C in air	placed for 1000 hours	$\Delta R_{25} \leq \pm 5\%$ $\Delta B_{25/50} \leq \pm 3\%$	
3-3 High temperature humidity test	40℃, 95%R. H.	placed for 1000 hours	$\Delta R_{25} \leq \pm 5\%$ $\Delta B_{25/50} \leq \pm 3\%$	
3-4 Heat cycle test	-40℃, 3 minutes ⇔ [in air] 600 cycles	125℃, 3 minutes [in air]	$\Delta R_{25} \leq \pm 5\%$ $\Delta B_{25/50} \leq \pm 3\%$	

## 4. Mechanical characteristics

Testing item	Testing requirement	Characteristics after test
4-1 Pull test	From lead wire axis direction, hang a static load of 29.4N(3.0kg·f) and stay for 1 minute between case part and lead wire.	There is no abnormality in appearance and electrical characteristics.
4-2 Vibration test	Frequency:20~200Hz, Cycle:15 minutes. Acceleration:4.4G Vibrate up/down 4 hours,back/forth and right/left each 2 hours.	There is no abnormality in appearance and electrical characteristics.
4-3 Drop test	Drop on wood from height 1m 5 times.	There is no abnormality in appearance and electrical characteristics.

5. Shape - Dimension         9         9         9         9         9         9         9         15. 7         1000±20         (mmm)         0         0         0         (mmm)         0         (mmm)         (mmm)         0         (mmm)         0         (mmm)         0         (mmm)         0         (mmm)         0         (mmm)         (mmm)         (mmmm)         (mmmm)         (mmmm)         (mmmmm)         (mmmmm)         (mmmmmm)         (mmmmmmm)         (mmmmmm)         (mmmmmm)         (mmmmmmm)         (mmmmmmm)         (mmmmmm)         (mmmmm)		Thermistor S	ensor Specification	Drawing No.	PW-AP-3611E (1s	t Edition)	Page	3 ⁄ 4
Image: Second	5.S	Shape – Dimensi	on					
(mm) Some lot indication is shown on lead wire. Lot indication		7.2	7 6 6.2 15.7	1000±20		(30)	5±1	
Some lot indication is shown on lead wire.         D2 3 (made in Japan condition)       0.2 3 (made in Malaysia condition)         0.2 3 (made in Vietnam condition)       0.2 3 (made in Vietnam condition)         0.2 4 (made in Vietnam condition)       0.2 3 (made in Vietnam condition)         0.2 5 (made in Vietnam condition)       0.2 5 (made in Vietnam condition)         0.2 6 (made in Vietnam condition)       0.2 6 (made in Japan content indication         1 ~ 9 Month characters,       0.2 7 (made in Japan or Vietnam condition)         0.2 8 (made in Japan or Vietnam condition)       MacAvZ (MacAvZZ (made in Malaysia condition))         Marx DZ, AA~AZZ (made in Malaysia condition)       MacAvZ (MacAvZZ (made in Malaysia condition))         Marx MZ, AA~AZ, BA~BZ (made in Malaysia condition)       Yes         6 Adhesive       Heatproof low expansion Epoxy resin       Yes         5 Coating       Heatproof low expansion Epoxy resin       Yes         4 Coating       Heatproof low expansion Epoxy resin       Yes         3 Lead wire       Cross linked polyethylene parallel wire       150°C Heatproof       Yes         2 Solder       Lead free       Yes       Yes       Yes       Yes         1 Thermistor       Chip thermistor       Yes       Yes       No.       Parts       Specifications       RoHS compliant </td <td></td> <td></td> <td></td> <td>£)5)</td> <td>3</td> <td></td> <td></td> <td>( m m )</td>				£)5)	3			( m m )
7CaseRing tongue terminal 5.5-S3 (JST)Yes6AdhesiveHeatproof low expansion Epoxy resinYes5CoatingHeatproof low expansion Epoxy resinYes4CoatingHeatproof low expansion Epoxy resinYes3Lead wireCross linked polyethylene parallel wire 150°C Heatproof φ1.08 0.14mm² (7/0.16) [Black] Tin plated soft copper wireYes2SolderLead freeYes1ThermistorChip thermistorYesNo.PartsSpecificationsRoHS compliant	S	Some lot indicatio 1 2 3 (made 3 2 1 (made V 1 2 3 (made V 1 2 3 (made 1 : End of No 2 : Month ind 1~9 Mont 10-X, 11-Y 3 : Lot seria A~Z or A MA~MZ, AA	cation is shown on lead wi in Japan condition) in Malaysia condition) le in Vietnam condition) . for year of christian era. C lication .h characters, /1 No. on that month indication .A ~ZZ (made in Japan or Viet ~AZ,BA ~BZ (made in Malays)	re. )~9 n tnam condition ia condition)	1),			
7CaseRing tongue terminal5.5-S3(JST)Yes6AdhesiveHeatproof low expansion Epoxy resinYes5CoatingHeatproof low expansion Epoxy resinYes4CoatingHeatproof low expansion Epoxy resinYes3Lead wireCross linked polyethylene parallel wire150°C Heatproof φ 1.08Yes2SolderLead freeYes1ThermistorChip thermistorYesNo.PartsSpecificationsRoHS compliant	<b></b>							
6AdnesiveHeatproof low expansion Epoxy resinYes5CoatingHeatproof low expansion Epoxy resinYes4CoatingHeatproof low expansion Epoxy resinYes3Lead wireCross linked polyethylene parallel wire150°C Heatproof φ 1.08Yes2SolderLead freeYes1ThermistorChip thermistorYesNo.PartsSpecificationsRoHS compliant	7	Case	King tongue terminal 5.	5-S3 (JST)			Yes	
5CoatingHeatproot low expansion Epoxy resinYes4CoatingHeatproof low expansion Epoxy resinYes3Lead wireCross linked polyethylene parallel wire150°C Heatproof (\$\$\phi\$1.08_0.14mm^2_(\$\$7/0.16)_[Black] Tin plated soft copper wire]Yes2SolderLead freeYes1ThermistorChip thermistorYesNo.PartsSpecificationsRoHS compliant	6	Adhesive	Heatproof low expansion Epoxy resin				Yes	
4CoatingHeatproot low expansion Epoxy resinYes3Lead wireCross linked polyethylene parallel wire $150^{\circ}$ C HeatproofYes3Lead wireCross linked polyethylene parallel wire $150^{\circ}$ C HeatproofYes2SolderLead freeYes1ThermistorChip thermistorYesNo.PartsSpecificationsRoHS compliant	5	Coating	Ing Heatproof low expansion Epoxy resin				Yes	
3Lead WireGross linked polyethylene parallel wire150°C HeatproofYes $\phi$ 1. 080. 14mm² (7/0. 16) [Black] Tin plated soft copper wireYes2SolderLead freeYes1ThermistorChip thermistorYesNo.PartsSpecificationsRoHS compliant	4	Coating	Goating     Heatproof low expansion Epoxy resin				Yes	
2SolderLead freeYes1ThermistorChip thermistorYesNo.PartsSpecificationsRoHS compliant	3	Lead wire Cross linked polyethylene parallel wire 150°C Heatproof $\phi$ 1.08 0.14mm <sup>2</sup> (7/0.16) [Black] Tin plated soft copper wire			proot ber wire	Yes		
1ThermistorYesNo.PartsSpecificationsRoHS compliant	2	Solder	Lead free				Yes	
No. Parts Specifications RoHS compliant	1	Thermistor	Chip thermistor				Yes	
	No.	Parts	Sr	pecifications	3	Ro	HS comp	liant

6. Caution in Thermistor Sensor usage

Due to the possibilities of destruction of the sensor, damage or miss use of equipment, please strictly follow below matter.

- ①The sensor is designed for individual usage. When it is going to be used beyond the specified condition, please speak to your daily contact person for our products.
- (2)Whenever designing the equipment, make sure to check sensor operation and if there is no lack of quality.
- ③Do not use the sensor exceeding rated electric power.
- (4) Due to possibility of causing the decrease of the value of resistance with self heat and malfunction of the equipment or the precision decrease of the inspection temperature, carefully refer to the dissipation constant usage of electric power and voltage.
- ⑤Do not use the sensor beyond operating temperature range.
- © Avoid from exceeding radical temperature change, which is beyond operating temperature range.
- ⑦In case of independently use of the sensor as a main control of the device, make sure to design and devise through safety measures for [safe circuit] and [parallel use with same function sensor] etc, to prevent from accident.
- (B)Under the environment which receives the influence of electric noise, make sure to take countermeasure by installing a protection circuit and seal the sensor. (including the lead wire)
- (9) When the case type sensor is used under high humidity environment, make sure to design so that the protected case tip must be exposed to environment (in water, moisture) condition, and to the [utmost] open part of the case must be prevented from not touching water and steam directly.
   Please note how such as making the opening downward to install it so as not to stay in this part when you generate the be dewy water.
- Do not add excessive vibrating shocking pressure.
- ①Avoid from excessive pulling and bending of the lead wire.
- Do not impress excessive voltage in the insulated part and between the electrode. This might cause to occur the insulated malfunction.
- (3) Consider wiring, due to contact failure might occur if the terminal of the lead wire (including the connector) is immersed into [water] [steam] [electrolyte] etc.
- Do not use in corrosiveness gas atmosphere (Cl<sub>2</sub>, NH<sub>3</sub>, SO<sub>x</sub>, NO<sub>x</sub>) beyond the designated condition.
   Do not use at the place where the sensor touches the electrolytic, brine, acid, alkaline and organic solvent beyond the designated condition.
- (5)Due to possibility of the equipment becoming malfunction depending upon metal corrosion, consider not to cause potential difference with the contact metal for the case and screw equipped type sensor.

If there is any others unclear point, please inquire to our company sales in-charge.