

SPECIFICATION SHEET

SPECIFICATION SHEET NO.	Q0301- XB11M05920S410
DATE	March 01, 2023
REVISION	AO
DESCRIPITION	MHz SMD Crystal, Seam Seal, L7.0*W5.0*H1.1mm, 4 Pads, CM75 series 11.0592MHz, Tolerance +/-30ppm, Load Capacitor 10pF, Frequency stability +/-30ppm @Operating Temp. Range -40°C ~+85°C, ESR 60 ohm Max, Reflow Profile Condition 260 °C Max. Tape/Reel, 1000pcs/Reel RoHS/RoHS III compliant
CUSTOMER	
CUSTOMER PART NUMBER	
CROSS REF. PART NUMBER	
ORIGINAL PART NUMBER	TGS CM75 11M0592A30-10-30-40-60TLF
PART CODE	XB11M05920S410

VENDOR APPROVE

Issued/Checked/Approved








DATE: March 01, 2023

CUSTOMER APPROVE			

DATE:

03/01/2023



SMD CRYSTAL 7050 TYPE 4 PADS

MAIN FEATURE





- SMD Crystal, Seam Seal, L7.0*W5.0*H1.1mm, 4 pads
- Low cost, High precision, High frequency stability
- Reflow Profile Condition 260 °C Max.
- Cross more competitors part
- RoHS/RoHS III compliant

APPLICATION

- Bluetooth, wireless communication set
- Communication Electronics

PART CODE GUIDE



ХВ	11M05920	S	410
1	2	3	4

- 1) XB: Part family Code for SMD Crystal, Seam Seal, L7.0*W5.0*H1.1mm, 4 pads (CM75)
- 2) 11M05920: Frequency range code for 11.0592MHz
- 3) S: SMD type, Package Tape/Reel, 1000pcs/Reel
- 4) 410: Specification code for original part No.: TGS CM75 11M0592A30-10-30-40-60TLF

03/01/2023


SMD CRYSTAL 7050 TYPE 4 PADS

DIMENSION (Unit: mm)

Image for reference




CM75



Marking

standard


4.6 2.54




Connection


#1 Crystal #2 Ground #3 Crystal


#4 Ground





Recommend Pad Layout





SMD CRYSTAL 7050 TYPE 4 PADS


ELECTRICAL PARAMETERS

Parameter		Part No. Symbol	Units	Value			Condition
		37111501		Min.	Typical	Max.	
Original	Manufacturer	TGS		TGS	Crystals		
Holder T	уре	CM75	SMD Crysta	l, Seam Seal,	L7.0*W5.0*H1.1	mm, 4 pads	
Frequen	cy Range	11M0592	MHz		11.0592		
Mode of	Oscillation	А			AT Fundamenta	al	
Frequen	cy Tolerance	30	ppm	-30		+30	@25°C
Load Cap	oacitance	-10	pF		10		
Stability Operation	over on Temperance	-30	ppm	-30		+30	
Operation	on Temperance	-40	°C	-40		+85	
Storage '	Temperance		°C	-55		+125	
Equivale Resistan	nt Series ce (ESR)	-60	Ω			60	
Drive Lev	vel		μW	300		300	
Shunt Ca	apacitance (CO)		pF	0 7.0			
Motiona (C1)	Il Capacitance		fF	N/A			
DLD2			Ω	N/A			
FLD2			ppm	N/A			
RDL2			Ω	N/A			
SPDB			dB	N/A			
Aging			ppm/year			±3	@1 st year
Insulatio	on Resistance		ΜΩ	500			@100VDC ± 15VDC
	Package	Т		Тар	pe/Reel		
	RoHS Status	LF		RoHS III compliant N/A			
Others	Add Value						
	Internal Control Code *			N/A			

Note: 1) Original Part Number: TGS CM75 11M0592A30-10-30-40-60TLF

2) *Internal Control Code- 2 letter or digits; Blank: N/A


03/01/2023



SMD CRYSTAL 7050 TYPE 4 PADS


MECHANICAL PERFORMANCE

Item	Condition	Standard
Drop characteristics	Free drop from 75cm height on a hard wooden board for 3 times. (Board is thickness more than 30 mm.)	Frequency change: ≤5ppm Rr as specification
Shake characteristics	Shake frequency 10~55Hz, cyc1~2 minutes, swing 1.5mm, direction x/y/z, all 30 minutes, test after 1 hours.	Frequency change: ≤5ppm Rr as specification
Airproof characteristics	Put crystal into the pressure cabin with alcohol, keep pressure 0.4~0.5mpa 10 minutes, then take out and blow for 5 minutes	IR≥500MΩ
Weld characteristics	260±5°C, 3 seconds	90% exhibit tin ok
Humidity characteristics	+40±2°C & 90%~95% R.H. 250 hours	Frequency change: ≤5ppm Rr as specification
Low temperature characteristics	-30 \pm 2°C, 250 hours, put in room temperature, test after 1 hours.	Frequency change: ≤5ppm Rr as specification
High temperature characteristics	+85 \pm 2°C, 250 hours, put in room temperature, test after 1 hours.	Frequency change: ≤5ppm Rr as specification
Temperature cycling	-30 \pm 3°C/30 \pm 3 min~+85 \pm 2°C/30 \pm 3min, 5 cycles	Frequency change: ≤5ppm Rr as specification



SMD CRYSTAL 7050 TYPE 4 PADS

SUGGESTED REFLOW PROFILE (For Reference Only)





03/01/2023 6

SMD CRYSTAL 7050 TYPE 4 PADS

TAPE/REEL (Unit: mm)

All Devices are packed in accordance with EIA standard RS-481-2 and specifications., 1000pcs/Reel





5.4 ^{±01}
7.4 ^{±0.1}
16.0 ^{±0.2}
7.5 ^{±0.1}
1.75 ^{±0.1}
8.0 ^{±0.1}
2.0 ^{±0.1}
4.0 ^{±0.1}
1.55 ^{±0.05}
1.4 ^{±0.1}
1.6+0.1/0
0.3 ^{±0.05}

Item		Empty Space	
Tapa Leader	Cover Tape	Min.500mm	
	Empty Pockets	Min.20 pockets	
Tape Trailer	Cover Tape	Min.0mm	
	Empty Pockets	Min.40mm	

DISCLAIMER

NextGen Components, Inc. reserves the right to make changes to the product(s) and or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information

03/01/2023

7