

8303 and 8503 Handheld Airborne Particle Counters

0.1 CFM (2.83 LPM)

- Industry's highest concentration of 15,000,000 particles/ft³ @ 10% coincidence loss
- · Ideal for use in research, industrial health and safety, indoor air quality, and cleanroom applications
- Up to 10 hours continuous operation on a fully charged battery
- Industry's first Sleep Mode and Power Conservation Mode with Intelligent Battery
- The most comprehensive internal self-diagnostics of any handheld particle counter
- Real-Time Meter detects particle contamination sources with visual and audible indication
- Internet of Things (IoT) communication allows for network or cloud-based data options



The Particles Plus® 8303 and 8503 Handheld Particle Counters measure 0.3 to 25.0 μm with a flow rate of 0.1 CFM (2.83 LPM).

Easy to configure, this instrument displays up to 3 user-selectable size channels as well as (optional) temperature and relative humidity. View data and generate ISO 14644-1, EU GMP Annex 1 or FS 209E reports. Export to Particles Plus® data-software. The 8303 also has a mass concentration mode that approximates density in μ g/m³.

All Particles Plus® counters meet ISO 21501-4 and JIS B9921. The 8303 and 8503 ensure compliance with an on-board pulse height analyzer.


Features and Benefits

- 8303 Measures 0.3 μm to 25.0 μm
- 8305 Measures 0.5 μm to 25.0 μm
- 0.1 CFM (2.83 LPM) flow rate
- Long life laser diode technology
- Measures up to 3 channels of simultaneous data
- Approximates mass concentration in µg/m³ with density and refractive index corrections
- Integrated handle for one-handed operation
- · Large easy-to-use icon driven color touch screen display
- Temperature and relative humidity probe included
- Stores up to 45,000 sample records, 1,000 sample locations and 50 recipes
- Annotation function allows user to save 32 character notations to a sample record
- Remote diagnostics allows for remote service investigation through the Internet
- · Easy configuration and transferable from instrument to instrument
- Connect using Ethernet, USB or (optional) Wireless 802.11 b/g, RS 485 or RS232
- Displays user-definable reports for ISO 14644-1, EU GMP Annex 1 and FS 209E
- · Internal audible alarm with comprehensive alarm management
- User-selectable channel sizes
- Complies with ISO 21501-4 and JIS B9921 standards
- · Easy to clean and wipe down with minimal particle traps
- · Seamless integration into a facility monitoring system
- · Lightweight high-impact injection molded plastic enclosure
- 2 year limited warranty. Extended warranties available.

Specifications

opecifications		
Model	8303	8503
Size Range	0.3 to 25 µm	0.5 to 25 μm
Size Channels	Factory calibrated at 0.3, 0.5, 5.0 µm	Factory calibrated at 0.5, 1.0, 5.0 µm
Flow rates	0.1 CFM (2.83 LPM)	
Concentration Limits	15,000,000 particles/ft³ @ 10% coincidence (per ISO 21501-4), 30,000,000 particles/ft³ @ 10% coincidence (as tested and validated¹)	
Battery Run Time	>10 hours continuous operation	
Light Source	Long life laser diode	
Counting Efficiency	50% @ 0.3 μm; 100% for particles >0.45 μm per JIS	
Zero Count	<1 count / 60 minutes (<1 particles / 6 ft³)	
Count Modes	Real-Time Meter and graph, cumulative/differential count/m ³ and count/ft ³ , and mass concentration (PM)	
Count Alarms	1 to 9,999,999 counts	
Calibration	NIST traceable	
Display	4.3" (10.9 cm) WQVGA (480×272) color touch screen	
Printer	(Optional) External thermal printer available	
Vacuum Source	Internal pump with automatic flow control	
Filtered Exhaust	Internal HEPA filter	
Number of Channels	3	
Custom Size Channels	Calibration for custom size channels available	
Audible Alarm	Adjustable built-in alarm	
Battery	Removable Li-ion (Recharge time: 4 hours within instrument, <2 hours with external battery charger)	
Reports	ISO 14644-1, EU GMP Annex 1, FS 209E	
Recipes	50 user-configurable recipes	
Communication Modes	Ethernet and USB. (Optional) Wireless 802.11 b/g, RS485 or RS232	
Environmental Sensor	Includes temperature 32° to 122°F (0° to 50°C) \pm 1°F (0.5°C) and relative humidity probe 15-90% \pm 2%	
Alarm	Alarms on counts for all particle sizes, sensor failure, environmental sensors and flow	
Standards	ISO 21501-4 and JIS B9921	
Calibration	Recommended minimum once per year	
External Surface	High impact injection molded plastic	
	5.12" x 4.25" x 12.26" (13.0 cm x 10.8 cm x 31.1 cm) includes handle and does not include probes	
Dimensions (L x W x H) Weight	2.2 lb (1.0 kg)	
Accessories	Operating manual and IMS software on USB flash drive, isokinetic probe, temperature relative humidity sensor, purge	
	filter, battery, data download software, USB cable, power supply and cable	
Optional Accessories	Printed manual, carrying case, spare battery, external battery charger, external printer and isokinetic probes, barbed fittings, IMS-RT monitoring system	
Buffer Memory	45,000 sample records (rotating buffer) including particle count data, environmental data, locations, annotations, and times. Scrollable on screen or printout.times. Scrollable on screen or printout	
Sample Locations	Up to 1,000 locations 20 characters long	
Sample Time	1 second to 99 hours	
Power	110 to 240 VAC 50/60 Hz universal in-line power supply	
Operating Conditions	41° to 104°F (5° to 40°C) / 20% to 95% non-condensing	
Storage Conditions	32° to 122°F (0° to 50°C) / Up to 98% non-condensing	
Warranty	2 Years. Extended warranties available.	

1- Validated by independent analysis see paper available at www.particlesplus.com/aac2022 paper



PAT. https://particlepatents.com/ Additional Patents Pending. Particles Plus, Inc. reserves the right to change specifications without notice. Contact hello@particlesplus.com or your local distributor for more details. Particles Plus and the Particles Plus logo are trademarks of Particles Plus, Inc. @2022 Particles Plus, Inc. All rights reserved.



31 Tosca Drive Stoughton, MA 02072 U.S.A. +1-781-341-6898 www.particlesplus.com