

PRODUCT SPECIFICATION

DOCUMENT NO. ENS000126560				
DESCRIPTION	DRAWN BY	DESIGNED BY	CHECKED BY	APPROVED BY
WIP322512A-1R0ML	Rueiying	Phil	JiaJing	Wiley







RoHS | (N) WIP322512A-1R0ML Series Engineering Specification

1. Scope


Feature

- High saturation current realized by material properties and structure design
- Low DC resistance to achieve high conversion efficiency and lower temperature rising
- Low Profile: $3.2 \text{ mm} \times 2.5 \text{ mm} \times 1.2 \text{ mm}$.
- Magnetically shielded structure to accomplish high resolution in EMC protection.
- Halogen free, Lead Free, RoHS Compliance.

Applications

- WIP322512A-1R0ML is generic applied in portable DC to DC converter line.
- Smart phone, PAD
- DC/DC converter
- Thin-type power supply module

2. Explanation of Part Number



- 1 : Series Name: Wire-wound type power inductor
- 2 : Size Code: The first two digitals: length(mm), The last two digitals: width(mm)
- 3: Thickness in mm
- 4 : Material code: Iron powder
- 5: Initial inductance value: 1R0 = 1.0 μH
- 6: Model code, Tolerance of Inductance ±20%.
- ♦ 7 : Electrode type.
- 8 : Control code.

TITLE: WIP322512A-1R0ML Engineering **Specification**

DOCUMENT NO. ENS000126560


SPEC REV.: P11 Page 1 of 9



3. Construction & Dimensions


3.1. End termination: Ni/Sn

3.2. Construction & Dimension



L	W	T	E
[mm]	[mm]	[mm]	[mm]
3.2±0.2	2.5±0.2	1.2 max.	0.6±0.2

3.3. Recommend Land Pattern Dimensions



A	В	С
[mm]	[mm]	[mm]
2.5 typ.	1.7 typ.	3.2 typ.

4. General specifications

4.1. Temperature Specifications

Operating Temperature range : -40° C to $+125^{\circ}$ C Storage Temperature range : -50° C to $+125^{\circ}$ C



5. Performance Characteristics

5.1. Specifications

INPAQ Part Number	Li [µH] Initial inductance	RDC [mΩ] DC Resistance		Isat [A] Saturation Current		Irms [A] Heat Rating Current	
			Maximum	Typical	Maximum	Typical	Maximum
WIP322512A-1R0MLDG	1	25	32	5.5	5.0	4.9	4.4

Note 1: Customized design is available, please contact us.

Note 2: All test referenced to 26°C ambient

Note 3: Inductance tolerance +/- 20%

Note 4: Inductance is measured with Agilent® LCR meter 4285A (or equivalent) at 1MHz/1V.


Note 5: DC resistance is measured with HIOKI® micro-ohm meter RM3542 or equivalent.

Note 6: Isat means that DC current will cause a 30% inductance reduction from initial value.

Note 7: Irms means that DC current will cause part temp. rising 40°C whichever is smaller.



5.2 Current Characteristic





6. Reliability and Test Condition

В

Test item	Test condition	Criteria
Resistance to Solder Heat	 Solder temperature : 260 ± 5°C Flux : Rosin DIP time : 10 ± 1 sec 	 More than 95 % of terminal electrode should be covered with new solder No mechanical damage Inductance value should be within ± 20 % of the initial value
Adhesive Test	 Reflow temperature : 245℃ It shall be Soldered on the substrate applying direction parallel to the substrate Apply force(F) : 5 N Test time : 10 sec 	No mechanical damage Soldering the products on PCB after the pulling test force > 5 N
Thermal shock	 Temperature:-50 ~ 125°C For 30 minutes each Cycle: 500 cycles Measurement: At ambient temperature 24 hours after test completion 	No mechanical damage Inductance should be within ±20% of the initial value
Dry Heat Test	 Temperature: 85 ± 2°C Testing time: 500 hrs Applied current: Full rated current Measurement: At ambient temperature 24 hours after test completion 	No mechanical damage Inductance should be within ± 20% of the initial value
Humidity Test	 Temperature: 60 ± 2°C Humidity: 90-95 % RH Applied current: Full rated current Testing time: 500 hrs Measurement: At ambient temperature 24 hours after test completion 	No mechanical damage Inductance should be within ±20% of the initial value


TITLE: WIP322512A-1R0ML Engineering DOCUMENT NO. Specification ENS000126560 SPEC REV.: P11 Page 5 of 9

<u>www.inpaq.com.tw</u> ; <u>www.inpaqgp.com</u> I-FM-04-40




7. Tape and reel specifications

7.1. Carrier tape dimensions



	A0	В0	K0	t
mm	2.80 ± 0.1	3.45 ± 0.1	1.34 ± 0.1	0.23 ± 0.05

7.2 Taping reel dimensions



PART SIZE (EIA SIZE)	3225 (1210)
Qty.(pcs)	3,000
BOX	5 reels / inner box

TITLE: WIP322512A-1R0ML Engineering DOCUMENT NO. Specification SPEC REV.: P11 Page 6 of 9

<u>www.inpaq.com.tw</u>; <u>www.inpaqgp.com</u>

B I-FM-04-40



7.3 Taping specifications

There shall be the portion having no product in both the head and the end of taping, and there shall be the cover tape in the head of taping.

7.4 Label Marking

The label specified as follows shall be put on the side of reel.

- (1) Part No.
- (2) Quantity
- (3) Lot No.
 - * Part No. And Quantity shall be marked on outer packaging.

7.5 Quantity of products in the taping package

- (1) Standard quantity: 3000pcs/Reel
- (2) Shipping quantity is a multiple of standard quantity.

8. Precautions for Handling

8.1. Precaution for handling of substrate

Do not exceed to bend the board after soldering this product extremely. (reference examples)

- Mounting place must be as far as possible from the position, which is close to the break line of board, or on the line of large holes of board.
- Do not bend extremely the board, in mounting another components.

 If necessary, use back-up pin (support pin) to prevent from bending extremely.
- Do not break the board by hand. We recommend to use the machine or the jig to break it.

8.2. Precaution for soldering

Note that this product will be easily damaged by rapid heating, rapid cooling or local heating.

Do not give heat shock over 100°C in the process of soldering. We recommend to take preheating and gradual cooling.


TITLE: WIP322512A-1R0ML Engineering Specification

DOCUMENT NO. ENS000126560

SPEC REV.: P11 Page 7 of 9



8.3. Recommendable reflow soldering



Reference IPC-020c-5-1

Profile Feature	Pb free Assembly	
Average Ramp Rate	3 °C/second max	
(Ts max to Tp)		
Preheat		
- Temperature Min (Ts _{min})	150℃	
- Temperature Min (Ts _{max})	200℃	
- Time(ts _{min} to ts _{min})	60-180 seconds	
Time maintained above:		
- Temperature (TL)	217 ℃	
- Time (tL)	60-150 seconds	
Peak Temperature (T _p)	260°C +0/-5 °C	
Time within 5 °C of actual Peak	20-40 seconds	
Temperature (T _p)		
Ramp-Down Rate	6 °C/second max.	
Time 25 [°] C to Peak Temperature	8 minutes max	

TITLE: WIP322512A-1R0ML Engineering Specification

DOCUMENT NO. ENS000126560

SPEC REV.: P11 Page 8 of 9



8.4. Soldering gun procedure

Note the follows, in case of using solder gun for replacement.

- (1) The tip temperature must be less than 280°C for the period within 3 seconds by using soldering gun under 30 W.
- (2) The soldering gun tip shall not touch this product directly.

8.5. Soldering volume

Note that excess of soldering volume will easily get crack the body of this product.

8.6. Taping Package Storage Condition

Storage Temperature : 5 to 40 $\,^{\circ}\mathrm{C}$

Relative Humidity: < 65%RH Storage Time : 12 months max

TITLE: WIP322512A-1R0ML Engineering Specification

DOCUMENT NO. ENS000126560

SPEC REV.: P11 Page 9 of 9