



496Y

**Universal Phase Monitor** 

- Monitors up to 700 VAC
- DIN Rail or Surface Mount
- Operating Range 200-630 VAC
- Manual or Automatic Reset
- Adjustable Restart Delay
- · Adjustable Fault Delay

#### PROTECTS AGAINST:

- Rapid Cycling
- · Phase Loss
- · Phase Reversal
- · Phase Unbalance
- · Phase Shift
- · Over/Under Voltage
- Over/Under Frequency

### ORDERING INFORMATION


MODEL NUMBER	DESCRIPTION		
SLU-600-ASTDS	Universal Phase Monitor/Relay		

The ATC-Diversified Electronics **SLU-600-ASTDS** Universal Phase Monitor protects 3-phase motors up to 700VAC. The **RAPID CYCLING** feature prevents motors cycling due to load-induced line fault conditions. Powered by 120VAC, this reliable motor protection relay is unaffected by transients and disturbances from the monitored power source. The SLU-600 Series is UL Listed under UL File Number E55826.


### **SPECIFICATIONS**

AUTO RANGING	Frequency	Nominal Line-to- Line Voltages	Adjustable Range		
SCALES	60Hz	208, 220, 240	200-250		
		380, 415, 440,	360-500		
		460, 480, 575, 600	550-630		
	50Hz	208, 220, 240	200-250		
		346, 380, 415	330-430		
<b>3Ø VOLTAGE</b>	Drop-out		etting (Under/Over)		
BAND	Pick-up ±7% of Range Setting (Under/Over)				
CONTROL VOLTAGE	120 VAC ±10%, 50/60Hz				
MAXIMUM VOLTAGE	700 VAC (Line-to-Line)				
PHASE SEQUENCE	ABC (Will Not Operate On CBA Sequence)				
POWER REQUIRED	90VA Max.				
PHASE	2% to 10%, Adjustable Drop-out				
UNBALANCE	Hysteresis 10% of Setting				
PHASE SHIFT	13° Drop-out, 12° Pick-up (Ø-Loss)				
FREQUENCY	50/60 Hz				
SHIFT	Drop-out	± 4%			
	Pick up	± 3%			
RAPID CYCLING	5 Cycle Lockout, 30-Min. Cycle Count Reset				
RESET	Automatic or Manual Mode Clears Rapid Cycle Count				
RELAY OUTPUT	DPDT, 10A @	240 VAC Resistive			
LED'S		Flashing	Continuous		
	Normal	Fault Delay	Relay		
	(Green LED)	Active	Energized		
	Fault (Red LEI	,	Relay		
	Over (Red LED	Active D) Restart Delay	De-energized Relay		
	Over (neu LLL	Active	De-energized		
	Unbal / Ø Loss		Relay		
	(Red LED)	Active	De-energized		
RESPONSE	Power Up	2.5 S Minimum			
	Fault Delay	0.1 to 25 S, Adjust	0.1 to 25 S, Adjustable 100mS (Ø-Loss, Unbalance or Ø Reversal)		
	Severe Fault	•			
	Restart	0.5 to 300 S, Adju	0.5 to 300 S, Adjustable (Auto Reset)		
TEMPERATURE	Operate		32° to 131°F (0° to +55°C)		
RATINGS	Storage	-49° to 185°F (-4	-49° to 185°F (-45° to +85°C)		
REPEAT ACCURACY	1% @ Fixed Condition				
TERMINALS	Plug and Socket Term Block with Spring Pressure Wire Retention, 12 AWG Max.				
ENCLOSURE	35mm DIN Rail or Surface Mount, Polycarbonate Housing				
WEIGHT	1.10 lbs.				

# **DIMENSIONS** (INCHES/MILLIMETERS)



## **TOP LABEL**



## **LED STATUS CHART**

● = OFF ○ = ON ∹ = FLASHING	Normal Green LED	Under Red LED	Over Red LED	Unbal & Ø Loss Red LED
Powering Up/First 3 Sec	•	•	•	<del>.</del> ☆-
Powered Up/Normal Voltages	0	•	•	•
Relay ON/Under Voltage Detected/FAULT DELAY active	-;Ċ-	•	•	•
Relay ON/Over Voltage Detected/ FAULT DELAY active	-;¢-	•	•	•
Relay ON/Unbal or Ø Loss Detected/FAULT DELAY active	-;Ċ-	•	•	•
Relay OFF/Under Voltage Failure	•	0	•	•
Relay OFF/Over Voltage Failure	•	•	0	•
Relay OFF/Unbal or Ø Loss Failure	•	•	•	0
Relay OFF/Under Voltage Corrected/RESTART DELAY active	•	- <del>`</del> .	•	•
Relay OFF/Over Voltage Corrected/RESTART DELAY active	•	•	<del>-</del> ;¢-	•
Relay OFF/Unbal or Ø Loss Corrected/RESTART DELAY active	•	•	•	<del>\</del>