soberton inc. **SP DYNAMIC SPEAKER UNIT**

Acoustic Product Specification

Product Number: SP-5728T



Release | Revision: B/2022

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1 Speaker Electroacoustic Characteristics

General Specifications

Page 2 **Reliability Tests**

Page 3 Measuring Method (Speaker Mode)

Sound Pressure Level

90±3dB (0.1W/0.1M) @AVE 1.0, 1.2, 1.5, 2.0KHz (0dB SPL=20µPa) Measuring conditions: 0.1W (sine wave) 0.1M measured with baffler shown in Fig 2

Frequency Response Curve

As shown in Fig 2

Resonance Frequency

220±20% Hz @1V (without baffler)

Input Power (Nominal and Maximum)

Rated Noise Power: 3.0W

Short Term Max Power: 5.0W

Frequency Range

F0 ~ 20KHz resonant frequency down -10dB

Audible Noise

Must be free audible noise 200 ~ 4KHz, Input level up to 4.0Vrms.

Measuring Diagram

Shown in Fig 1

DC Resistance:

 $7.4\Omega \pm 15\%$

AC Impedance

 $8\Omega \pm 15\%$

Distortion

Less Than 10% @1KHz 0.1W

Dimension

Ø 57.0 x H25.0mm

General Specifications

Operating Temperature Range

-20°C~+70°C

Storage Temperature Range

-30°C ~ +80°C

Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing

Standard Test Conditions

Temperature 5°C~35°C

Relative Humidity 45%~85%(RH)

Air Pressure 860 mbar ~ 1060 mbar

Front Clearance:

Keep clear of speaker front by 0.0mm for undisturbed sound reproduction: 1 -30°C ~ +80°C



Acoustic Product Specification

Product Number: SP-5728T



Release | Revision: B/2022

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2 Reliability Tests

Page 3 Measuring Method (Speaker Mode)

Reliability Tests

The sound pressure as specified will neither deviate more than ±3dB from the initial value, nor have any significant damage after any of following testing.

High Temperature Test

High Temperature +70±3°C

Duration 16 hours

Low Temperature Test

Low Temperature -30±3°C

Duration 16 hours

Humidity Test


Temperature +40±2°C

Relative Humidity 90%~95%

Duration 16 hours

Heat Shock Test


High Temperature+70°CLow Temperature-30°CChangeover Time<30 seconds</td>Duration1 hourCycle5



Temperature Cycle Test

High Temperature Low Temperature Duration Temperature gradient Cycle

+70°C -30°C 45 minutes 1 ~ 3°C / minutes 5



Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing

Drop Test

Height: 1.5m Cycle: 10 cycles (onto the concrete board)

Load Test

White noise (EIA filter) for 48 hours @3.0W input power



Acoustic Product Specification

Product Number: SP-5728T



Release | Revision: B/2022

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics


General Specifications

Page 2 Reliability Tests

Page 3

Measuring Method (Speaker Mode)

Measuring Method (Speaker Mode) (Fig. 1)



Standard baffler Recommended In IEC 268 where 491mm(W) × 600mm(H)

Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing



Acoustic Product Specification

Product Number: SP-5728T



Release | Revision: B/2022

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications


Page 2 Reliability Tests

Page 3

Measuring Method (Speaker Mode)

Frequency Response Curve (Fig. 2))

0.1W / 0.1M



Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing

www.soberton.com



4

Acoustic Product Specification

Product Number: SP-5728T



Release | Revision: B/2022

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2 Reliability Tests

Page 3 Measuring Method (Speaker Mode)

Part NameMaterialFrameMF0057-02YokeSPCC PlatedPole PieceSPCC

5 Cap Paper

No.

1


2

3

4

Dimensions

Tolerance: ±0.5 (unit: mm)



Page 4 Frequency Response Curve
Page 5 Dimensions
Page 6 Packing

6	Diaphragm	PU + Paper
7	Coil	Copper Wire (DS-UP)
8	Gasket	Non-Woven dustproof
9	Screen	Poron SR-S-70P



Acoustic Product Specification

Product Number: SP-5728T



Release | Revision: B/2022

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1


Speaker Electroacoustic Characteristics


General Specifications


Page 2 Reliability Tests

Page 3 Measuring Method (Speaker Mode)

Packing







Packing Order:

Per Tray: 100 pcs Tray Size: 550 x 260 x H70mm

Per Carton: 400 pcs

Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing

Updated: 3 August 2022 6

