AC/DC Switching Power Supply





GK220SXX-35W Switching Power Supply

Wide voltage input Isolated voltage stabilized single output AC/DC switching power supply



Product Feature

- Full range of voltage input
- Metal mesh shell package, good heat dissipation
- Working temperature up to +60°C
- Wide application range
- Conform to international and domestic safety regulations
- High efficiency, high life and low power consumption
- International standard pin
- Comply with RoHS instruction
- Heat dissipation mode: natural air cooling

Product Overview

GK220SXX-35W is the latest product developed by our company, the volume is 99 *82 * 30mm, and has the characteristics of high efficiency and low power consumption

Products meet the requirements of green environmental protection, metal aluminum shell, with good shielding and anti-interference performance and electromagnetic compatibility, short circuit protection, self-recovery and other functions.

Application Area

GK220SXX-35W series power supply has OVP, OLP, OTP and other complete protection function,meet with EN62368-1, EN61558, EN60335, GB4943 and other international and domestic safety regulations, can be widely used in: Industrial control systems, industrial automation machinery, mechanical and electrical equipment, electronic instruments, electronic equipment, devices, household appliances and other fields.

Product Brief Introduction

GK220SXX-35W series is a 35W single output power supply, the whole series provides 5V, 12V, 15V, 24V, 36V, 48V output, high output precision, with the output voltage external fine-tuning function. Suitable for 90-264VAC full range AC input, 33mm low height metal mesh shell design, not only small size, but also good heat dissipation ability, so that the whole series can operate for a long time under the ring temperature of -25°C to 60°C without fan.



AC/DC Switching Power Supply




GK220SXX-35W Switching Power Supply Parameters


GK220SXX-35W								
Part No.	Input Voltage	Output Voltage	Full load output current	Efficie ncy	Input/Output isolation withstand voltage	Material		
GK220S05-35W	90VAC~ 264VAC	5VDC±2%	7A Max	≥80%	3000VAC	Aluminum shell		
GK220S12-35W	90VAC~ 264VAC	12VDC±2%	2.917A Max	≥80%	3000VAC	Aluminum shell		
GK220S15-35W	90VAC~ 264VAC	15VDC±2%	2.333A Max	≥80%	3000VAC	Aluminum shell		
GK220S24-35W	90VAC~ 264VAC	24VDC±2%	1.458A Max	≥80%	3000VAC	Aluminum shell		
GK220S36-35W	90VAC~ 264VAC	36VDC±2%	0.972A Max	≥80%	3000VAC	Aluminum shell		
GK220S48-35W	90VAC~ 264VAC	48VDC±2%	0.729A Max	≥80%	3000VAC	Aluminum shell		




Overall dimensions and pin patterns

Metal aluminum case package





Topview



Frontview

Pin definition:

Function
AC/L
AC/N
FG
DC OUTPUT -V
DC OUTPUT +V

Unit of size: mm[inch]

Unmarked tolerance: $\pm 0.25 \pm 0.010$]



http://www.henlv.net http://www.henlv.com.cn

AC/DC Switching Power Supply







Electrical Characteristics


		Electrical Characte	ristic	S						
ltem		Condition except as otherwise herein provided Vi ,-20°C ≤Tc≤60°C		Lim						
	Symbol			Min	Max	Unit				
Output Voltage	Vo	Full Load	Vo-2%Vo	Vo+2%Vo	V					
Max Output Current	Iomax	-	-	Po/Uo	А					
Output Ripple Voltage	Vp-p	Full Load , Vi , BW=20MHz , Normal Temperature			XXmV p - p	mVp				
/oltage regulation factor	Sv	Vimin、Vi、Vimax , Full Load		-	3.00	%				
Load regulation	Si	Vi , Io =(10%~100%)Iomax		-	3.00	%				
Efficiency	η	Vi , Full Load , Normal Temperature		80.00	-	%				
Insulation Resistance	RI	Add 500VDC between the input and output points Room temperature, t≥3S		50	-	МΩ				
		General Characte	ristic							
EMC	Magnetic field sensitivity test Electrostatic discharge sensitivity test Radiation sensitivity test Conduction sensitivity test		GB6833.2-87 GB6833.3-87 GB6833.5-87 GB6833.6-87							
Temperature excursion		0.02%/°C								
Frequency	47 Hz~63 Hz (MAX)									
Humidness	90% (max)									
Leak Current	5mA (max)									
MTBF	>500 , 000 Hours									






Temperature curve **Efficiency curve**


• Typical efficiency curve




Reduction Graph



Static Characteristic Graph



Efficiency/Load Graph



Efficiency/Input Voltage Graph










Typical efficiency curve notes matters

Packing

This series of switching power supply is packaged in an independent heat shrinkable paper box.



Transport

The package equipped with switching power supply is allowed to be transported by any means of transport, which should avoid direct rain or snow and mechanical damage.

Store

Switching power supply should be stored in the ambient temperature of -40 degrees ~ 85 degrees, relative humidity of 20%~90%, the surrounding environment without acid, alkaline and other harmful gases in the warehouse.

The above are the performance indicators of the product series listed in this manual. Some indicators of nonstandard products may exceed the above requirements. In case of any inconsistency between the manual and the product specification documents, please refer to the specification documents.