

**Harvatek Surface Mount CHIP LED Data Sheet  
B1101NG--20C000133U1930**

|  |                                     |             |           |
|--|-------------------------------------|-------------|-----------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |           |
| Tentative Product  | *****                               | *****       |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 1/14 |

**DISCLAIMER**..... 3

**PRODUCT SPECIFICATIONS**..... 4

**ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION** .....4

**LABEL SPECIFICATIONS**..... 5

**PRODUCT SPECIFICATIONS**..... 5

**PRODUCT FEATURES** ..... 6

**ELECTRO-OPTICAL CHARACTERISTICS**.....6

**PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW**

**SOLDERING**.....7

**ABSOLUTE MAXIMUM RATINGS** .....7

**PRECAUTION FOR USE** .....8

**CHARACTERISTICS OF B1101NG** .....9

**PACKAGING** ..... 10

**TAPE DIMENSION** .....10

**REEL DIMENSION**.....11

**PACKING**.....11

**DRY PACK**..... 12

**BAKING** .....12

**PRECAUTIONS** .....12

**REFLOW SOLDERING** ..... 13

**REWORKING**.....13

**CLEANING**.....13

**REVISE HISTORY**.....14

|  |                                     |             |           |
|--|-------------------------------------|-------------|-----------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |           |
| Tentative Product  | *****                               | *****       |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 2/14 |

**DISCLAIMER**

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

**LIFE SUPPORT POLICY**

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
  
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

|  |                                     |             |           |
|--|-------------------------------------|-------------|-----------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |           |
| Tentative Product  | *****                               | *****       |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 3/14 |

## Product Specifications

|                        | Specification  | Material                          | Quantity         |
|------------------------|--|-----------------------------------|------------------|
| Luminous Intensity(Iv) | NG:180.0-450.0 mcd<br>@20mA/ T <sub>S</sub> = 25°C;Tolerance: ± 10%        |                                   |                  |
| Wavelength             | NG:520-535 nm<br>@20mA/ T <sub>S</sub> = 25°C;Tolerance: ± 0.5nm           |                                   |                  |
| Vf                     | NG:2.7-3.9 V(0.2V/BIN)<br>@20mA/ T <sub>S</sub> = 25°C ;Tolerance: ± 0.05V |                                   |                  |
| Ir                     | < 10 μA @ V <sub>R</sub> = 5 V   |                                   |                  |
| Resin                  | Clear  | Epoxy resin                       |                  |
| Carrier tape           | EIA 481-1A specs   | Conductive black tape             | 3000pcs per reel |
| Reel                   | EIA 481-1A specs   | Conductive black                  |                  |
| Label                  | HT standard  | Paper                             |                  |
| Packing bag            | 250x230mm  | Aluminum laminated bag/ no-zipper | One reel per bag |
| Carton                 | HT standard  | Paper                             | Non-specified    |

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, λ<sub>D</sub> and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

### ATTENTION: Electrostatic Discharge (ESD) protection




The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

|  |                                     |             |           |
|--|-------------------------------------|-------------|-----------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |           |
| Tentative Product  | *****                               | *****       |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 4/14 |

## Label Specifications



### Harvatek P/N:

**B 110 1 NG-- 20C- 0001 33**

| Product | Package                 | Dice Qty | Color | Current | Series Number | Taping                   |
|---------|-------------------------|----------|-------|---------|---------------|--------------------------|
| B:PCB   | 3.2(L)x1.0(W)x1.5(H) mm | 1:Single | Green | 20mA    | X001~XZZZ     | 1.Taping style<br>2. Qty |

### Lot No.:

| 1                     | 2 | 3         | 4          | 5         | 6                  | 7      | 8            | 9      | 10      |
|-----------------------|---|-----------|------------|-----------|--------------------|--------|--------------|--------|---------|
| E                     | 1 | A         | 1          | A         | 2                  | 2      | L            | 1      | 2       |
| Code 1 2              |   | Code 3    | Code 4     | Code 5    | Code 6             | Code 7 | Code 8       | Code 9 | Code 10 |
|                       |   | Mfg. Year | Mfg. Month | Mfg. Date | Consecutive number |        | Special code |        |         |
| Internal Tracing Code |   | 2020-L    |            | 1:A       | 01~ZZ              |        | 000~ZZZ      |        |         |
|                       |   | 2021-M    |            | 2:B       |                    |        |              |        |         |
|                       |   | 2022-P    |            | 3:C       |                    |        |              |        |         |
|                       |   | 2023-Q    | 1:Jan.     | ...       |                    |        |              |        |         |
|                       |   | ...       | 2:Feb.     | ...       |                    |        |              |        |         |
|                       |   | 2026-T    | ...        | 26:Z      |                    |        |              |        |         |
|                       |   | 2027-V    | A:Oct.     | 27:7      |                    |        |              |        |         |
|                       |   | ...       | B:Nov.     | 28:8      |                    |        |              |        |         |
|                       |   | 2030-Y    | ...        | 29:9      |                    |        |              |        |         |
|                       |   | 2031-Z    | C:Dec.     | 30:3      |                    |        |              |        |         |
| ...                   |   | 31:4      |            |           |                    |        |              |        |         |

## Product specifications

### Luminous Intensity (Iv) Bin:

| Color | Bin Code | Spec. Range |
|-------|----------|-------------|
|-------|----------|-------------|

|  |                                     |             |           |
|--|-------------------------------------|-------------|-----------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |           |
| Tentative Product  | *****                               | *****       |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 5/14 |

|           |          |                        |
|-----------|----------|------------------------|
| <b>NG</b> | <b>S</b> | <b>180.0-285.0 mcd</b> |
|           | <b>T</b> | <b>285.0-360.0 mcd</b> |
|           | <b>U</b> | <b>360.0-450.0 mcd</b> |

Note: It maintains a tolerance of  $\pm 10\%$  on Luminous Intensity

## ■ Wavelength Bin:

| Color     | Bin Code | Spec. Range           |
|-----------|----------|-----------------------|
| <b>NG</b> | <b>B</b> | <b>520.0-525.0 nm</b> |
|           | <b>C</b> | <b>525.0-530.0 nm</b> |
|           | <b>D</b> | <b>530.0-535.0 nm</b> |

Note: It maintains a tolerance of  $\pm 0.5\text{nm}$  on Wavelength Bin

## ■ Forward Voltage (Vf) Bin:

| Color     | Bin Code  | Spec. Range      |
|-----------|-----------|------------------|
| <b>NG</b> | <b>G8</b> | <b>2.7-2.9 V</b> |
|           | <b>H7</b> | <b>2.9-3.1 V</b> |
|           | <b>H8</b> | <b>3.1-3.3 V</b> |
|           | <b>J7</b> | <b>3.3-3.5 V</b> |
|           | <b>J8</b> | <b>3.5-3.7 V</b> |
|           | <b>K7</b> | <b>3.7-3.9 V</b> |

Note: It maintains a tolerance of  $\pm 0.05\text{V}$  on forward voltage measurements

## Product Features

### Electro-Optical Characteristics

| Series   | Emitting Color                      | Material | $V_F(V)$ | Wavelength $\lambda(\text{nm})$ | $I_V(\text{mcd})$ | Viewing   |
|--|-------------------------------------|----------|----------|---------------------------------|-------------------|-----------|
| (T <sub>Soldering</sub> , 25 °C)   |                                     |          |          |                                 |                   |           |
| Official Product   | HT Part No. B1101NG--20C000133U1930 |          |          |                                 |                   |           |
| Tentative Product  | *****                               |          | *****    |                                 |                   |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                                     |          |          | 11/17/2020                      | Version 1.3       | Page 6/14 |

|             |    |       |     |     |             |             |                 |         |                             |
|-------------|----|-------|-----|-----|-------------|-------------|-----------------|---------|-----------------------------|
|             |    |       | typ | max | $\lambda_D$ | $\lambda_P$ | $\Delta\lambda$ | Typical | Angle $2\theta \frac{1}{2}$ |
| B1101NG--20 | NG | InGaN | 3.3 | 3.9 | 527         | 520         | 40              | 285.0   | X=140<br>Y=115              |

### Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering

Unit: mm Tolerance: +/-0.1

| Outline Dim.   | Soldering Pattern |
|--|-------------------|
|  |                   |
| Soldering terminals may shift in the x, y direction. |                   |

### Absolute Maximum Ratings

( $T_{\text{Soldering}} 25\text{ }^{\circ}\text{C}$ )

| Series | $P_D$ (mW)        | $I_F$ (mA)      | $I_{FP}$ (mA)*        | $T_{OP}$ ( $^{\circ}\text{C}$ ) | $T_{ST}$ ( $^{\circ}\text{C}$ ) |
|--------|-------------------|-----------------|-----------------------|---------------------------------|---------------------------------|
| Color  | Power Dissipation | Forward Current | Pulse Forward Current | Operating Temperature           | Storage Temperature             |
| NG     | 78                | 20              | 80                    | -40~+85                         | -40~+100                        |

\*Condition for  $I_{FP}$  is pulse of 1/10 duty and 0.1msec width

|  |                                     |             |           |
|--|-------------------------------------|-------------|-----------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |           |
| Tentative Product  | *****                               | *****       |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 7/14 |





## Precaution for Use

1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
4. The LEDs must be used within 4 weeks after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
5. The appearance and specifications of the products may be modified for improvement without further notice.
6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs. If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs. Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.


|  |                                     |             |           |
|--|-------------------------------------|-------------|-----------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |           |
| Tentative Product  | *****                               | *****       |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 8/14 |




## Characteristics of B1101NG



### Directive Characteristics




### Directive Characteristics




|  |                                     |             |           |
|--|-------------------------------------|-------------|-----------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |           |
| Tentative Product  | *****                               | *****       |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 9/14 |

**Packaging**  
**Tape Dimension**




| Dim. A    | Dim. B    | Dim. C    | Qty/Reel |
|-----------|-----------|-----------|----------|
| 3.40±0.10 | 1.70±0.10 | 1.20±0.10 | 3K       |




|  |                                     |             |            |
|--|-------------------------------------|-------------|------------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |            |
| Tentative Product  | *****                               | *****       |            |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 10/14 |

## Reel Dimension



## Packing



5 or 10 boxes per carton is available depending on shipment quantity.


|  |                                     |             |            |
|--|-------------------------------------|-------------|------------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |            |
| Tentative Product  | *****                               | *****       |            |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 11/14 |

## Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



## Baking

Baking before soldering is recommended when the package has been unsealed for 4 weeks.

The conditions are as followings:

1.  $60\pm 3^{\circ}\text{C} \times (12\sim 24\text{hrs})$  and  $<5\% \text{RH}$ , taped reel type.
2.  $100\pm 3^{\circ}\text{C} \times (45\text{min}\sim 1\text{hr})$ , bulk type.
3.  $130\pm 3^{\circ}\text{C} \times (15\text{min}\sim 30\text{min})$ , bulk type.

## Precautions

1. Avoid exposure to moisture at all times during transportation or storage.
2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlInGaP products.
3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
5. Avoid direct contact with the surface through which the LED emits light.
6. If possible, assemble the unit in a clean room or dust-free environment.


|  |                                     |             |            |
|--|-------------------------------------|-------------|------------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |            |
| Tentative Product  | *****                               | *****       |            |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 12/14 |

## Reflow Soldering

Recommend soldering paste specifications:

1. Operating temp.: Above 217°C ,60~150 sec
2. Peak temp.:260 °C Max.,10sec Max.
3. Reflow soldering should not be done more than two times.
4. Never attempt next process until the component is cooled down to room temperature after reflow.
5. The recommended reflow soldering profile (measured on the surface of the LED terminal) is as following:

Lead-free Solder Profile



## Reworking

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

## Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultrasonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 °C max, <3min

|  |                                     |             |            |
|--|-------------------------------------|-------------|------------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |            |
| Tentative Product  | *****                               | *****       |            |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 13/14 |

**Cautions of Pick and Place**

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

**Revise History**

| Rev. | Descriptions              | Date       | Page |
|------|---------------------------|------------|------|
| 1.0  | -                         | 05/28/2013 | -    |
| 1.1  | Renew form                | 06/12/2017 | -    |
| 1.2  | Renew form                | 02/25/2020 | -    |
| 1.3  | Add Customer Product Code | 11/17/2020 | P5   |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |
|      |                           |            |      |

|  |                                     |             |            |
|--|-------------------------------------|-------------|------------|
| Official Product   | HT Part No. B1101NG--20C000133U1930 |             |            |
| Tentative Product  | *****                               | *****       |            |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | 11/17/2020                          | Version 1.3 | Page 14/14 |