

www.vishay.com

Vishay Semiconductors

# **1IR Receiver Modules for Remote Control Systems**





#### LINKS TO ADDITIONAL RESOURCES



#### DESCRIPTION

The TSMP77138 series are miniaturized SMD IR receiver modules for infrared remote control systems. Two PIN diodes and a preamplifier are assembled on a leadframe, the epoxy package contains an IR filter. The modulated output signal, carrier out, can be used for repeater applications and code learning applications.

These components have not been qualified according to automotive specifications.

#### FEATURES

- Two lenses for high sensitivity and wide receiving angle
- AC coupled response from 30 kHz to 55 kHz, all data formats
- If the IR signal strength is less then 0.5 W/m<sup>2</sup> (distance more than 0.5 m with a typical IR remote control), the frequency range is up to 60 kHz
- Improved shielding against electrical field disturbance
- AGC to suppress ambient noise
- High sensitivity, long receiving range
- Supply voltage: 2.5 V to 5.5 V
- · Carrier out signal for IR repeater applications
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

#### **MECHANICAL DATA**

#### Pinning:


1, 4 = GND, 2 = V<sub>S</sub>, 3 = OUT

#### **ORDERING CODE**


#### Taping:

TSMP77138TT - top view taped, 2200 pcs/reel TSMP77138TR - side view taped, 2300 pcs/reel

#### **BLOCK DIAGRAM**



#### APPLICATION CIRCUIT



Recommended circuit for best sensitivity of the TSMP.... in repeater applications. It limits the output voltage swing  $V_0$  to about 0.7 V in order to avoid internal coupling. 22638-1



#### RoHS COMPLIANT HALOGEN FREE GREEN

(5-2008)



www.vishay.com

# Vishay Semiconductors

**TSMP77138** 

PARTS TABLE			
AGC		LEGACY, FOR LONG BURST REMOTE CONTROLS (AGC2)	
Carrier frequency 38 kHz		TSMP77138	
Package		Heimdall	
Pinning		1, 4 = GND, 2 = V <sub>S</sub> , 3 = OUT	
Dimensions (mm)		6.8 W x 3.0 H x 3.2 D	
Mounting		SMD	
Application		Repeater	
Special options		<ul> <li>Extended temperature range: <u>www.vishay.com/doc?82738</u></li> <li>Narrow optical filter: <u>www.vishay.com/doc?81590</u></li> <li>Wide optical filter: <u>www.vishay.com/doc?82726</u></li> </ul>	

ABSOLUTE MAXIMUM RATINGS				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Supply voltage		V <sub>S</sub>	-0.3 to +6	V
Supply current		I <sub>S</sub>	5	mA
Output voltage		Vo	-0.3 to (V <sub>S</sub> + 0.3)	V
Output current		Ι <sub>Ο</sub>	5	mA
Junction temperature		Tj	100	°C
Storage temperature range		T <sub>stg</sub>	-25 to +85	°C
Operating temperature range		T <sub>amb</sub>	-25 to +85	°C
Power consumption	$T_{amb} \le 85 \ ^{\circ}C$	P <sub>tot</sub>	10	mW

Note


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only
and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this specification
is not implied. Exposure to absolute maximum rating conditions for extended periods may affect the device reliability

ELECTRICAL AND O	PTICAL CHARACTERISTICS (T <sub>amb</sub> = 25	°C, unles	s otherwi	se specif	ied)	
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply voltage		Vs	2.5	-	5.5	V
Supply current	$V_{\rm S} = 5  V,  E_{\rm v} = 0$	I <sub>SD</sub>	0.55	0.7	0.9	mA
Supply current	$E_v = 40$ klx, sunlight	I <sub>SH</sub>	-	0.8	-	mA
Transmission distance	$E_v = 0$ , test signal see Fig. 1, IR diode TSAL6200, I <sub>F</sub> = 50 mA	d	-	7	-	m
Output voltage low	$I_{OSL} = 0.5 \text{ mA}, E_e = 0.7 \text{ mW/m}^2,$ test signal see Fig. 1	V <sub>OSL</sub>	-	-	100	mV
Minimum irradiance	Less than 5 missing or 5 additional sub carrier pulses related to one burst	E <sub>e min.</sub>	-	1	2	mW/m <sup>2</sup>
Maximum irradiance	Less than 5 missing or 5 additional sub carrier pulses related to one burst	E <sub>e max.</sub>	30	-	-	W/m <sup>2</sup>
Directivity	Angle of half transmission distance	φ1/2	-	± 50	-	0

Rev. 1.9, 11-Oct-2022



# **Vishay Semiconductors**






Fig. 1 - Output Active Low




Fig. 2 - Pulse Length and Sensitivity in Dark Ambient






Fig. 3 - Relative Spectral Sensitivity vs. Wavelength






Rev. 1.9, 11-Oct-2022



www.vishay.com

**Vishay Semiconductors** 

#### **PACKAGE DIMENSIONS** in millimeters



#### **ASSEMBLY INSTRUCTIONS**

#### **Reflow Soldering**

- Reflow soldering must be done within 72 h while stored under a max. temperature of 30 °C, 60 % RH after opening the dry pack envelope
- Set the furnace temperatures for pre-heating and heating in accordance with the reflow temperature profile as shown in the diagram. Exercise extreme care to keep the maximum temperature below 260 °C. The temperature shown in the profile means the temperature at the device surface. Since there is a temperature difference between the component and the circuit board, it should be verified that the temperature of the device is accurately being measured
- Handling after reflow should be done only after the work surface has been cooled off

#### Manual Soldering


- $\bullet$  Use a soldering iron of 25 W or less. Adjust the temperature of the soldering iron below 300  $^\circ C$
- Finish soldering within 3 s
- Handle products only after the temperature has cooled off

Rev. 1.9, 11-Oct-2022





**Vishay Semiconductors** 

#### VISHAY LEAD (Pb)-FREE REFLOW SOLDER PROFILE



### TAPING VERSION TSMP..TR DIMENSIONS in millimeters





Drawing-No.: 9.700-5337.01-4 Issue: 2; 06.10.15



Rev. 1.9, 11-Oct-2022

Document Number: 82795


End of Life May-2023 - Alternative Device: TSMP95100



www.vishay.com

Vishay Semiconductors

## TAPING VERSION TSMP..TT DIMENSIONS in millimeters






technical drawings according to DIN specifications


Drawing-No.: 9.700-5338.01-4 Issue: 4; 12.06.13



## **Vishay Semiconductors**

### **REEL DIMENSIONS** in millimeters





Form of the leave open of the wheel is supplier specific.

Dimension acc. to IEC EN 60 286-3


Tape width 16



technical drawings according to DIN specifications

Drawing-No.: 9.800-5052.V2-4 Issue: 1; 07.05.02

### LEADER AND TRAILER DIMENSIONS in millimeters



#### **COVER TAPE PEEL STRENGTH**

According to DIN EN 60286-3 0.1 N to 1.3 N  $300 \pm 10 \text{ mm/min.}$  $165^{\circ}$  to  $180^{\circ}$  peel angle

Rev. 1.9, 11-Oct-2022

### End of Life May-2023 - Alternative Device: TSMP95100



**TSMP77138** 

**Vishay Semiconductors** 

#### **OUTER PACKAGING**

The sealed reel is packed into a pizza box.

CARTON BOX DIMENSIONS in millimeters					
	hickness Width	Length			
	THICKNESS	WIDTH	LENGTH		
Pizza box (SMD and heimdall) (taping in reels)	50	340	340		

#### LABEL

#### Standard bar code labels for finished goods

The standard bar code labels are product labels and used for identification of goods. The finished goods are packed in final packing area. The standard packing units are labeled with standard bar code labels before transported as finished goods to warehouses. The labels are on each packing unit and contain Vishay Semiconductor GmbH specific data.

VISHAY SEMICONDUCTOR Gr		
PLAIN WRITING	ABBREVIATION	LENGTH
Item-description	-	18
Item-number	INO	8
Selection-code	SEL	3
LOT-/serial-number	BATCH	10
Data-code	COD	3 (YWW)
Plant-code	PTC	2
Quantity	QTY	8
Accepted by	ACC	-
Packed by	PCK	-
Mixed code indicator	MIXED CODE	-
Origin	xxxxxx+	Company logo
LONG BAR CODE TOP	TYPE	LENGTH
Item-number	Ν	8
Plant-code	Ν	2
Sequence-number	Х	3
Quantity	Ν	8
Total length	-	21
SHORT BAR CODE BOTTOM	ТҮРЕ	LENGTH
Selection-code	Х	3
Data-code	Ν	3
Batch-number	Х	10
Filter	-	1
Total length	-	17

Rev. 1.9, 11-Oct-2022

ESD PRECAUTION

**CODE LABELS** (example)

data.

22178



# **TSMP77138**

Vishay Semiconductors

Proper storage and handling procedures should be followed

to prevent ESD damage to the devices especially when they


are removed from the antistatic shielding bag. Electrostatic sensitive devices warning labels are on the packaging.

VISHAY SEMICONDUCTORS STANDARD BAR

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific

### **DRY PACKING**

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



### FINAL PACKING

The sealed reel is packed into a cardboard box.

#### **RECOMMENDED METHOD OF STORAGE**

Dry box storage is recommended as soon as the aluminum bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.

After more than 72 h under these conditions moisture content will be too high for reflow soldering.


In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

192 h at 40 °C + 5 °C / - 0 °C and < 5 % RH (dry air / nitrogen) or

96 h at 60  $^\circ\text{C}$  + 5  $^\circ\text{C}$  and < 5 % RH for all device containers or

24 h at 125 °C + 5 °C not suitable for reel or tubes.

An EIA JEDEC<sup>®</sup> standard J-STD-020 level 4 label is included on all dry bags.



EIA JEDEC standard J-STD-020 level 4 label is included on all dry bags

Rev. 1.9, 11-Oct-2022





Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.