
## **CONFIDENTIAL & PROPRIETARY INFORMATION**

This document contains Confidential and Proprietary Information of Alliance LLC, and all design, manufacturing, reproduction, use, and sale rights of such information are expressly reserved





1. MAGNET PROPERTIES PER BIF-12:

Br: 2,450-2,650 G Hc: 2,140-2,640 Oe Hci: ≥2,640 Oe

BH<sub>(max)</sub>: 1.4-1.6 MGOe T max: 120° C

## **TOLERANCES** (UNLESS OTHERWISE NOTED)

DECIMAL METRIC  $X.XX = \pm .01$   $X.X = \pm .25$  $X.XXX = \pm .005 \ X.XX = \pm .13$ **ANGLES** 

Rev

Date

Ву

± .5°

DO NOT SCALE DRAWING

## **Alliance LLC** 1450 CLARK DRIVE, VALPARAISO, INDIANA 46385

DESCRIPTION: INJECTION MOLDED FERRITE

P/N: YB-104-1		BONDED MAGNET
MATERIAL:	Dwg by: BT	REV LEVEL: A
COATING: NONE	Apr by: DV	Apr. Dated: 03-14-2020