







Product Outline:

This is the high efficiency LED with reflector type. EMC 3030 Single color is a surface-mount LED which with heat sink to enhance operating performance. With special binning technology, these LEDs are ideal for architecture lighting and special lighting needs.

Features:

- Royal Blue color
- High brightness output @ 150mA,
- High driving current to 200mA.
- Package Dimension = 3.2mmX3.0mmX0.6mm
- RoHS compliant
- Custom Bin available upon special request

Application:

- Warning lamp
- Decoration lamp
- Architecture Lighting
- Garden Lighting
- Horticulture Lighting

Compliance and Certification:











Mechanical Property: (Dimension)



- * All dimensions are in millimeters,
- * Tolerances are ± 0.10mm.

Recommended Solder footprint:



- * All dimensions are in millimeters.
- * The LEDs is designed to be reflow soldered on to a PCB. IF dip soldered that QL cannot guarantee its reliability.
- * Reflow soldering must not be performed more than twice.





Characteristics

■ Absolute Maximum Ratings

(Ta=25°C)

Parameter	Symbol	Rating	Unit
DC Forward Current	If	200	mA
Leakage Current	lr	1.0	μΑ
Power Dissipation	Pd	0.6	W
Pulse Forward Current	lfp	240	mA
LED Junction Temperature	TJ	125	°C
Storage Temperature	Tstg	-40 ~ 100	°C
Operation Temperature	Topr	-40 ~ 85	°C
Soldering Temperature	Tsol	260 < 10 sec	°C
ESD Sensitivity(HBM)		8	KV
Thermal Resistance	Rth	10	°CW

⁽¹⁾ Proper current rating must be observed to maintain junction temperature below maximum at all time

■ Electrical / Optical Characteristic

(Ta=25 oC)

Product	Color	I _F (mA)	V _F (V) Typ. max		Wavelength		htness n/mW)
					nm	min	typ.
QLSP04RBH	Royal Blue	150	3.0	3.5	447.5~460		250 mW



⁽²⁾ IFP Condition: Duty 1/10, Pulse within 10msec



Radiometric Power Bin Structure at 150mA

Product	Color	Radiometric Power (mW)		PPF (µmol/s)		PPF/W (μmol/J)	
rroddet	Color	min.	max.	min.	max.	Тур.	
QLSP04RBH	Royal Blue	240	280	0.93	1.04	2.4	

■ Groups
Dominant Wavelength

Wd (nm) @ 150mA				
Color Code name Min. Max.				
Dovol Pluo	DA	450	455	
Royal Blue	DB	455	460	

Measurement tolerance is +/- 1nm

Forward Voltage (V_F) Bin:

VF Rank @ 150mA (Vf)			
Color	Code name	Low	High
Royal Blue	01	2.8	3.0
	23	3.0	3.2
	45	3.2	3.4
	67	3.4	3.6

The forward voltage tolerance is $\pm 0.1V$

Luminous Flux Bin:

luminous flux tolerance is ± 7%

Rank @ 150mA (mW)			
Color Code name Low High			
Royal Blue MN1 240 280			


luminous flux tolerance is ± 7%






Characteristic Curves

(1) Color Spectrum











(2). Typical Representative Spatial Radiation Pattern




(3). Forward Current Characteristics







(4). Forward Current vs Forward Voltage







■ Reliability test:

No	Item	Condition	Time/Cycle	Sample size
1	Steady State Operating Life of Room Temperature	25 [°] C Operating	1000 Hrs	20 pcs
2	Steady State Operating Life of Low Temperature -40°C	-40°C Operating	1000 Hrs	20 pcs
3	Steady State Operating Life of Low Temperature $60^{\circ}\!\mathbb{C}$	60°C Operating	1000 Hrs	20 pcs
4	Steady State Operating Life of Low Temperature $85^{\circ}\!\mathbb{C}$	85 [°] C Operating	1000 Hrs	20 pcs
5	Low temperature storage -40°C	-40°C Storage	1000 Hrs	20 pcs
6	High temperature storage 100°C	100°C Storage	1000 Hrs	20 pcs
7	Steady State Operating Life of High Humidity Heat 60° € 90%	60°C/90% Operating	1000 Hrs	20 pcs
8	Steady State Pulse Operating Life Condition	25°C 10Hz duty=1/10 Operating	200 Cycle	20 pcs
9	Resistance to soldering heat on PCB (JEDEC MSL3)	pre-store@60°ℂ, 60%RH for 52hrs Tsld max.=260 10sec	3 Times	20 pcs
10	Heat Cycle Test (JEDEC MRC)	25℃~65℃~-10℃, 90%RH, 24hr/1cycle	10 Cycle	20 pcs
11	Thermal shock	-40°C / 20minr~ 5minr~100°C /20min	300 Cycle	20 pcs

■ Judgment Criteria:


Item	Symbol	Test Condition	Judgment Criteria
Forward Voltage	Vf	150 mA	△Vf< 10%
Luminous Flux	lv	150 mA	△Iv< 30%





Solder Profile:

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):




Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Temperature Min(T _{smin})	100°C	150℃
Temperature Max(T _{smax})	150℃	200℃
Time(t _a) from (T _{smin} to T _{smax})	60-120 seconds	60-120 seconds
Ramp-up rate(T_L to T_P)	3°ℂ/second max.	3℃/second max.
Liquidous Temperature (T_L)	183℃	217℃
Time(t _L) maintained above T _L	60-150 seconds	60-150 seconds
Peak package body temperature(T _P)	235℃	260℃
Time within 5° C of Actual Peak temperature (t_p)	20seconds*	30 seconds*
Ramp-down rate(T_P to T_L)	6℃/second max.	6℃/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.


 $^{^{*}}$ Tolerance for peak profile temperature (T $_{ extsf{P}}$) is defined as a supplier minimum and a user maximum.





Taping & Packing:








Unit: mm













Labeling

Quantity: XXXX

Quelighting P/N: XXXXXX

lv Bin: XX Color Bin: XX Vf Bin: XX Date Code: XXXX

QueLighting

Ordering Information:

Part #	Multiple Quantities	Quantity per Reel
QLSP04RBH		1000, 2000 pcs





Revision History:

Revision Date:	Changes:	Version #:
09-21-2020	Initial release	1.0

