

Dwg. Number	Customer P/N	Times P/N	Length(L) in 'mm'
IE-00409-01	-	MGS200-KMKM-0.5M	500+10/-0
IE-00409-02	-	MGS200-KMKM-1.0M	1000+20 /-0
IE-00409-03	-	MGS200-KMKM-2.0M	2000+40/-0
IE-00409-04	-	MGS200-KMKM-2.5M	2500+50/-0

1.0 Scope

This drawing documents the construction and performance of Maxgain 200 cable assemblies manufactured by Times Microwave systems.

2.0 Cable Information

- 2.1 Cable to be MAXGAIN 200
- 2.2 Jacket color to be Blue
- 2.3 Jacket material to be FEP
- 2.4 Nominal cable impedance to be 50 ohms
- 2.5 Cable diameter to be 5.10mm [0.201"].

3.0 Connector Information

3.1 Forward Connector

Type K (M) Straight Connector (SP013) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated

3.2 After Connector Type K (M) Straight Connector (SP013) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated

Unless otherwise spec- ified, dimensions are in MM. Tolerances are applicable when spec- ified.				TIMES MICROWAVE SYSTEMS					
	Drawn	SVP	10/20/22		www.timesmicrowave.com				
These drawings and specifications contain proprietary information which is the property of	Checked			MG200 CABLE ASSEMBLY					
	Approved			(Space Assemblies)					
Times Microwave	Approved			Size	Size CAGE CC		Drawing	No.:	
Systems.				A	68999		IE	-00409-XX	
				Scale:	Scale: NA		(A)	Sheet: 1 of 3	

	THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE	SAME AS SHEET	1
REV	DESCRIPTION	DATE	BY
А	INITIAL RELEASE	10/20/22	SVP

4.0 Electrical Performance

- 4.1 Frequency range: DC 30GHz
- 4.2 Insertion loss & VSWR: As per below table,

Dwg. Number	Max. Insertion Loss in dB	Max. VSWR		
Dwg. Number	@ 30GHz	@ 30GHz		
IE-00409-01	1.43	1.35		
IE-00409-02	2.31	1.35		
IE-00409-03	4.07	1.35		
IE-00409-04	4.95	1.35		

5.0 Mechanical Performance

- 5.1 Overall Length to be specified length.
- 5.2 Minimum Bend radius is 31.8mm [1.25"].

6.0 Environmental Performance

- 6.1 Installation Temperature Range (-55°C to +150°C)
- 6.2 Storage Temperature Range (-55°C to +150°C)
- 6.3 Operating Temperature Range (-55°C to +150°C)

7.0 Marking

- 7.1 Markers are to be black text on White Color Marker Sleeve.
- 7.2 Marker Configuration to be:

Dwg. Number	Marking details	Marker Numbers	Marker Position	
IE-00409-01	Times Microwave Systems MGS200-KMKM-0.5M \$\$\$\$\$	1	In Center of the Cable Assy.	
IE-00409-02	Times Microwave Systems MGS200-KMKM-1.0M \$\$\$\$\$	1	In Center of the Cable Assy.	
IE-00409-03	Times Microwave Systems MGS200-KMKM-2.0M \$\$\$\$\$	1 & 2	At Both Ends	

Unless otherwise spec- ified, dimensions are in MM. Tolerances are applicable when spec- ified. These drawings and specifications contain proprietary information									
	Drawn	SVP	10/20/22		www.timesmicrowave.com				
	Checked			MG200 CABLE ASSEMBLY (Space Assemblies)					
which is the property of	Approved				blies)				
Times Microwave	Appioveu			Size CAGE C A 6899		CODE Drawin		g No.:	
Systems.						99	IE	E-00409-XX	
				Scale:	NA	Rev.	(A)	Sheet: 2 of 3	

	THE RE	VISION STAT	TUS OF	ALL SHEET	S OF TH	IIS DRAWI	NG IS TH	HE SAME A	S SHEET 1	
REV		DESCRIPTION						DA	TE	BY
A I	NITIAL RE	LEASE						10/2	0/22	SVP
I			Т	ïmes Microwa	ave Svst	ems]
		IE-00409-0	4	MGS200-KN \$\$\$	ИКМ-2.5 \$\$	М	1 & 2	At E	Both Ends	
		\$\$\$\$\$ = 5-dig Register to be					ration.			
8.	0 NOTES									
		All Dimension	s are in	MM.						
	8.2	Assemblies bu	uilt in Cl	ass 100,000 (clean roo	om.				
		Low outgassir	-	•						
	8.4	Unless Otherv	vise Spe	ecified: Tolera	ance will	be,				
		Linear Dime	ension	Tolerar	nce					
		<500 m	ım	±10 m	m					
		500-2000	mm	±15 m	m					
		>2000 mm ±20 mm								
	t	**Tolerances	s are n	ot accumul	ative.					
Jnless other	wise spec-									
ied, dimens /M. Tolerar pplicable w	ions are in nces are								TEMS	
ied.	-	Drawn	SVP	10/20/22			W	ww.timesmi	crowave.com	۱
hese drawin pecification roprietary ir	s contain	Checked				MG200 CA			SEMBLY blies)	
hich is the Times Mic	property of prowave	Approved			Size				No.:	
Syste	ms.				A	689	68999		IE-00409-XX	
					Scale:	NA	Rev. ((A)	Sheet: 3	3 of 3