PCN Number:		202	21	03:	1004.1 <mark>A</mark>		PC	N Date:	March 29, 2023	
Title:		•	ualification of new Fab site (RFAB) using qualified Process Technology, Die Revision,							
		Datasheet up	date	an	nd additional Assembly site options for select devices					
Cus	tomer	Contact:	F	<u> PCI</u>	N M	<u>anager</u>	ager Dept:		Q	uality Services
Proposed 1 st Ship Date:			lan	า 31	., 2023	Sample requests accepted until:		1 1/1	ov 30, 2022*	
*Sa	mple ı	requests rece	ived	aí	fteı	November 30, 20	22 will no	t b	e suppoi	ted.
Cha	nge Ty	/pe:								
\boxtimes	Assen	nbly Site				Assembly Process			Assem	oly Materials
□ Design		Electrical Specificat	ion		Mechai	nical Specification				
	Test S	Site			X	Packing/Shipping/L	abeling		Test Pr	ocess
☐ Wafer Bump Site					Wafer Bump Material			Wafer	Bump Process	
			X	Wafer Fab Materials		\boxtimes	Wafer	Fab Process		
						Part number chang	е			
	PCN Details									

Description of Change:

The purpose of Revision A is to correct a typo in the SFAB wafer diameter as shown in the yellow highlight below.

Texas Instruments is pleased to announce the qualification of a new fab & process technology (RFAB, LBC7) and additional Assembly site (MLA) for selected devices listed below in the product affected section.

	Current Fab S	ite	Additional Fab Site		
Current Fab Site	Process	Wafer Diameter	Additional Fab Site	Process	Wafer Diameter
DL-LIN	LBC2	150 mm			
DL-LIN	LBC2	200 mm	RFAB	LBC7	300 mm
SFAB	OI	200 150 mm	READ	LBC/	300 111111
SFAB	JI1	200 150 mm			

The die was also changed as a result of the process change.

Additionally, there will be a BOM/Assembly options introduced for these devices:

Group 1 (RFAB/Process migration & no construction differences)

Group 2 (RFAB/Process migration & MLA as an additional Assembly site, no construction differences):

Group 3 (RFAB/Process migration & CDAT as an additional Assembly site [CARZ])

	CARZ	CDAT
Mold Compound	SID#441086	4222198
Mound Compound	SID#435143	4207123

Group 4 (RFAB/Process migration & CDAT as an additional Assembly site [CRS])

	CRS	CDAT
Mold Compound	SID#441272	4222198
Mound Compound	SID#435143	4207123

The datasheets will be changing as a result of the above mentioned changes. The datasheet change details can be reviewed in the datasheet revision history. The links to the revised datasheets are available in the table below.



	ctober 2022) Page
 Changed the data sheet format to the latest data sheet 	
Changed the Thermal Information table	4
TEXAS INSTRUMENTS	SN75ALS181 SLLS152E – DECEMBER 1992 – REVISED OCTOBER 2022
Character Bardelan B (Assessed 2042) to Bardelan E	(Outshar 2000)
Changes from Revision D (August 2013) to Revision E Added the Pin Configuration and Functions	(October 2022) Page
Deleted the Package thermal impedance from the Abso	
Added the Thermal Information table	
Added the Detailed Description section	10
TEXAS INSTRUMENTS	SN55LBC180, SN65LBC180, SN75LBC180 SLLS174I – FEBRUARY 1994 – REVISED OCTOBER 2022
Changes from Revision H (June 2022) to Revision I (Oc	
Changed RSA (QFN) values in the Thermal Information	Table 6
TEXAS INSTRUMENTS	SN75LBC179, SN65LBC179, SN65LBC1790 SLLS173G – JANUARY 1994 – REVISED OCTOBER 2022
Changes from Revision F (April 2006) to Revision G (O	ctober 2022) Page
Changed the data sheet format to the latest data sheet Added the Thermal Information table	format1
TEXAS INSTRUMENTS	SN55LBC176, SN65LBC176, SN75LBC176 SLLS067I – AUGUST 1990 – REVISED OCTOBER 2022
TEXAS INSTRUMENTS Changes from Revision H (December 2010) to Revision	SN55LBC176, SN65LBC176, SN75LBC176 SLLS067I – AUGUST 1990 – REVISED OCTOBER 2022
INSTRUMENTS	SN55LBC176, SN65LBC176, SN75LBC176 SLLS0671 – AUGUST 1990 – REVISED OCTOBER 2022 I I (October 2022) Page al Information tables, Detailed Description section, Support section, and Mechanical, Packaging, and
Changes from Revision H (December 2010) to Revision Added Pin Configuration and Functions section, Therma Device Functional Modes, Device and Documentation S	SN55LBC176, SN65LBC176, SN75LBC176 SLLS067I – AUGUST 1990 – REVISED OCTOBER 2022 I I (October 2022) Page al Information tables, Detailed Description section, Support section, and Mechanical, Packaging, and 1
Changes from Revision H (December 2010) to Revision Added Pin Configuration and Functions section, Therma Device Functional Modes, Device and Documentation S Orderable Information section	SN55LBC176, SN65LBC176, SN75LBC176 SLLS067I – AUGUST 1990 – REVISED OCTOBER 2022 It (October 2022) Page al Information tables, Detailed Description section, Support section, and Mechanical, Packaging, and 1 SN75176A SLLS100C – JUNE 1984 – REVISED OCTOBER 2022
Changes from Revision H (December 2010) to Revision • Added Pin Configuration and Functions section, Therma Device Functional Modes, Device and Documentation S Orderable Information section TEXAS INSTRUMENTS Changes from Revision B (January 2015) to Revision C	SN55LBC176, SN65LBC176, SN75LBC176 SLLS067I – AUGUST 1990 – REVISED OCTOBER 2022 It (October 2022) Page It Information tables, Detailed Description section, Support section, and Mechanical, Packaging, and SN75176A SLLS100C – JUNE 1984 – REVISED OCTOBER 2022 (October 2022) Page
Changes from Revision H (December 2010) to Revision Added Pin Configuration and Functions section, Therma Device Functional Modes, Device and Documentation S Orderable Information section	SN55LBC176, SN65LBC176, SN75LBC176 SLLS067I – AUGUST 1990 – REVISED OCTOBER 2022 I I (October 2022) Page al Information tables, Detailed Description section, Support section, and Mechanical, Packaging, and SN75176A SLLS100C – JUNE 1984 – REVISED OCTOBER 2022 (October 2022) Page

Product Folder	Current Datasheet Number	New Datasheet Number	Link to full datasheet
SN75179B	SLLS003E	SLLS003F	http://www.ti.com/product/SN75179B
SN75ALS181	SLLS152D	SLLS152E	http://www.ti.com/product/SN75ALS181
SN65LBC180, SN55LBC180	SLLS174H	SLLS174I	http://www.ti.com/product/SN55LBC180
SN65LBC179	SLLS173F	SLLS173G	http://www.ti.com/product/SN75LBC179
SN65LBC176	SLLS067H	SLLS067I	http://www.ti.com/product/SN55LBC176
SN75176A	SLLS100B	SLLS100C	http://www.ti.com/product/SN75176A

Temp and Tube variants of the devices are included in EOL notice PDN# 20221031005.3

Qual details are provided in the Qual Data Section.

Reason for Change:

These changes are part of our multiyear plan to transition products from our 150-milimeter factories to newer, more efficient manufacturing processes and technologies, underscoring our commitment to product longevity and supply continuity.

Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):

None

Impact on Environmental Ratings

Checked boxes indicate the status of environmental ratings following implementation of this change. If below boxes are checked, there are no changes to the associated environmental ratings.

RoHS	REACH	Green Status	IEC 62474
⊠ No Change	⊠ No Change	⊠ No Change	⊠ No Change

Changes to product identification resulting from this PCN:

Fab Site Information:

Chip Site	Chip Site Origin Code (20L)	Chip Site Country Code (21L)	Chip Site City
DL-LIN	DLN	USA	Dallas
SH-BIP-1	SHE	USA	Sherman
RFAB	RFB	USA	Richardson

Die Rev:

Current	New		
Die Rev [2P]	Die Rev [2P]		
ABF	_		

Assembly Site Information:

Assembly Site	Assembly Site Origin (22L)	Assembly Country Code (23L)	Assembly City
FMX	MEX	MEX	Aguascalientes
CARZ	CSZ	CHN	Jiangsu
CRS	CRS	MYS	Jelapang, Ipoh
MLA	MLA	MYS	KUALA LUMPUR
CDAT	CDA	CHN	Chengdu

Sample product shipping label (not actual product label)

TEXAS
INSTRUMENTS
MADE IN: Malaysia
2DC: 20:

MSL 2 /260C/1 YEAR SEAL DT MSL 1 /235C/UNLIM 03/29/04

PT: 39 LBL: 5A (L)TO:1750



(1P) \$N74L\$07N\$R (Q) 2000 (D) 0336 (31T)LOT: 3959047MLA (4W) TKY(1T) 7523483812

(2P) REV: (V) 9993317 (20L) CSO: SHE (21L) CCO:USA (22L) ASO: MLA (23L) ACO: MYS

Product Affected:

Group 1 Device list (RFAB/Process migration & no construction differences)

SN75179BP	SN75179BPSR	SN75ALS181NSR	SN75ALS181NSRG4
SN75179BPE4			

Group 2 Device list (RFAB/Process migration & MLA as an additional Assembly site, no construction differences)

SN75176ADR	SN65LBC176DR	SN75176ADRE4	SN65LBC176DRG4
SN75179BDR	SN65LBC179DR	SN75179BDRG4	SN65LBC179DRG4

Group 3 Device list (RFAB/Process migration & CDAT as an additional Assembly site [CARZ])

SN65LBC180RSAR

Group 4 Device list (RFAB/Process migration & CDAT as an additional Assembly site [CRS])

SN55LBC180RSAR

For alternate parts with similar or improved performance, please visit the product page on $\overline{\text{TI.com}}$

Qualification Report Approve Date 10-October-2022

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	#	Test Name	Condition	Duration	Qual Device: SN65LBC176DR	Qual Device: SN65LBC179DR	Qual Device: SN55LBC180RSAR	QBS Reference: ICAN1044VDRQ1	QBS Reference: ICAN1044VDRQ1	QBS Reference: IPS51217DSCR	QBS Reference: TLIN10283DRBRQ1	QBS Reference: TLIN10285DRBRQ1	QBS Reference: ICAN1043DQ1	QBS Reference: IPS2590RSAR
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-					3/231/0			-	-
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	-	1/77/0	2/154/0	-	1/77/0	2/154/0	-	-
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-			-	-	-			3/231/0	-
UHAST	А3	Autoclave	121C/15psig	96 Hours	-	-	-		-	3/231/0	-		-	1/77/0
UHAST	А3	Autoclave	121C/15psig	96 Hours	-			1/77/0	2/154/0	-	1/77/0	2/154/0	3/231/0	-
тс	Α4	Temperature Cycle	-55C/150C	1000 Cycles	-	-	-		-	-	-	1/77/0	-	-
тс	Α4	Temperature Cycle	-65C/150C	500 Cycles	-	-	-		-	3/231/0	-		-	1/77/0
тс	Α4	Temperature Cycle	-65C/150C	500 Cycles	-	-	-	1/77/0	2/154/0	-	1/77/0	1/77/0	3/231/0	-
HTSL	A6	High Temperature Storage Life	150C	1000 Hours	-					-	1/77/0	2/154/0	-	
HTSL	A6	High Temperature Storage Life	170C	420 Hours	-	-	-		-	3/231/0	-	-	-	-
HTSL	A6	High Temperature Storage Life	175C	500 Hours	-			1/45/0	2/90/0	-	-	-	-	-
HTSL	A6	High Temperature Storage Life	175C	500 Hours	-		-	-		-	-	-	1/45/0	-
HTOL	B1	Life Test	125C	1000 Hours	-			1/77/0	2/154/0				1/77/0	-
HTOL	81	Life Test	135C	635 Hours	-		-		-	3/231/0			-	-
HTOL	81	Life Test	150C	1000 Hours	-			-	-	-	1/77/0	2/154/0	-	-
WBS	C1	Ball Shear	76 balls, 3 units min	Wires	1/76/0	1/76/0	1/76/0	-	-	-	-		-	1/3/0
SD	C3	PB Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-		-	-	1/15/0		-	1/15/0	1/15/0	-

- QBS: Qual By Similarity
- Qual Device SN65LBC176DR is qualified at MSL1 260C
- Qual Device SN65LBC179DR is qualified at MSL1 260C
- Qual Device SN55LBC180RSAR is qualified at MSL2 260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

Qualification Report Approve Date 10-October-2022

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	#	Test Name	Condition	Duration	Qual Device: SN75176ADR	Qual Device: SN75179BDR	Qual Device: SN75179BP	Qual Device: SN75179BPSR	QBS Reference: TCAN1044VDRQ1	QBS Reference: TCAN1044VDRQ1	QBS Reference: TL092CPS	QBS Reference: TPS51217DSCR	QBS Reference: SE555P	QBS Reference: SN104571P	QBS Reference: TPIC6A596NE
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	-	-	-	-	-	3/231/0			-
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	-	-	1/77/0	2/154/0	-	-	-	-	-
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	-	-	-	-	-	-	-	-	3/231/0
UHAST	А3	Autoclave	121C/15psig	96 Hours	-	-	-	-	-	-	3/230/0	3/231/0	-	-	-
UHAST	А3	Autoclave	121C/15psig	96 Hours	-	-	-	-	1/77/0	2/154/0	-	-	-	-	-
UHAST	А3	Autoclave	121C/15psig	96 Hours	-	-	-	-	-	-	-	-	3/231/0	3/231/0	3/231/0
тс	A4	Temperature Cycle	-65C/150C	500 Cycles	-		-	-	-	-	3/231/0	3/231/0	-	-	-
тс	A4	Temperature Cycle	-65C/150C	500 Cycles	-		-	-	1/77/0	2/154/0	-	-	-	-	-
тс	A4	Temperature Cycle	-65C/150C	500 Cycles	-	-	-	-	-	-	-	-	3/231/0	3/231/0	3/231/0
HTSL	A6	High Temperature Storage Life	170C	420 Hours	-	-	-	-	-	-	3/231/0	3/231/0	-	-	-
HTSL	A6	High Temperature Storage Life	175C	500 Hours	-	-	-	-	1/45/0	2/90/0	-	-	-	-	-
HTSL	A6	High Temperature Storage Life	175C	500 Hours	-	-	-	-	-	-	-	-	3/135/0	3/135/0	3/135/0
HTOL	B1	Life Test	125C	1000 Hours	-	-	-	-	1/77/0	2/154/0		-	-	-	3/231/0
HTOL	B1	Life Test	135C	635 Hours	-	-	-	-	-	-	-	3/231/0	-	-	-
WBS	C1	Ball Shear	76 balls, 3 units min	Wires	1/76/0	1/76/0	1/76/0	1/76/0	-	-	-	-	-	-	-
WBP	C2	Bond Pull	76 Wires, 3 units min	Wires	1/76/0	1/76/0	1/76/0	1/76/0	-	-	-	-	-	-	-
SD	СЗ	PB Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)		-		-	-	-	1/15/0		-	3/45/0	3/45/0	3/45/0
SD	СЗ	PB Solderability	Precondition w.155C Steam Age (8 hrs +/- 15 minutes)		-	-	-	-	-	1/15/0			3/45/0	3/45/0	3/45/0
SD	C3	PB-Free Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	-	-	-	1/15/0			3/45/0	3/45/0	3/45/0
SD	C3	PB-Free Solderability	Precondition w.155C Steam Age (8 hrs +/- 15 minutes)	-	-	-	-	-	-	1/15/0			3/45/0	3/45/0	3/45/0
PD	C4	Physical Dimensions	Cpk>1.67	-	-	-	-	-	1/10/0	2/20/0	-	-	3/30/0	3/30/0	3/30/0
ESD	E2	ESD CDM	-	1500 Volts	-		-	-	-	-	-	3/9/0	-	-	-
ESD	E2	ESD CDM	-	250 Volts	1/3/0	1/3/0	1/3/0	1/3/0	-	-	-	-		-	-
ESD	E2	ESD HBM	-	1000 Volts	1/3/0	1/3/0	-	-	-	-	-	-	-	-	-
ESD	E2	ESD HBM	-	15000 Volts	1/3/0	-	-	-	-	-	-	-	-	-	-
ESD	E2	ESD HBM	-	2000 Volts	-		-	-			-	3/9/0	-	-	-
LU	E4	Latch-Up	Per JESD78	-	1/3/0	1/3/0		-	-	-		3/18/0	-	-	-
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	1/30/0	-	-	-	-	-	3/60/0	-	-	-
CHAR	E5	Electrical Distributions	Cpk>1.67 Room, hot, and cold	-	-	-	-	-	2/60/0	-	-	-	3/90/0	-	3/90/0
FTY	E6	Final Test Yield	-	-	1/1/0	1/1/0	1/1/0	1/1/0	-	-		-	-	-	-

- QBS: Qual By Similarity
 Qual Device SN75176ADR is qualified at MSL1 260C
 Qual Device SN751798DR is qualified at MSL1 260C
 Qual Device SN751798DR is qualified at MSL1 260C
 Qual Device SN751798PS is qualified at NDC CLASSIFIED NOT CLASSIFIED
 Qual Device SN751798PSR is qualified at MSL1 260C

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Blased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
 The following are equivalent HTOL options based on an activation energy of 0.7ev : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 175C/240 Hours
 The following are equivalent HTSL options based on an activation energy of 0.7ev : 150C/1k Hours, and 170C/420 Hours
 The following are equivalent Temp Cycle options per JESD47:-55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

Green/Pb-free Status:

Qualification Report Approve Date 10-October-2022

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	#	Test Name	Condition Duration		Qual Device: SN75ALS181NSR	QBS Reference: <u>TL092CPS</u>	QBS Reference: SN75ALS1177NS	QBS Reference: TPS51217DSCR
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	-	3/231/0
UHAST	A3	Autoclave	121C/15psig	96 Hours	-	3/230/0	3/231/0	3/231/0
HTSL	A6	High Temperature Storage Life	170C	420 Hours	-	3/231/0	-	3/231/0
HTOL	B1	Life Test	135C	635 Hours	Hours -		-	3/231/0
WBS	C1	Ball Shear	76 balls, 3 units min	Wires	1/76/0	-	-	-
WBP	C2	Bond Pull	76 Wires, 3 units min	Wires	1/76/0	-	-	-
ESD	E2	ESD CDM	-	1500 Volts	-	-	-	3/9/0
ESD	E2	ESD CDM	-	250 Volts	1/3/0	-	-	-
ESD	E2	ESD HBM	-	1000 Volts	1/3/0	-	-	-
ESD	E2	ESD HBM	-	2000 Volts	-	-	-	3/9/0
LU	E4	Latch-Up	Per JESD78	-	1/3/0	-	-	3/18/0
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	-	-	3/60/0
FTY	E6	Final Test Yield	-	-	1/1/0	-	-	-

- · QBS: Qual By Similarity
- Qual Device SN75ALS181NSR is qualified at MSL1 260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

For questions regarding this notice, e-mails can be sent to the contact below or your local Field Sales Representative.

Location	E-Mail					
WW Change Management Team	PCN www admin_team@list.ti.com					

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disdaims responsibility for,

and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.