







Product Outline:

This is the small TOP LED with reflector type with single color led. This special package is ideal for customer's application in traffic signal and sign boards. With special binning technology, Quelighting is able to provide special binning for customer's needs

Features:

- White color LED
- High brightness output @ 140mA,
- High driving current to 250mA.
- Package Dimension = 3.4mmX3.3mmX1.9mm
- MSL level 2
- RoHS compliant
- Custom Bin available upon special request
- View angel >110°
- AEC-Q101

Application:

- Architecture Lighting
- Sign board backlighting
- Emergency vehicle lighting
- Traffic signal lighting
- Automotive lighting

Compliance and Certification:










QLSP05WCG PLCC 6 Series


Mechanical Property: (Dimension)








0 8010 01



* All dimensions are in millimeters, * Tolerances are ± 0.10mm.

Recommended Solder footprint:



* All dimensions are in millimeters.

* The LEDs is designed to be reflow soldered on to a PCB. IF dip soldered that QL cannot guarantee its reliability. * Reflow soldering must not be performed more than twice.



Characteristics

Absolute	Maximum	Ratings

Absolute Maximum I	(Ta=25℃)		
Parameter	Symbol	Rating	Unit
DC Forward Current	lf	250	mA
Power Dissipation	Pd	0.82	W
Pulse Forward Current	lfp	400	mA
Storage Temperature	Tstg	-40 ~ 105	°C
Operation Temperature	Topr	-40 ~ 105	°C
Soldering Temperature	Tsol	260 < 10 sec	°C
ESD (HBM)	ESD(HBM)	8000	V

(1) Proper current rating must be observed to maintain junction temperature below maximum at all time(2) IFP Condition: Duty 1/10, Pulse within 10msec

Electrical / Optic	(Ta=25 oC)					
Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Forward Voltage	Vf	140mA	2.8		3.4	V
View Angle	θ	140MA		120		deg

(1) Tolerance of measurement: VF=+/- 0.1V

Specification


Product	Color	Vf(V) IF=140mA	Color Temperature		s intensity mA (Im)
		IF=140IIIA	(K)	Min.	Тур.
QLSP05WCG	White	3.2	5000K~7000K	45	56

*Tolerance = +/- 10%



Groups

Dominate Wavelength (nm) Bin:



Tolerance of measurements of the Chromaticity Coordinate is ± 0.005 .

Forward Voltage (V_F) Bin:

v	Condition			
Color	Code name	Low	High	unit
	А	2.8	3.0	
White	В	3.0	3.2	V
	С	3.2	3.4	

The forward voltage tolerance is $\pm 0.1V$

Luminous Intensity Bin:

Intensity Rank (Im) @ 140mA					
Code name	Min.	Max.	Units		
VS	45	50			
VT	50	55	Im		
VU	55	60	lm		
VV	60	65			


Luminous intensity tolerance is $\pm 8\%$








(1) Color Spectrum




(2). Typical Representative Spatial Radiation Pattern




(3). Forward Current Characteristics







(4). Forward Current vs Forward Voltage





Reliability test:

No	Item	Condition	Time/Cycle	Sample size
1	Steady State Operating Life of Room Temperature	25°C Operating	1000 Hrs	20 pcs
2	Steady State Operating Life of Low Temperature -40 $^\circ\!\!\mathbb{C}$	-40°C Operating	1000 Hrs	20 pcs
3	Steady State Operating Life of Low Temperature $60^\circ\!\mathrm{C}$	60℃ Operating	1000 Hrs	20 pcs
4	Steady State Operating Life of Low Temperature 85 $^\circ\!\mathrm{C}$	85°C Operating	1000 Hrs	20 pcs
5	Low temperature storage -40 $^\circ\!C$	-40°C Storage	1000 Hrs	20 pcs
6	High temperature storage $100^\circ C$	100°C Storage	1000 Hrs	20 pcs
7	Steady State Operating Life of High Humidity Heat $60^\circ\!\!\!\!\!C90\%$	60°C/90% Operating	1000 Hrs	20 pcs
8	Steady State Pulse Operating Life Condition	25°C10Hz duty=1/10 Operating	200 Cycle	20 pcs
9	Resistance to soldering heat on PCB (JEDEC MSL3)	pre-store@60℃, 60%RH for 52hrs Tsld max.=260 10sec	3 Times	20 pcs
10	Heat Cycle Test (JEDEC MRC)	25℃~65℃~-10℃, 90%RH, 24hr/1cycle	10 Cycle	20 pcs
11	Thermal shock	-40℃/ 20minr~ 5minr~100℃ /20min	300 Cycle	20 pcs

■ Judgment Criteria:

ltem	Symbol	Test Condition	Judgment Criteria
Forward Voltage	Vf	140 mA	∆Vf< 10%
Luminous Flux	lv	140 mA	∆Iv< 30%








■ Solder Profile:

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):




Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Temperature Min(T _{smin})	100°C	150 ℃
Temperature Max(T _{smax})	150 ℃	200 ℃
Time(t _a) from (T _{smin} to T _{smax})	60-120 seconds	60-120 seconds
Ramp-up rate(T_L to T_P)	3℃/second max.	3℃/second max.
Liquidous Temperature(T _L)	183℃	217 ℃
Time(t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature(T _P)	235℃	260℃
Time within 5℃ of Actual Peak temperature (t _p)	20seconds*	30 seconds*
Ramp-down rate(T_P to T_L)	6℃/second max.	6℃/second max.
Time 25 $^\circ\!\!\mathbb{C}$ to peak temperature	6 minutes max.	8 minutes max.


Tolerance for peak profile temperature (T_P) is defined as a supplier minimum and a user maximum.



QLSP05WCG PLCC 6 Series

Taping & Packing:






UNIT:mm

symbol	Ao	Bo	Ko	Po	P1	P2	Т
spec	3.70±0.10	3.70±0.10	2.27±0.10	4.00±0.10	8.00±0.10	2.00±0.05	0.30±0.10
symbol	E	F	Do	D1	W	10Po	
spec	1.75±0.10	5.50±0.05	1.55±0.05	1.50±0.10	12.0±0.30	40.0±0.20	

(Unit : mm)











QLSP05WCG PLCC 6 Series

Labeling	
Quantity: XXXX	QueLighting
Quelighting P/N: XXXXXX	
Lot number: XXXXX	
lv Bin: XX Color Bin: XX Vf Bin: XX	Date Code: XXXX

Ordering Information:

Part #	Multiple Quantities	Quantity per Reel
QLSP05WCG		500,1000,2000 pcs





Revision History:

Revision Date:	Changes:	Version #:
07-04-2020	Initial release	1.0

