

Dwg. Number	Customer P/N	Times P/N	Length(L) in 'mm'
IE-00410-01	-	MGS200-SMSM-0.5M	500+10/-0
IE-00410-02	-	MGS200-SMSM-1.0M	1000+20 /-0
IE-00410-03	-	MGS200-SMSM-2.0M	2000+40/-0
IE-00410-04	-	MGS200-SMSM-2.5M	2500+50/-0

## 1.0 Scope

This drawing documents the construction and performance of Maxgain 200 cable assemblies manufactured by Times Microwave systems.

## 2.0 Cable Information

- 2.1 Cable to be MAXGAIN 200
- 2.2 Jacket color to be Blue
- 2.3 Jacket material to be FEP
- 2.4 Nominal cable impedance to be 50 ohms
- 2.5 Cable diameter to be 5.10mm [0.201"].

# 3.0 Connector Information

3.1 Forward Connector

Type SMA (M) Straight Connector (SP018) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated

3.2 After Connector Type SMA (M) Straight Connector (SP018)

Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated

These drawings and					TIMES MICROWAVE SYST				
	Drawn	SVP	10/20/22			www.timesmicrowave.com			
	Checked			MG200 CABLE ASSEMBLY (Space Assemblies)					
which is the property of	Approved					(Spa	(Space Assemblies)		
Times Microwave	, pproved			Size	CAGE CODE		Drawing No.:		
Systems.				A	68999		IE-00410-XX		
				Scale:	NA	Rev.	(A)	Sheet: 1 of 3	

THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE SAME AS SHEET 1								
REV	DESCRIPTION	DATE	BY					
А	INITIAL RELEASE	10/20/22	SVP					

# 4.0 Electrical Performance

- 4.1 Frequency range: DC 22GHz
- 4.2 Insertion loss & VSWR: As per below table,

Dwg. Number	Max. Insertion Loss in dB	Max. VSWR		
Dwg. Number	@ 22GHz	@ 22GHz		
IE-00410-01	1.03	1.35		
IE-00410-02	1.76	1.35		
IE-00410-03	3.21	1.35		
IE-00410-04	3.94	1.35		

#### 5.0 Mechanical Performance

- 5.1 Overall Length to be specified length.
- 5.2 Minimum Bend radius is 31.8mm [1.25"].

## 6.0 Environmental Performance

- 6.1 Installation Temperature Range (-55°C to +150°C)
- 6.2 Storage Temperature Range (-55°C to +150°C)
- 6.3 Operating Temperature Range (-55°C to +150°C)

#### 7.0 Marking

- 7.1 Markers are to be black text on White Color Marker Sleeve.
- 7.2 Marker Configuration to be:

Dwg. Number	Marking details	Marker Numbers	Marker Position		
IE-00410-01	Times Microwave Systems MGS200-SMSM-0.5M \$\$\$\$\$	1	In Center of the Cable Assy.		
IE-00410-02	Times Microwave Systems MGS200-SMSM-1.0M \$\$\$\$\$	1	In Center of the Cable Assy.		
IE-00410-03	Times Microwave Systems MGS200-SMSM-2.0M \$\$\$\$\$	1 & 2	At Both Ends		

Unless otherwise spec- ified, dimensions are in MM. Tolerances are applicable when spec- ified. These drawings and specifications contain proprietary information					TIMES MICROWAVE SYSTEMS				
	Drawn	SVP	10/20/22			www.timesmicrowave.com			
	Checked			MG200 CABLE ASSEMBLY					
which is the property of	Approved				(Space Assemblies)				
Times Microwave	Approveu			Size	CAGE (	CODE	Drawing No.:		
Systems.				A	68999		IE-00410-XX		
				Scale:	NA	Rev. (	(A)	Sheet: 2 of 3	

	THE RE	VISION STA	TUS OF	ALL SHEET	S OF TH	IIS DRAW	ING IS TH	HE SAME A	S SHEET 1	
REV		DESCRIPTION							TE	BY
A IN	NITIAL RE	LEASE						10/2	0/22	SVP
		IE-00410-0 \$\$\$\$\$ = 5-dig Register to be	it Serial		MSM-2.5 \$\$ his spec	ific configu	1 & 2 iration.	At I	Both Ends	]
<b>8.0 NOTES</b> 8.1 8.2 8.3		All Dimensions are in MM. Assemblies built in Class 100,000 cla Low outgassing materials per ASTM Unless Otherwise Specified: Toleran Linear Dimension Toleran								
		<500 n	nm	±10 r	mm					
	-	500-2000	) mm	±15 r	nm	-				
		>2000	mm	±20 r	nm					
Unless otherw ified, dimensio MM. Tolerand	ons are in ces are						TIMES	MICROW	VAVE SYS	TEMS
applicable wh ified.	-	Drawn	SVP	10/20/22			W	ww.timesmi	crowave.con	n
These drawing specifications proprietary inf	contain	Checked				N		CABLE AS	SEMBLY blies)	
which is the propert Times Microwav Systems.	Owave	Approved	red		Size A	CAGE 689	CODE	Drawing	Drawing No.: IE-00410-XX	
					Scale:	NA	Rev.	(A)	Sheet:	3 of 3