

Dwg. Number	Customer P/N	Times P/N	Length(L) in 'mm'
IE-00406-01	-	MGS130-2.4M2.4M-0.3M	300+6/-0
IE-00406-02	-	MGS130-2.4M2.4M-0.5M	500+10 /-0
IE-00406-03	-	MGS130-2.4M2.4M-1.0M	1000+20/-0
IE-00406-04	-	MGS130-2.4M2.4M-1.5M	1500+30/-0

1.0 Scope

This drawing documents the construction and performance of Maxgain 130 cable assemblies manufactured by Times Microwave systems.

2.0 Cable Information

- 2.1 Cable to be MAXGAIN 130
- 2.2 Jacket color to be Blue
- 2.3 Jacket material to be FEP
- 2.4 Nominal cable impedance to be 50 ohms
- 2.5 Cable diameter to be 3.30mm [0.130"] (Nominal).

3.0 Connector Information

- 3.1 Forward Connector Type 2.4mm (M) Straight Connector (SP014) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated
- 3.2 After Connector Type 2.4mm (M) Straight Connector (SP014) Connector Body – Stainless Steel, Passivated Center Contact – Beryllium Copper, Gold Plated

These drawings and						TIMES MICROWAVE SYSTEMS		
	Drawn	SVP	10/19/22			www.timesmicrowave.com		
	Checked			MG130 CABLE ASSEMBLY (Space Assemblies)				
which is the property of Times Microwave	Approved							,
Systems.				Size A			Drawing No.: IE-00406-XX	
				Scale:	NA	Rev.	(A)	Sheet: 1 of 3

	THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE SAME AS SHEET 1							
REV	DESCRIPTION	DATE	BY					
А	INITIAL RELEASE	10/19/22	SVP					

4.0 Electrical Performance

4.1 Frequency range: DC – 50GHz

4.2 Insertion loss & VSWR: As per below table,

Dwg. Number	Max. Insertion Loss in dB	Max. VSWR			
Dwg. Number	@ 50GHz	@ 50GHz			
IE-00406-01	1.87	1.40			
IE-00406-02	2.64	1.40			
IE-00406-03	4.62	1.40			
IE-00406-04	6.60	1.40			

5.0 Mechanical Performance

- 5.1 Overall Length to be specified length.
- 5.2 Minimum Bend radius is 16mm [0.625"].

6.0 Environmental Performance

- 6.1 Installation Temperature Range (-55°C to +150°C)
- 6.2 Storage Temperature Range (-55°C to +150°C)
- 6.3 Operating Temperature Range (-55°C to +150°C)

7.0 Marking

- 7.1 Markers are to be black text on White Color Marker Sleeve.
- 7.2 Marker Configuration to be:

Dwg. Number	Marking details	Marker Numbers	Marker Position
IE-00406-01	Times Microwave Systems MGS130-2.4M2.4M-0.3M \$\$\$\$\$	1	In Center of the Cable Assy.
IE-00406-02	Times Microwave Systems MGS130-2.4M2.4M-0.5M \$\$\$\$\$	1	In Center of the Cable Assy.
IE-00406-03	Times Microwave Systems MGS130-2.4M2.4M-1.0M \$\$\$\$\$	1	In Center of the Cable Assy.

Unless otherwise spec- ified, dimensions are in MM. Tolerances are applicable when spec- ified. These drawings and specifications contain proprietary information						TIMES MICROWAVE SYSTEMS		
	Drawn	SVP	10/19/22			www.timesmicrowave.com		
	Checked			MG130 CABLE ASSEMBLY (Space Assemblies)				
which is the property of	Approved							blies)
Times Microwave	Approved			Size	Size CAGE CODE 68999		Drawing No.: IE-00406-XX	
Systems.				A				
				Scale:			(A)	Sheet: 2 of 3

	THE RE	VISION STA	TUS OF	ALL SHEET	S OF TH	IIS DRAWI	NG IS TH	HE SAME A	S SHEET 1	
REV		DESCRIPTION							TE	BY
A II	NITIAL RE	ELEASE							9/22	SVP
		IE-00406-0 \$\$\$\$\$ = 5-dig Register to be	it Serial		M2.4M-1 <u>\$\$</u> his spec	.5M	1 & 2 ration.	At E	Both Ends]
8.0	8.1 / 8.2 / 8.3	All Dimension Assemblies bu Low outgassir Unless Other	s are in uilt in Cla ng mater wise Spe	MM. ass 100,000 rials per AST ecified: Tolera	clean roo M E595. ance will	om. be,	7			
	-	Linear Dimension Tolerance								
		<5) mm	_					
	-	500-		5 mm	_					
		>2000 mm ±20 mm								
Jnless otherv fied, dimension MM. Tolerand	ons are in ces are									TEMS
applicable wh fied.	en spec-	Drawn	SVP 10/19/22		wwv			ww.timesmi	w.timesmicrowave.com	
These drawin specifications proprietary inf	contain	Checked				M		ABLE AS	SEMBLY	
which is the propert Times Microwave Systems.	roperty of rowave	Approved			Size CAGE CODE A 68999			Drawing	•	(
					Scale:	NA	Rev. ((A)	Sheet:	3 of 3