



QLUV07N3GEU 3535 50mW UVC LED





Product Outline:

The high output type 3535 LEDs, UVC LED series are designed for high current operation and high power output applications. Quelighting UV LED is ideal UV light source for water disinfection.

Features:

- UVC LED
- Quartz glass lens
- Max. current = 500mA, up to 3.5W
- Package Dimension = 3.5mmX3.5mmX1.5mm
- Ceramic subtract
- MSL 3 qualified according to J-STD 020
- Low thermal resistance
- View angle = 120 degree
- RoHS compliant
- Custom Bin available upon special request

Application:

- Water disinfection
- Air purifiers
- Disinfection
- Phototherapy
- Bio-Analysis/Detection Features

Compliance and Certification:










Mechanical Property: 120 Degree Field Angle




Note:

- 1. All dimension in millimeters
- 2. tolerance is ±0.2mm



Recommended Solder footprint:



Note:

- 1. All dimension in millimeters
- 2. The drawing without tolerances is for reference only
- 3. Suggest stencil T=0.12 mm

Electrical / Optical Characteristic

(T=25 °C)

Product	View angle	I _F (mA)		(V)	Wavelength	Radiant Po	wer(mW)
oudet		3, (333.3)	Тур.	max	(nm)	min	typ.
QLUV07N3GEU	130	500	6.5	8	270-280	50	60

- (1) The Forward Voltage tolerance is ±0.1V
- (2) The Peak wavelength tolerance is ±2
- (3) The Radiant power is ± 7%

Absolute Maximum Rating

(T=25 °C)

Part #	P _d (mW)	I _F (mA)	I _{FP} (mA)*	V _R (V)	T _{OP} (°C)	T _{ST} (°C)	Tj (°C)**	T _{SOL} (°C)**	R _{th(J-S)} (C/W)***
QLUV07N3GEU	3.5	500	500	-5	-20 – 60	-20 - 85	85	240	8

^{*}Duty 1/10 @ 10Khz

^{**} Junction Temperature

^{***} IR Reflow for no more than 10 sec @ 260 °C

^{****} Thermal resistance is calculated from junction to solder




Peak Wavelength Binning

Wavelength Rank @ 100mA						
Code name	Low	High	Units			
U265	265	270				
U270	270	275	nm			
U275	275	280				


Forward Voltage (V_F) Bin:

VF Rank @ 100mA						
Code name	Min.	Max.	Units			
А	5.0	5.5				
В	5.5	6.0				
С	6.0	6.5	\/			
D	6.5	7.0	V			
E	7.0	7.5				
F	7.5	8.0				

Characteristic Curves




Forward Voltage vs. Forward Current




Forward current vs. Relative luminous intensity







Relative Luminous Intensity vs Ambient Temperature



Solder Temperature (Slug) vs. Maximum Forward Current



Spectrum Distribution



Typical Representative Spatial Radiation Pattern



■ Reliability test:

No	Item	Condition	Time/Cycle	Sample size
1	Steady State Operating Life of Room Temperature	25°C Operating	500 Hrs	10 pcs
2	Steady State Operating Life of Low Temperature -40°C	-40°C Operating	500 Hrs	10 pcs
3	Steady State Operating Life of Low Temperature 60°C	60°C Operating	500 Hrs	10 pcs
4	Steady State Operating Life of Low Temperature $85^{\circ}\!\mathbb{C}$	65°C Operating	500 Hrs	10 pcs
5	Low temperature storage -40°C	-40°C Storage	500 Hrs	10 pcs
6	High temperature storage 100°C	100°C Storage	500 Hrs	10 pcs
7	Steady State Operating Life of High Humidity Heat 60°C 90%	60°C/90% Operating	500 Hrs	10 pcs
8	Steady State Pulse Operating Life Condition	25°C 10Hz duty=1/10 Operating	100 Cycle	10 pcs
9	Resistance to soldering heat on PCB (JEDEC MSL3)	pre-store@60℃, 60%RH for 52hrs Tsld max.=260 10sec	3 Times	10 pcs
10	Heat Cycle Test (JEDEC MRC)	25℃~65℃~-10℃, 90%RH, 24hr/1cycle	10 Cycle	10 pcs
11	Thermal shock	-40 $^{\circ}$ C/ 20minr~ 5minr~100 $^{\circ}$ C /20min	100 Cycle	10 pcs

■ Judgment Criteria:


Item	Symbol	Test Condition	Judgment Criteria
Forward Voltage	Vf	500 mA	△Vf< 10%
Luminous Flux	lv	500 mA	∆lv< 30%





Solder Profile:

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):




Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Temperature Min(T _{smin})	100℃	150℃
Temperature Max(T _{smax})	150℃	200℃
Time(t _a) from (T _{smin} to T _{smax})	60-120 seconds	60-120 seconds
Ramp-up rate(T _L to T _P)	3°C/second max.	3°C/second max.
Liquidous Temperature(T _L)	183℃	217℃
Time(t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature(T _P)	235℃	260℃
Time within 5°C of Actual Peak	20seconds*	30 seconds*
Ramp-down rate(T_P to T_L)	6°C/second max.	6°C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.

^{*} Tolerance for peak profile temperature (T_P) is defined as a supplier minimum and a user maximum.





Taping & Packing:




Notes:

- 1. Drawing not to scale.
- 2. All dimensions are in millimeters.
- 3. Unless otherwise indicated, tolerances are $\pm\,0.10\mbox{mm}.$







Eye Safety Guidelines During operation

The LED emits high intensity ultraviolet (UV) light, which is harmful to skin and eyes. UV light is hazardous to skin and may cause cancer.

- 1) Avoid looking directly at the UV light: Wear protective glasses/goggle with ANSI Z87 rated.
- 2) Wear facial shield / Lab Coat with long sleeve / Gloves to cover skin may exposed to UVC LEDs.

QueLighting



3) Attach warning labels on products/systems that is composed with UV LEDs.

Warning label:



Eye and skin hazard—avoid exposure to eyes/skin Do not look directly at light—use eye protection Use warning labels on systems containing UV LEDs

Labeling

	 1/1/		

Quantity: XXXX

Quelighting P/N: XXXXXX

Lot number: XXXXX

Iv Bin: XX Color Bin: XX Vf Bin: XX Date Code: XXXX

Ordering Information:

Part #	Multiple Quantities	Quantity per Reel
QLUV07N3GEU		100, 250, 500





Revision History:

Revision Date:	Changes:	Version #:
12-10-2021	Initial release	1.0

