

## 9510 Remote Airborne Particle Counter

1.0 CFM (28.3 LPM)





The 9510 particle counters provide a range of particle size measurement from 0.5 to 10.0  $\mu$ m at a flow rate of 1.0 CFM (28.3 LPM). These sensors allow for efficient particle counting with specifications that exceed the ISO 21501-4 and JIS B9921 calibration standards.


These sensors have 6 user-selectable particle size channels (up to 30 channels optional) and are equipped with an integral critical orifice and flow sensor to provide a stable flow rate from an external vacuum source. Integration into a building automation or facility monitoring system is easy via isolated RS-485 Modbus communication.

## 9510: Features and Benefits

- Measures 0.5 µm to 10 µm
- 1.0 CFM (28.3 LPM) flow rate
- Long life laser diode technology
- · Measures up to 30 channels of simultaneous data
- Particle concentrations up to 1,500,000 Particles/ft<sup>3</sup> @ 10% coincidence loss
- Internal critical orifice
- User-selectable channel sizes
- Stores up to 65,000 sample records for on-board data redundancy
- · (Optional) temperature and relative humidity probe available
- Connect using Modbus RTU/ASCII over isolated RS-485
- Complies with ISO 21501-4 and JIS B9921 standards
- · Easy to clean and wipe down with minimal particle traps
- Versatile mounting options
- Alarm light
- LED Indicators
- · Seamless integration into a facility monitoring system
- Lightweight stainless steel enclosure
- 2 year warranty. Extended warranties available.









## **Specifications**

| Model                  | 9510   |
|------------------------|--|
| Size Range             | 0.5 μm to 10 μm  |
| Size Channels          | Factory calibrated at 0.5, 1.0, 2.5, 5.0, 10.0 µm  |
| Number of Channels     | 6 channels (up to 30 optional)   |
| Counting Efficiency    | 50% @ 0.5μm; 100% for particles > 0.75 μm per JIS  |
| Flow Rate              | 1.0 CFM (28.3 LPM)   |
| Concentration Limits   | 1,500,000 particles/ft <sup>3</sup> @ 10% coincidence (per ISO 21501-4), 3,000,000 particles/ft <sup>3</sup> @ 10% coincidence (as tested and validated <sup>1</sup> ) |
| Light Source           | Long life laser diode  |
| Zero Count             | < 1 count / 5 minutes (< 1 particles / 15ft <sup>3</sup> )   |
| Alarms                 | Channel alarms on Raw counts, concentrations or mass (alarms on environmental sensors optional)  |
| Calibration            | NIST traceable   |
| Vacuum Requirements    | External vacuum > 15" (38.1cm) of Hg   |
| Airflow                | Internally monitored   |
| Configuration/Download | USB mini-B   |
| Alarm                  | Alarm LED ring   |
| Communication Modes    | MODBUS™ RTU or ASCII outputs (over isolated RS-485)  |
| Standards              | ISO 21501-4 and JIS B9921  |
| Instrument Calibration | Recommended minimum once per year  |
| External Surface       | Stainless steel  |
| Dimensions (L x W x H) | 3.59" x 1.83" x 5.01" (9.1 cm x 4.6 cm x 12.7 cm) including probes and connectors  |
| Weight                 | 1.08 lb. (494 grams)   |
| Accessories            | Wiring Connector, operating manual on USB flash drive  |
| Optional Accessories   | Power Supply, Remote Mounting Bracket, Stainless Steel Barbed Isoprobe (1.0 CFM/28.3 LPM), Purge<br>Filter Assembly, and Sample & Vacuum Tubing                        |
| Buffer Memory          | 65,000 sample records (rotating buffer) including particle count data and environmental data   |
| Sample Time            | 1 second to 99 hours   |
| Power                  | 9 - 24 VDC (< 1.5 watts)   |
| Operating Conditions   | 41° to 104°F (5° to 40°C) / 20% to 95% non-condensing  |
| Storage Conditions     | 32° to 122°F (0° to 50°C) / Up to 98% non-condensing   |
| Warranty               | 2 year limited warranty. Extended warranties available.  |
| -                      |  |

1- Validated by independent analysis see paper available at www.particlesplus.com/aac2022\_paper

PAT. https://particlepatents.com/ Additional Patents Pending. Particles Plus, Inc. reserves the right to change specifications without notice. Contact hello@particlesplus.com or your local distributor for more details. Particles Plus and the Particles Plus logo are trademarks of Particles Plus, Inc. ©2022 Particles Plus, Inc. All rights reserved.

PLUS\*

