

Inductors for power circuits Thin-film metal magnetic material **PLE** series









PLEA67B type













FEATURES

- Thin-film power inductor based on the thin-film processing techniques and metallic magnetic materials.
- Oue to the high magnetic permeability magnetic material, it has both high inductance of 2.2uH and low DC resistance in spite of its small size of 1006 (L1.0xW0.6xT0.7mm).
- The low-loss magnetic material makes it possible to achieve low AC loss and provide a highly efficient power supply circuit in solutions that emphasize AC loss.

APPLICATION

- Wearable product (wireless earphones and smart watch), small power supply module and low power consumption communication module of Bluetooth Low Energy
- O Application guides: TWS (True Wireless Stereo)

■ PART NUMBER CONSTRUCTION

PLE	A67	BBA -	2R2	М	- 1P	Т	00
Series name	L×W×H dimensions 1.0x0.6x0.7 mm	Characteristic type	Inductance (µH)	Inductance tolerance	Number of lines	Packaging style	Internal code

CHARACTERISTICS SPECIFICATION TABLE

L		L measuring frequency	DC resistance		Rated current*			Part No.	
					Isat		Itemp		
(µH)	Tolerance	(MHz)	(m Ω)max.	(m Ω)typ.	(A)max.	(A)typ.	(A)max.	(A)typ.	
1.0	±20%	1.0	265	220	8.0	1.0	1.0	1.2	PLEA67BBA1R0M-1PT00
2.2	±20%	1.0	620	510	0.5	0.6	0.5	0.8	PLEA67BBA2R2M-1PT00
4.7	±20%	1.0	1080	900	0.3	0.35	0.4	0.6	PLEA67BCA4R7M-1PT00

^{*} Rated current: smaller value of either Isat or Itemp.

Isat: When based on the inductance change rate (30% below the initial L value)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

Measurement equipment

Measurement item	Product No.	Manufacturer
L	E4991	Keysight Technologies
DC resistance	4338A	Keysight Technologies
Rated current Isat	F4991+16200B	Keysight Technologies

^{*} Equivalent measurement equipment may be used.

■TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range*	Storage temperature range**	Individual weight
−40 to +125 °C	−40 to +85 °C	3 mg

^{*} Operating temperature range includes self-temperature rise.






^{**} The storage temperature range is for after the assembly.



PLEA67B type

L FREQUENCY CHARACTERISTICS




Measurement equipment

Product No.	Manufacturer
E4991	Keysight Technologies

^{*} Equivalent measurement equipment may be used.

■INDUCTANCE VS. DC BIAS CHARACTERISTICS



Measurement equipment


Product No.	Manufacturer
E4991+16200B	Keysight Technologies

^{*} Equivalent measurement equipment may be used.



PLEA67B type


SHAPE & DIMENSIONS




Dimensions in mm

■PACKAGING STYLE

□REEL DIMENSIONS



TAPE DIMENSIONS




Type	Α	В	K
PLEA67	0.76	1.22	0.98


■ RECOMMENDED LAND PATTERN



Dimensions in mm

■ RECOMMENDED REFLOW PROFILE





Dimensions in mm

□PACKAGE QUANTITY

Package quantity	5000 pcs/reel
	<u> </u>



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment

person or property.

(4) Power-generation control equipment

set forth in the each catalog, please contact us.

- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions