

### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

### **Product image**











# Digital output modules P- or N-switching; short-circuit-proof; up to 3-wire + FE

Digital output modules are available in the following variants: 4 DO, 8 DO with 2- and 3-wire technology, 16 DO with or without PLC interface connection. They are mainly used for the incorporation of decentralised actuators. All outputs are designed for DC-13 actuators acc. to DIN EN 60947-5-1 and IEC 61131-2 specifications. As with the digital input modules, frequencies of up to 1 kHz are possible. Protection of the outputs ensures maximum system safety. This consists of an automatic restart following a short-circuit. Clearly visible LEDs signal the status of the entire module as well as the status of individual channels.

In addition to the standard applications of the digital output modules, the range also includes special variants such as the 4RO-SSR module for rapidly switching applications. Fitted with solid state technology, 0.5 A is available here to each output. Furthermore, there is also the 4RO-CO relay module for power-intensive applications. It equipped with four CO contacts, optimised for a switching voltage of 255 V UC and designed for a switching current of 5 A.

The module electronics supply the connected actuators from the output current path  $(U_{\text{OUT}})$ .

Version	Remote I/O module, IP20, Digital signals, Output,
	PLC
Order No.	<u>1315270000</u>
Туре	UR20-16DO-P-PLC-INT
GTIN (EAN)	4050118118162
Qty.	1 pc(s).
Replacement parts	<u>1350930000</u> <u>1346740000</u> <u>1483940000</u>



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

# **Dimensions and weights**

Depth	76 mm	Depth (inches)	2.992 inch
Height	120 mm	Height (inches)	4.724 inch
Width	11.5 mm	Width (inches)	0.453 inch
Mounting dimension - height	128 mm	Net weight	85 g

### **Temperatures**

Storage temperature	-40 °C +85 °C	Operating temperature	-20 °C +60 °C
Operating temperature, min.	-20 °C	Operating temperature, max.	60 °C

### digital outputs

Actuator connection	PLC-Interface	
Feedback-free	Yes	
Individual channel diagnosis	No	
Inductive load (DC13)	0.2 Hz	
Lamp load (12 W)	1 kHz	
Max. response time, high	100 µs	
Max. response time, low	250 μs	
Module diagnosis	Yes	
Number of digital outputs	16	
Output current per channel, max.	500 mA	
Output current per module, max.	8,000 mA	
Output current per module, remark	2 A with supply via a flat ribbon cable	
Resistive load (min. 47 Ω)	1 kHz	
Response time of the protective circuit (current limiting)	< 100µs	
Short-circuit-proof	Yes (thermal cut-out)	
Simultaneity factor	min.	0 %
	nominal	0 %
	max.	0 %
Switch-off energy (inductive)	< 150 mJ / channel	
Туре	Lamp load, Ohmic, Inductive	

### **Connection data**

I/O plug-in connector	20-pin ribbon cable	Type of connection	
	connection		PUSH IN
Wire connection cross section, finely	/	Wire connection cross section, finely	
stranded, max.	1.5 mm²	stranded, min.	0.14 mm <sup>2</sup>
Wire cross-section, finely stranded, max.		Wire cross-section, finely stranded, mir	· ·
(AWG)	AWG 16	(AWG)	AWG 26
Wire cross-section, solid, max.	1.5 mm <sup>2</sup>	Wire cross-section, solid, max. (AWG)	AWG 16
Wire cross-section, solid, min.	0.14 mm <sup>2</sup>	Wire cross-section, solid, min. (AWG)	AWG 26



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

### **General data**

Air humidity (operation)	10% to 95%, non- condensing as per DIN EN 61131-2	Air humidity (storage)	10% to 95%, non- condensing as per DIN EN 61131-2
Air humidity (transport)	10% to 95%, non- condensing as per DIN EN 61131-2	Air pressure (operation)	≥ 795 hPa (height ≤ 2000 m) as per DIN EN 61131-2
Air pressure (storage)	1013 hPa (height 0 m) to 700 hPa (height 3000 m) as per DIN EN 61131-2	Air pressure (transport)	1013 hPa (height 0 m) to 700 hPa (height 3000 m) as per DIN EN 61131-2
Pollution severity	2	Rail	TS 35
Shock	15 g over 11 ms, half sinus wave, acc. to IEC 60068-2-27	Surge voltage category	II
Test voltage	500 V	UL 94 flammability rating	V-0
Vibration resistance	5 Hz ≤ f ≤ 8.4 Hz: 3.5- mm amplitude as per IEC 60068-2-6, 8.4 Hz ≤ f ≤ 150 Hz: 1 g acceleration as per IEC 60068-2-6		

### **Power supply**

Current consumption from I <sub>OUT</sub> (th	e	Current consumption from I <sub>sys</sub> , typ.
respective power segment)	20 mA + load	. 8 mA
Voltage supply	24 V DC +20 %/ -15 %,	
	via the system bus	

### System data

Connection type	PUSH IN	Diagnostic data	1 Bit
Field bus protocol	PROFINET IRT, PROFINET RT, PROFIBUS DP-V1, EtherCAT, Modbus/TCP, EtherNet/IP, CANopen, DeviceNet, POWERLINK, CC-Link, CC-Link IE TSN, IEC 61162-450	Galvanic isolation	500 V DC between the current paths
Interface	u-remote system bus	Module type	Special module
Process data	2 Byte	Transmission speed of syster	n bus, max. 48 Mbit

### Classifications

ETIM 6.0	EC001599	ETIM 7.0	EC001599
ETIM 8.0	EC001599	ECLASS 9.0	27-24-26-04
ECLASS 9.1	27-24-26-04	ECLASS 10.0	27-24-26-04
ECLASS 11.0	27-24-26-04	ECLASS 12.0	27-24-26-04

### **Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	82327f13-cd27-455a-ab5b-a62e1996dcf8



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Technical data

### **Approvals**

Approvals















ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197
Certificate no. (cULusEX)	E223527

#### **Downloads**

Approval/Certificate/Document of	Compass safe distance certificate
Conformity	<u>Lloyds Register certificate</u>
	DNV/GL certificate
	ABS certificate
	RINA certificate
	Bureau Veritas - Type Approval Certificate
	PRS (Polish Register of Shipping)
	NIPPON KAIJI KYOKAI Certificate
	DEMKO15ATEX1525X
	CCC certificate
	<u>UKCA Declaration of Conformity - EN</u>
	CE Declaration of Conformity - DE
Engineering Data	CAD data – STEP
	Compatibility information – Combinability of UR20
Engineering Data	WSCAD, Zuken E3.S
User Documentation	MAN U-REMOTE DE
	MAN_U-REMOTE_EN
Catalogues	Catalogues in PDF-format




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

# **Drawings**

# **Block diagram**




# **Connection diagram**



### **Explanation of abbreviations**

### Digital output modules





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

### **Accessories**



### Potential-distribution modules; system accessory

A wide range of accessory modules is available for individual requirements of machine and plant engineering. Various potential distribution modules are available for the supply of sensors with 2- to 4-wire connection technology directly from the remote I/O system. These offer 16 "PUSH IN" potential points and supply your application with any auxiliary potential available. An empty module, where the system bus and voltage supply are looped through, allows you to plan expansion slots in a system and to start these up without any interruptions if required.

### **General ordering data**

Туре	UR20-SM-ACC	Version
Order No.	1339920000	Cover, ,
GTIN (EAN)	4050118144727	
Qty.	20 pc(s).	
Туре	UR20-EBK-ACC	Version
	ONEO EDITATION	Version
Order No.	<u>1346610000</u>	End bracket, ,

### Stainless steel



Stainless steel is a collective term for all types of steel (alloys) with a high degree of purity and corrosion resistance.

Туре	TS 35X7.5 2M/CRN	Version
Order No.	<u>1747350000</u>	Rail, TS 35, TS 35 x 7.5, without slot, Stainless steel, rust-proof,
GTIN (EAN)	4032248003372	Stainless steel 1.4301, untreated
Qty.	2 m	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

### **Blank**



### **General ordering data**

 Type
 PM 2.7/2.6 MC NE WS
 Version

 Order No.
 1323710000
 OMNIMATE Signal - series PM, Pusher markers, 2.7 x 2.6 mm, Pitch in mm (P): 3.50 Weidmueller, white

 Qty.
 960 pc(s).

### Ribbon cable, not halogen-free



Туре	PAC-UNIV-HE20-LCH-1M	Version
Order No.	<u>7789306010</u>	Pre-assembled cable, PAC, Cable LiYY, 0.14 mm <sup>2</sup>
GTIN (EAN)	8430243969062	
Qty.	1 pc(s).	
Туре	PAC-UNIV-HE20-HE20-1M	Version
Order No.	<u>1349670010</u>	Pre-assembled cable, PAC
GTIN (EAN)	4032248161294	
Qty.	1 pc(s).	
Туре	PAC-UNIV-HE20-F-1M	Version
Order No.	1349790010	Pre-assembled cable, PAC
GTIN (EAN)	4032248161003	
Qty.	1 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

### **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- · Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

ype DEK 5/8-11.5 MC SDR

Order No. <u>1341610000</u> De

GTIN (EAN) 4050118146059

Qty. 100 pc(s).

Version

Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00

Weidmueller, To customer specification

### **Custom printing**



### **General ordering data**

Type PM 2.7/2.6 MC SDR

Order No. <u>1323700000</u> GTIN (EAN) 4050118126761

Qty.

4050118126761 192 pc(s). Version

OMNIMATE Signal - series PM, Pusher markers, 2.7 x 2.6 mm, Pitch in

mm (P): 3.50 Weidmueller, To customer specification



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

### **Aluminum**



Aluminum has the second best electrical conductivity after copper. One advantage is low weight, an Miscellaneous is outstanding corrosion protection.

### **General ordering data**

 Type
 TS 35X7.5 2M/AL/BK
 Version

 Order No.
 0330800000
 Rail, TS 35, TS 35 x 7.5, without slot, Aluminium, untreated

 GTIN (EAN)
 4008190100650

#### Steel

Qty.



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

Type	TS 35X7.5/LL 2M/ST/ZN	Version
Order No.	0514500000	Rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanic zinc plated and
GTIN (EAN)	4008190046019	passivated
Qty.	2 m	
Туре	TS 35X7.5/LL 1M/ST/ZN	Version
Order No.	0514510000	Rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanic zinc plated and
GTIN (EAN)	4008190116620	passivated
Qty.	1 m	
Туре	TS 35X7.5/LL 2M/ST/SZ	Version
Type Order No.	TS 35X7.5/LL 2M/ST/SZ 7915060000	Version Rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanic zinc plated and
	, , ,	
Order No.	7915060000	Rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanic zinc plated and
Order No. GTIN (EAN)	7915060000 4032248296279	Rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanic zinc plated and
Order No. GTIN (EAN) Qty.	7915060000 4032248296279 2 m	Rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanic zinc plated and passivated
Order No. GTIN (EAN) Oty. Type	7915060000 4032248296279 2 m TS 35X7.5 2M/ST/ZN	Rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanic zinc plated and passivated  Version



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

#### **Blank**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- · Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

Type DEK 5/8-11.5 MC NE WS Version

Order No. 1341630000 Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00

GTIN (EAN) 4050118145946 Weidmueller, white

Qty. 500 pc(s).



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Replacement parts

### **Electronic modules**



### **General ordering data**

Type UR20-EM-1315270000-SP

Order No. <u>1346740000</u>

GTIN (EAN) 4050118151589

Qty. 1 pc(s).

Version

Replacement part, ,

### **Plugkit**



### **General ordering data**

Type UR20-PK-1315270000-SP Order No. 1483940000

GTIN (EAN) 4050118293524

Ωty. 5 pc(s).

Version

Replacement part



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Replacement parts

### **Basic modules**



Туре	UR20-BM-SP	Version	Packaging
Order No.	1350930000	Replacement part, , Flange-mounted housing	Cardboard
GTIN (EAN)	4050118402735		box
Qty.	5 pc(s).		