Mosaic Core Specification

	Mosaic Core Specifica	ation	
Core Number: C304SP	Starter Kit Number: S304SP	Mktg Rev. 3	11/05/2021
Product Specifications:	Description		
Microbolometer	Uncooled Vanadium Oxide		
Pixel Pitch	12 Microns		
Spectral Response	7.8 - 14 Microns		
Sensor Resolution (Array Format)	320 (h) x 240 (v); 76,800 pixels		
Frame Rate	Slow Frame - <9Hz		
Non-Uniformity Correction (NUC)	Automatic NUC (with shutter)		
Video Output Interfaces	USB		
Power:			
Power Requirment	3.3-5.0V, <50mW (Core only), 300mW (Cor	e + Coprocessor Board)	
Optical & Mechanical:	0.0 0.0 1, 0.0 (0.0 0, 1, 1, 0.0 (0.0		
Focal Length	4.0mm EFL		
F-number (Focal Length/aperture)	f/1.00		
Spatial Resolution (IFOV, center)	3.00		
Field of View (FOV)	56° Horizontal x 42° Vertical		
` '	333m (based on Johnson Criteria)		
Detection Range	· · · · · · · · · · · · · · · · · · ·		
Recognition Range	83m (based on Johnson Criteria)		
Identification Range	48m (based on Johnson Criteria)		
Distance to Spot Ratio	56:1	T .	
Core Size / Core Weight	20mm x 20mm x 21mm	Core Weight: 12 g	
Seek Software Development Kit:			
Supported Platforms	USB: Seek Linux, Windows, & Android SDK		
Output Formates (User selectable)	Linux / Windows SDK	Android SDI	(
	16-bit filtered pre AGC	16-bit filtered pre AGC	
	32-bit ARGB post colorization.	32-bit ARGB post colorization in the bitmap image.	
	32-bit floating point or 16-bit fixed point	32-bit floating point or 16-bit fixed p	oint thermography data
Imaging Specifications:	Calibrated Output in °C, °F, K		
Imaging Range	-40°C to +330°C at ambient operating temprature		
Thermography Accuracy	Center spot temperature greater of ±5°C or 5% between 5°C to 140°C		
	Center spot temperature greater of ±10°C or 10% (typical) above 140°C		
	All measured at 25°C ambient operating temperature and nominal measurement distance of 12 inches.		
	Temperature reported is Center Spot temperature, which is an average of the center 36 pixels.		
Sensor Sensitivity	65 mK (typical), <100 mK (max) @ 25°C		
Emmissivity	Factory default emissivity is set to 0.97. Emissivity is adjustable using the SDK.		
Environmental Conditions:	· · ·	, ,	
Operating Temperature Range	-10°C to +60°C (-14°F to 140°F)		
Storage Temperature Range	-40°C to +80°C (-40°F to 176°F)		
Solar Protection	Yes		
Humidity	10%~95%RH, non-condensing		
Regulatory	ROHS, WEEE, REACH		
Accessories:			
Cushion	Yes CUSHION THERMAL BRACKET CAMPEA	SENSOR FLEX INTERFACE USB FLEX BOARD	
Bracket	Yes		
Sensor Flex	Yes N m		
Coprocessor Board	Yes		
USB Flex	Yes	COPROCESSOR BOARD AND INTERFACE KIT Provided by Seek or receive design files for	
Customer Responsibilities:	1.03	integration into other electronics	
IP Rating	IP67		
Shock/Vibe	Customer responsibility with proper integra	tion into final product housing	
Convright 2021 Seek Thermal Inc		Specifications are subject to	



