									_	
PCN Number:	2000.1	).1 F			CN D	ate:	February 23, 2023			
Title: Qua	Title: Qualification of RFAB as an additional Fab site option for select LBC8 devices									
<b>Customer Cont</b>	<u>anager</u>	<u>nager</u>			ept:		Quality Services			
Proposed 1st S	Proposed 1st Ship Date: May 22, 20				Sample accepto				Mar 22, 2023*	
*Sample reque	sts receive	d after	March 22,	2023 wi	ll not b	e s	upp	orted.		
Change Type:										
Assembly S	Site	Assembly Process					Assembly Materials			
Design		Electrical Specification					<u> </u>	Mechanical Specification		
☐ Test Site			Packing/S				<u> </u>	Test Process		
<ul><li>✓ Wafer Bum</li><li>✓ Wafer Fab</li></ul>			Wafer But				<u> </u>	Wafer Bump Process Wafer Fab Process		
	Site		Wafer Fal					warer	Fab Process	
			Part numb							
Description of (	Change:		Notifica	tion De	talis					
additional Wafer	Texas Instruments is pleased to announce the qualification of its RFAB fabrication facility as an additional Wafer Fab source for the selected devices listed in the "Product Affected" section.									
	Current Fab Site Additional Fab Site									
Current Fab Process Site		Wafer Diameter		New Fab Site			roce	ess	Wafer Diameter	
MIHO8 LBC8			200 mm RFAB				LBC	8	300 mm	
Qual details are	Qual details are provided in the Qual Data Section.									
Reason for Cha	nge:									
Continuity of sup	oply.									
Anticipated imp	pact on Fit,	Form,	Function,	Quality o	r Relia	bili	ty (¡	ositive	/ negative):	
None.										
Changes to pro	duct identif	ication	resulting	from thi	s PCN:					
Fab Site Inform	ation:									
						) Chip Site City				
MIHO8 MH8						JPN			Ibaraki	
RFAB RFB USA Richardson										
Sample product shipping label (not actual product label)  Texas INSTRUMENTS MADE IN: Malaysia 20c: 20: (Q) 2000 (D) 0336										





(31T)LOT: 3959047MLA (4W) TKY(1T) 7523483SI2 (2D) REV: (20L) CSO: SHE (21L) CCO:USA (22L) ASO: MLA (23L) ACO: MY8

# **Product Affected:**

ISO1540DR	ISO	01640BDR	ISO1641BDR					
ISO1541DR	ISO	01640DWR	ISO1641DWR					

### Qualification Report Approve Date 09-February-2023

### Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	#	Test Name	Condition	Duration	Qual Device: ISO1640BDR	Qual Device: ISO1640DWR	Qual Device: ISO1641BDR	Qual Device: ISO1641DWR	QBS Reference: UCC23513QDWYQ1	QBS Reference: ISO1640BQDRQ1	QBS Reference: ISO6760QDWRQ1	QBS Reference: ISO6761QDWRQ1	QBS Reference: ISO6763QDWRQ1	QBS Reference: ISO6762QDWRQ1
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	-		3/231/0	3/231/0	1/77/0	-	1/77/0	1/77/0
UHAST	А3	Autoclave	121C/15psig	96 Hours		-	-	-	3/231/0	3/231/0	1/77/0	-	1/77/0	1/77/0
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	1/77/0	-		-	3/231/0	3/231/0	1/77/0	1/77/0	1/77/0	-
HTSL	A6	High Temperature Storage Life	150C	1000 Hours	-	-	-	-	-	1/45/0	-	-	-	-
HTSL	A6	High Temperature Storage Life	175C	500 Hours	-	-	-	-	3/135/0	-	1/45/0	1/45/0	1/45/0	-
HTOL	B1	Life Test	125C	1000 Hours	-	-		-	3/231/0	-	1/77/0	1/77/0	-	-
ELFR	B2	Early Life Failure Rate	125C	48 Hours		-		-	3/2400/0	-	-	-	-	-
SD	СЗ	PB Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	-	-	1/15/0	-	-	-	1/15/0	-
SD	C3	PB-Free Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	-	-	1/15/0	-	-	-	1/15/0	-
PD	C4	Physical Dimensions	Cpk>1.67	-		-	-	-	3/30/0	-	-	-	-	-
ESD	E2	ESD CDM	-	250 Volts	-	1/3/0	-	-	1/3/0	1/3/0	1/3/0	1/3/0	1/3/0	1/3/0
ESD	E2	ESD HBM	-	1000 Volts	-	1/3/0	-	-	1/3/0	1/3/0	1/3/0	1/3/0	1/3/0	1/3/0
LU	E4	Latch-Up	Per JESD78	-	-	1/3/0	-	-	1/6/0	1/6/0	1/6/0	1/6/0	1/6/0	1/6/0
CHAR	<b>E</b> 5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	1/30/0	-	-	3/90/0	3/90/0	-	-	-	-
FTY	E6	Final Test Yield	-	-	1/1/0	1/1/0	1/1/0	1/1/0	-	-	-	-	-	-

- QBS: Qual By Similarity
   Qual Device ISO1640BDR is qualified at MSL2 260C
- Qual Device ISO1640DWR is qualified at MSL2 260C
- Qual Device ISO1641BDR is qualified at MSL2 260C
   Qual Device ISO1641DWR is qualified at MSL2 260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/Ik Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
  The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/Ik Hours, and 170C/420 Hours
  The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

### Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

## Qualification Report Approve Date 12-OCTOBER -2022

#### **Qualification Results**

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	#	Test Name	Condition	Duration	Qual Device: ISO1644DWR	QBS Reference: UCC23513QDWYQ1	QBS Reference: UCC21520ADW
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	3/231/0
UHAST	A3	Autoclave	121C/15psig	96 Hours	-	-	3/231/0
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	-	-	3/231/0
HTSL	A6	High Temperature Storage Life	175C	300 Hours	-	-	3/135/0
HTOL	B1	Life Test	125C	1000 Hours	-	3/231/0	-
ELFR	B2	Early Life Failure Rate	125C	48 Hours	-	3/2400/0	-
WBS	C1	Ball Shear	76 balls, 3 units min	Wires	1/76/0	-	-
WBP	C2	Bond Pull	76 Wires, 3 units min	Wires	1/76/0	-	-
ESD	E2	ESD CDM	-	250 Volts	1/3/0	1/3/0	-
ESD	E2	ESD HBM	-	1000 Volts	1/3/0	1/3/0	-
LU	E4	Latch-Up	Per JESD78	-	1/3/0	-	-
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	3/90/0	-

- QBS: Qual By Similarity
- Qual Device ISO1644DWR is qualified at MSL2 260C
- · Qual Device ISO1643DWR is qualified at MSL2 260C
- Qual Device ISO1642DWR is qualified at MSL2 260C
- · Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

For questions regarding this notice, e-mails can be sent to the contact below or your local Field Sales Representative.

Location	E-Mail				
WW Change Management Team	PCN www admin team@list.ti.com				

# **IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property

right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<a href="www.ti.com/legal/termsofsale.html">www.ti.com/legal/termsofsale.html</a>) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

PCN# 20230222000.1