



# 3M™ Scotch-Weld™ Super Fast Instant Adhesive SF100

Last Revision Date: May, 2022

# **Product Description**

3M™ Scotch-Weld™ Super Fast Instant Adhesives rely less on surface moisture for cure speed than standard cyanoacrylates. They are designed to join together difficult-to-bond plastics and rubbers, acidic and/or contaminated surfaces such as woods, leathers, cardboard, and oily surfaces. These cyanoacrylates can be used for a super fast cure in high speed production applications.

# **Product Features**

3M™ Scotch-Weld™ Super Fast Instant Adhesive SF100 is a low viscosity super fast cyanoacrylate.

#### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Ethyl Hybrid

## Typical Uncured Physical Properties

Property	Values	Additional Information	
Color	Clear	View ^	
Notes: Colors may vary from nea	arly white to yellow/amber. Adhesive performance is not	ffected by color variation.	

## Typical Mixed Physical Properties

Base

Property	Values	Additional Information
Time to Handling Strength	<10 s	View ^

Notes: Min time between bond creation and ability to support a 5 psi tensile load. Open and set times determined by RT environment. Higher temps will lengthen open and set times, while lower temperatures will shorten open time and set time.

Time to Full Cure	24 hr	View ^	
Temp C: 23C Temp F: 73F			
Percent of Initial Strength	100 %	View ^	



Temp C: 23C Temp F: 73F

Percent of Initial Strength	75 %	View ^
Temp F: 167F		
Percent of Initial Strength	59 %	View ^
Temp F: 212F		
Percent of Initial Strength	18 %	View ^
Temp F: 257F		
Gap Fill	0.006 in	

## Typical Physical Properties

Property	Values	Additional Information
Specific Gravity	1.06 g/mL	

Appearance	Liquid

## Storage and Shelf Life

For short term storage (<30 days), keep adhesive in a cool (60°F to 80°F [16°C to 27°C]), dry place out of direct sunlight. Keep containers tightly covered and free of moisture. Refrigeration (40°F [4°C]) gives optimum long term storage stability.

3M™ Scotch-Weld™ Super Fast Instant Adhesives can be expected to have a shelf life of 15 months from the date of manufacture when stored under refrigerated conditions.

## **Bottom Matter**

3M Industrial Adhesives and Tapes Division 3M Center, Building 225-3S-06 St. Paul, MN 55144-1000 800-362-3550

#### Trademarks

3M and Scotch-Weld are trademarks of 3M Company.

# Automotive Disclaimer

Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, including, but not limited to, automotive electric powertrain battery or high voltage applications. This product does not fully adhere to typical automotive design or quality system requirements, such as IATF 16949 or VDA 6.3. This product may not be manufactured in an IATF certified facility and may not meet a Ppk of 1.33 for all properties. The product may not undergo an automotive production part approval process (PPAP). Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's automotive application and for conducting incoming inspections before use of the product. Failure to do so may result in injury, death, and/or harm to property. No written or verbal statement, report, data or recommendation by 3M related to automotive use of the product shall have any force or effect unless in an agreement



signed by the Technical Director of 3M's Automotive Division. Customer assumes all responsibility and risk if customer chooses to use this product in an automotive electric powertrain battery or high voltage application, and 3M will not be liable for any loss or damage arising from or related to the 3M product or customer's use of the product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity or recall costs), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. In no event shall 3M be liable for any damages in excess of the purchase price paid for the product.

NOTWITHSTANDING ANY OTHER STATEMENT TO THE CONTRARY, 3M MAKES NO REPRESENTATIONS, WARRANTIES OR CONDITIONS WHATSOEVER, EXPRESS OR IMPLIED, REGARDING THE PRODUCT IF USED IN AN AUTOMOTIVE ELECTRIC POWERTRAIN BATTERY OR HIGH VOLTAGE APPLICATION, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY ON PERFORMANCE, LONGEVITY, SUITABILITY, COMPATIBILITY, OR INTEROPERABILITY, OR ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.

#### Handling/Application Information

Directions for Use

- 1. Ensure that parts are clean, dry, and free from oil and grease.
- 2. An instant adhesive activator may be required if there are bonding gaps or porous substrate surfaces, if substrates are low surface energy plastics (e.g., polyethylene, polypropylene) or if substrates have acidic surfaces (e.g., paper, leather).
- 3. Bond speed is typically very fast so ensure that parts are properly aligned before dispensing.
- 4. Product is normally hand applied from the bottle. Apply sparingly to one surface and press parts firmly together until handling strength is achieved. As a general rule, as little cyanoacrylate as possible should be used. Over application will result in slower cure speed and lower bond strength.

#### Surface Preparation

For optimum strength structural bonds, paint, oxide films, oils, dust, mold release agents, and all other surface contaminants must be completely removed. However, the amount of surface preparation depends on the required bond strength and the environmental aging resistance desired by the user. Typical quick surface preparation would include wiping with a clean solvent (such as isopropyl alcohol\*), abrading the surface with a clean fine abrasive, and then wiping again with a clean solvent to remove loose particles.

\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

**Cured Bond Characteristics** 

- 1. Full bond strength will typically be achieved within a 24 hour cure time.
- 2. Low humidity or low temperature conditions will slow down the cure rate.
- 3. After curing, 3M™ Scotch-Weld™ Super Fast Instant Adhesive bonds are suitable for use up to about 180°F (82°C).
- 4. Cyanoacrylate bond resistance to most oils and solvents is excellent. Long term humidity, moisture, or water immersion may affect the strength of a cured cyanoacrylate bond depending on the substrates and the bond gap. Testing is recommended to evaluate the effect.

## References

Property	Values
3m.com Product Page	https://www.3m.com/3M/en_US/p/d/b40066913/
Safety Data Sheet SDS	https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&msdsLocale=en_US&co=ptn&q=SF100

# Family Group

Link Tags:



Products	Time to Full Cure
SF100	24 hr
SF20	24 hr

## ISO Statement

This product was manufactured under a quality system registered to ISO 9001 standards.



### Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

#### Information

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use.

Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

