

Harvatek Surface Mount PLCC LEDs Data Sheet T2133BGR-20C0001U2U1930

Official Product	luct HT Part No.T2133BGR-20C0001U2U1930					
Tentative Product	********					
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 1/14		



DISCLAIMER	3
LIFE SUPPORT POLICY	3
PRODUCT SPECIFICATIONS	4
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION	4
LABEL SPECIFICATIONS	5
SPECIFICATIONS RANGE	6
PRODUCT FEATURES	7
ELECTRO-OPTICAL CHARACTERISTICS	7
PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW	_
SOLDERINGABSOLUTE MAXIMUM RATINGS	
CHARACTERISTICS OF T2133BGR	
PRECAUTION FOR USE	
PACKAGING	10
Packing	10
DRY PACK	11
Baking	11
Precautions	11
HANDLING OF SILICONE RESIN LEDS	12
REFLOW SOLDERING	13
REWORKING	13
CLEANING	
CAUTIONS OF PICK AND PLACE	
Revise History	14

7					
Official Product	HT Part No.T2133BGR-20C0001U2U1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 2/14	



DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

7					
Official Product	HT Part No.T2133BGR-20C0001U2U1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 3/14	



Product Specifications

Item	Specification	Material	Quantity
Luminous	B:180-450 mcd @ 20 mA		
Intensity (Iv)	G:1440-2850 mcd @ 20 mA		
	R:285-1125 mcd @ 20 mA		
	T _s = 25°C;Tolerance: <u>+</u> 10%		
Dominant	B:460.0-470.0 nm @ 20 mA		
Wavelength (Wd)	G:520.0-530.0 nm @ 20 mA		
	R:615.0-625.0 nm @ 20 mA		
	T _S = 25°ℂ;Tolerance: <u>+</u> 0.1nm		
Forward	B:2.7-3.7 V @ 20 mA		
Voltage (Vf)	G:2.7-3.7 V @ 20 mA		
	R:1.6-2.4 V @ 20 mA		
	T _S = 25°C ;Tolerance: <u>+</u> 0.05V		
Ir	< 10 μA @ V _R = 5 V		
ESD	RGB≤2kV@HBM		
Resin	Clear	Silicon	
Carrier tape	EIA 481-1A specs	Conductive black tape	
Reel	EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	220x240mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	Non-specified

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, λ_D and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note: This is shipped test conditions

**Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.

ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must be taken during design and


assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.


Official Product HT Part No.T2133BGR-20C0001U2U1930					
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 4/14	



Label Specifications



Harvatek P/N:



Lot No.:

1	2	3	4	5	6	7	8	9	10
Е	1	Α	1	Α	2	2	L	1	2
Code	e 1 2	Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
		Mfg. Year	Mfg. Month	Mfg. Date	Consecuti	ve number		Special code	9
		2010-A		1:A					
		2011-B		2:B					
		2012-C	1:Jan.	3:C					
			2:Feb.						
Internal Tra	acing Code	2018-I/J		26:Z	01.	-ZZ		000~ZZZ	
internal ITa	acing Code	2019-K	A:Oct.	27:7	017	-22		000~222	
			B:Nov.	28:8					
			C:Dec.	29:9					
		2023-P		30:3					
				31:4					

7					
Official Product	HT Part No.T2133BGR-20C0001U2U1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 5/14	



Specifications Range

■Luminous Intensity (Iv) :

Color	Bin Code	Min	Max	Unit
	S	180	285	
В	Т	285	360	
	U	360	450	
	AA	1440	1800	
G	AB	1800	2250	mcd
	AC	2250	2850	
	AT	285	450	
R	AU	450	715	
	AV	715	1125	

Note: It maintains a tolerance of ±10% on Luminous Intensity

■Dominant Wavelength (Wd):

Color	Bin Code	Min	Max	Unit
В	AA	460	465	
В	ВВ	465	470	
	В	520	525	
G	С	525	530	nm
В	Α	615	620	
R	В	620	625	

Note: It maintains a tolerance of Wd ±1.0 nm

Forward Voltage (Vf):

Color	Bin Code	Min	Max	Unit
В	G4A	2.7	3.7	
G	G4A	2.7	3.7	V
R	E18	1.6	2.4	

Note: It maintains a tolerance of $\pm 0.1 \text{V}$ on forward voltage measurements

Official Product	HT Part No.T2133BGR-20C0001U2U1930				
Tentative Product	*********				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 6/14	

05 00




Product Features

Electro-Optical Characteristics

			V _F (V) Wavelength λd(nm)		I _V (mcd)	Viewing		
Series	Emitting Color	Material	Min.	Max.	Min.	Max.	Typical	Angle $2\theta \frac{1}{2}$
T2133BGR	В	InGaN	2.7	3.7	460	470	300	120
	G	InGaN	2.7	3.7	520	530	1850	120
	R	AlGaInP	1.6	2.4	615	625	600	120

Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering

(Unit:mm Tolerance: +/-0.1)



Absolute Maximum Ratings

(T_{Soldering} 25 °C)


Series	P _D (mW)	I _F (mA)	I _{FP} (mA)*	T _{OP} (°C)	T _{ST} (°C)
Color	Power Forward Pulse For		Pulse Forward	Operating	Storage
Color	Dissipation	Current	Current	Temperature	Temperature
Blue/Green	111	30	80	-40~+85	-40~+100
Red	72	30	80	-40~+65	-40~+100


^{*} Condition for I_{FP} is pulse of 1/10 duty and 0.1msec width


7				
Official Product	HT Part No.T2133BGR-20C0001U2U1930			
Tentative Product	********	********		
	t to changes for improvement without advance rawings, company confidential all rights reserved.	12/26/2022	1.0	Page 7/14





Characteristics of T2133BGR














Official Product	HT Part No.T2133BGR-20C0001U2U1930			
Tentative Product	********	********		
	t to changes for improvement without advance awings, company confidential all rights reserved.	12/26/2022	1.0	Page 8/14




Precaution for Use

- 1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within 72 hrs after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

7	-			
Official Product	HT Part No.T2133BGR-20C0001U2U1930			
Tentative Product	********	*******		
	t to changes for improvement without advance rawings, company confidential all rights reserved.	12/26/2022	1.0	Page 9/14




Packaging



Part No.	Dim. A	Dim. B	Dim. C	Q'ty/Reel
HT-B33A3	2.25±0.10	2.32±0.10	1.10±0.10	2K

Packing



5 or 10 boxes per carton is available depending on shipment quantity.

Official Product HT Part No.T2133BGR-20C0001U2U1930				
Tentative Product	********	*******		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 10/14




Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

Upon request, a humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



Baking

Baking before soldering is recommended when the package has been unsealed for 72 hrs. The conditions are as followings:

- 1. $60\pm3^{\circ}$ C ×(12~24hrs)and<5%RH, taped reel type.
- 2. $100\pm3^{\circ}$ × (45min~1hr), bulk type.
- 3. $130\pm3^{\circ}$ C ×(15min~30min), bulk type.

Precautions

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AllnGaP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product HT Part No.T2133BGR-20C0001U2U1930				
Tentative Product	********	*******		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 11/14



Handling of Silicone Resin LEDs

Handling Indications

During processing, mechanical stress on the surface should be minimized as much as possible.

Sharp objects of all types should not be used to pierce the sealing compound.




Figure 1

In general, LEDs should only be handled from the side. By the way ,this also applies to LEDs without a silicone sealant, since the surface can also become scratched.




Figure 2

When populating boards in SMT production, there are basically no restrictions regarding the from of the pick and place nozzle, except that mechanical pressure on the surface of the resin must be prevented.

This is assured by choosing a pick and place nozzle which is large than LEDs reflector area.


Official Product	roduct HT Part No.T2133BGR-20C0001U2U1930				
Tentative Product	********	*******			
	t to changes for improvement without advance rawings, company confidential all rights reserved.	12/26/2022	1.0	Page 12/14	



Reflow Soldering

Recommend soldering paste specifications:

- 1. Operating temp.: Above 217°C ,60~150 sec.
- 2. Peak temp.:260°C Max.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- 4. Never attempt next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measured on the surface of the LED terminal) is as following:



Reworking

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultrasonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 °C max, <3min

Official Product HT Part No.T2133BGR-20C0001U2U1930				
Tentative Product	********	********		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		12/26/2022	1.0	Page 13/14



Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Revise History

Rev.	Descriptions	Date	Page
1.0	New Format	12/26/2022	-

7				
Official Product	HT Part No.T2133BGR-20C0001U2U1930			
Tentative Product	********	*******		
	t to changes for improvement without advance awings, company confidential all rights reserved.	12/26/2022	1.0	Page 14/14