US1883

Melexis Inspired and Inspired a

Hall Latch - Medium Sensitivity

Features and Benefits

- Wide operating voltage range from 3.5V to 24V
- Medium magnetic sensitivity Multi-purpose
- CMOS technology
- Chopper-stabilized amplifier stage
- Low current consumption
- Open drain output
- Flat TO-92 3L (RoHS Compliant)

Applications

- Automotive, Consumer and Industrial
- Solid-state switch
- Brushless DC motor commutation
- Speed detection
- Linear position detection
- Angular position detection
- Proximity detection

Ordering information


Product code	Temperature Code	Package Code	Option code	Packing form code
US1883	L	UA	AAA-000	BU

Legend:

Temperature code: L(-40 to 150°C)
Package Code: UA = TO92-3L
Packing Form: BU = Bulk

Ordering Example: US1883LUA-AAA-000-BU

1. Functional Diagram



2. General Description

The Melexis US1883 is a Hall-effect latch designed in mixed signal CMOS technology.

The device integrates a voltage regulator, Hall sensor with dynamic offset cancellation system, Schmitt trigger and an open-drain output driver, all in a single package.

Thanks to its wide operating voltage range and high temperature grade, it is quite suitable for use in automotive, industrial and consumer applications.

The device is delivered in a Plastic Single In Line (TO-92 flat) for through-hole mount, RoHS compliant.

US1883

Hall Latch – Medium Sensitivity



Contents

Features and Benefits	1
Applications	1
Ordering information	1
1. Functional Diagram	1
2. General Description	1
3. Glossary of Terms	3
4. Absolute Maximum Ratings	3
5. Pin Definitions and Descriptions	3
6. General Electrical Specifications	4
7. Magnetic Specifications	4
8. Output Behaviour versus Magnetic Pole	4
9. Detailed General Description	5
10. Unique Features	5
11. Performance Graphs	6
11.1. Magnetic parameters vs. T _A	6
11.2. Magnetic parameters vs. V _{DD}	
11.3. V _{DSON} vs. T _A	
330.11	
11.4. V _{DSON} vs. V _{DD}	
11.5. I _{DD} vs. T _A	
11.6. I _{DD} vs. V _{DD}	
11.7. I _{OFF} vs. T _A	
11.8. I _{OFF} vs. V _{DD}	7
12. Test Conditions	7
12.1. Supply Current	7
12.2. Output Saturation Voltage	
12.3. Output Leakage Current	
12.4. Magnetic Thresholds	
13. Application Information	8
13.1. Typical Three-Wire Application Circuit	
13.2. Two-Wire Circuit	
13.3. Automotive and Harsh, Noisy Environments Three-Wire Circuit	8
14. Application Comments	8
15. Standard information regarding manufacturability of Melexis products with different soldering	•
processes	
16. ESD Precautions	
17. UA Package Information (TO92 flat)	10
18. Contact	
19. Disclaimer	11

Hall Latch - Medium Sensitivity



3. Glossary of Terms

MilliTesla (mT), Gauss Units of magnetic flux density:

1mT = 10 Gauss

RoHS Restriction of Hazardous Substances

TSOT Thin Small Outline Transistor (TSOT package) – also referred with the Melexis package

code "SE"

ESD Electro-Static Discharge
BLDC Brush-Less Direct-Current

Operating Point (B_{OP}) Magnetic flux density applied on the branded side of the package which turns

the output driver ON $(V_{OUT} = V_{DSon})$

Release Point (B_{RP}) Magnetic flux density applied on the branded side of the package which turns

the output driver OFF (V_{OUT} = high)

4. Absolute Maximum Ratings

Parameter	Symbol	Value	Units
Supply Voltage	V_{DD}	28	V
Supply Current	I_{DD}	50	mA
Output Voltage	V _{OUT}	28	V
Output Current	I _{OUT}	50	mA
Storage Temperature Range	T_S	-50 to 150	°C
Maximum Junction Temperature	TJ	165	°C

Table 1: Absolute maximum ratings


Exceeding the absolute maximum ratings may cause permanent damage. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

Operating Temperature Range	Symbol	Value	Units
Temperature Suffix "L"	ΤΛ	-40 to 150	°C

5. Pin Definitions and Descriptions

SE Pin No	UA Pin No	Name Type		Function
1	1	VDD	Supply	Supply Voltage pin
2	3	OUT	Output	Open Drain Output pin
3	2	GND	Ground	Ground pin

Table 2: Pin definitions and descriptions



Page 3 of 11



6. General Electrical Specifications

DC Operating Parameters $T_A = 25^{\circ}C$, $V_{DD} = 3.5V$ to 24V (unless otherwise specified)

T S N	, 55	or to 211 (diffess other wise spee	,			
Parameter	Symbol	Test Conditions	Min	Тур	Max	Units
Supply Voltage	V_{DD}	Operating	3.5		24	V
Supply Current	I_{DD}	$B < B_{RP}$			5	mA
Output Saturation Voltage	V_{DSon}	$I_{OUT} = 20 \text{mA}, B > B_{OP}$			0.5	V
Output Leakage Current	I _{OFF}	$B < B_{RP}$, $V_{OUT} = 24V$		0.3	10	μΑ
Output Rise Time	t _r	$R_L = 1k\Omega$, $C_L = 20pF$		0.25		μs
Output Fall Time	t _f	$R_L = 1k\Omega$, $C_L = 20pF$		0.25		μs
Maximum Switching Frequency	F_{SW}			10		KHz
Package Thermal Resistance	R _{TH}	Single layer (1S) Jedec board		200		°C/W

Table 3: Electrical specifications

7. Magnetic Specifications

DC Operating Parameters $V_{DD} = 5V$ to 24V (unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Тур	Max	Units
Operating Point	B _{OP}		10	14	18	mT
Release Point	B_RP		-18	-14	-10	mT
Hysteresis	B _{HYST}]	20	28	36	mT

Table 4: Magnetic specifications


Note 1: Typical values given at 12V and 25°C

8. Output Behaviour versus Magnetic Pole

DC Operating Parameters $T_A = -40$ C to 150 C, $V_{DD} = 3.5$ V to 24V (unless otherwise specified)

Parameter	Test Conditions (UA)	OUT (UA)
South pole	$B > B_{OP}$	Low
North pole	$B < B_{RP}$	High

Table 5: Output behaviour versus magnetic pole





9. Detailed General Description

Based on mixed signal CMOS technology, Melexis US1883 is a Hall-effect device with medium magnetic sensitivity. This multi-purpose latch suits most of the application requirements.

The chopper-stabilized amplifier uses switched capacitor technique to suppress the offset generally observed with Hall sensors and amplifiers. The CMOS technology makes this advanced technique possible and contributes to smaller chip size and lower current consumption than bipolar technology. The small chip size is also an important factor to minimize the effect of physical stress.


This combination results in more stable magnetic characteristics and enables faster and more precise design.

The wide operating voltage from 3.5V to 24V, low current consumption and high operating temperature range according to "L" specification make this device suitable for automotive, industrial and consumer applications.

The output signal is open-drain type. Such output allows simple connectivity with TTL or CMOS logic by using a pull-up resistor tied between a pull-up voltage and the device output.

10. Unique Features

The US1883 exhibits latch magnetic switching characteristics. Therefore, it requires both south and north poles to operate properly.



UA package - Latch characteristic

The device behaves as a latch with symmetric operating and release switching points ($B_{OP} = |B_{RP}|$). This means magnetic fields with equivalent strength and opposite direction drive the output high and low.

Removing the magnetic field ($B\rightarrow 0$) keeps the output in its previous state. This latching property defines the device as a magnetic memory.


A magnetic hysteresis B_{HYST} keeps B_{OP} and B_{RP} separated by a minimal value. This hysteresis prevents output oscillation near the switching point.

REVISION 005 – 13 JUNE 2019 Page 5 of 11




11. Performance Graphs


11.1. Magnetic parameters vs. T_A




11.2. Magnetic parameters vs. V_{DD}




11.3. V_{DSON} vs. T_A




11.4. V_{DSON} vs. V_{DD}



11.5. I_{DD} vs. T_A




11.6. I_{DD} vs. V_{DD}




Melexis

11.7. I_{OFF} vs. T_A




11.8. I_{OFF} vs. V_{DD}



12. Test Conditions

Note: DUT = Device Under Test

12.1. Supply Current




Note 1 - The supply current I_{DD} represents the static supply current. OUT is left open during measurement.

Note 2 - The device is put under magnetic field with B<B_{pp}.


OUT is left open during measurement.

12.3. Output Leakage Current



Note 1 - The device is put under magnetic field with B<B_{RP}


12.2. Output Saturation Voltage



Note 1 - The output saturation voltage $\rm V_{DSon}$ is measured at $\rm V_{DD}$ = 3.5V and $\rm V_{DD}$ = 24V.

Note 2 - The device is put under magnetic field with B>B_{OP}.

12.4. Magnetic Thresholds




Note 1 - B_{OP} is determined by putting the device under magnetic field swept from B_{RPmin} up to B_{OPmax} until the output is switched on.

Note 2 - B_{RP} is determined by putting the device under magnetic field swept from B_{OPmax} down to B_{RPmin} until the output is switched off.




13. Application Information


13.1. Typical Three-Wire Application Circuit



13.3. Automotive and Harsh, Noisy Environments Three-Wire Circuit



13.2. Two-Wire Circuit



Note:

With this circuit, precise ON and OFF currents can be detected using only two connecting wires.

The resistors RL and Rb can be used to bias the input current. Refer to the part specifications for limiting values.

$$\begin{split} I_{OFF} &= I_R \ + I_{DD} = V_{DD}/R_b + I_{DD} \\ I_{ON} &= I_{OFF} + I_{OUT} = I_{OFF} + V_{DD}/R_L \end{split}$$

14. Application Comments

For proper operation, a 100nF bypass capacitor should be placed as close as possible to the device between the V_{DD} and ground pin.

For reverse voltage protection, it is recommended to connect a resistor or a diode in series with the V_{DD} pin. When using a resistor, three points are important:

- the resistor has to limit the reverse current to 50mA maximum (V_{CC} / R1 \leq 50mA)
- the resulting device supply voltage V_{DD} has to be higher than V_{DD} min (V_{DD} = V_{CC} R1.I_{DD}) the resistor has to withstand the power dissipated in reverse voltage condition (P_D = V_{CC}^2 / R1)

When using a diode, a reverse current cannot flow and the voltage drop is almost constant (≈0.7V).

Therefore, a $100\Omega/0.25W$ resistor for 5V application and a diode for higher supply voltage are recommended. Both solutions provide the required reverse voltage protection.

When a weak power supply is used or when the device is intended to be used in noisy environment, it is recommended that figure 13.3 from the Application Information section is used.

The low-pass filter formed by R1 and C1 and the zener diode Z1 bypass the disturbances or voltage spikes occurring on the device supply voltage V_{DD}. The diode D1 provides additional reverse voltage protection.



15. Standard information regarding manufacturability of Melexis products with different soldering processes

Our products are classified and qualified regarding soldering technology, solderability and moisture sensitivity level according to following test methods:

Reflow Soldering SMD's (Surface Mount Devices)

- IPC/JEDEC J-STD-020
 Moisture/Reflow Sensitivity Classification for Nonhermetic Solid State Surface Mount Devices (classification reflow profiles according to table 5-2)
- EIA/JEDEC JESD22-A113
 Preconditioning of Nonhermetic Surface Mount Devices Prior to Reliability Testing (reflow profiles according to table 2)

Wave Soldering SMD's (Surface Mount Devices) and THD's (Through Hole Devices)

- EN60749-20
 - Resistance of plastic- encapsulated SMD's to combined effect of moisture and soldering heat
- EIA/JEDEC JESD22-B106 and EN60749-15
 Resistance to soldering temperature for through-hole mounted devices

Iron Soldering THD's (Through Hole Devices)

EN60749-15
 Resistance to soldering temperature for through-hole mounted devices

Solderability SMD's (Surface Mount Devices) and THD's (Through Hole Devices)

 EIA/JEDEC JESD22-B102 and EN60749-21 Solderability

For all soldering technologies deviating from above mentioned standard conditions (regarding peak temperature, temperature gradient, temperature profile etc) additional classification and qualification tests have to be agreed upon with Melexis.

The application of Wave Soldering for SMD's is allowed only after consulting Melexis regarding assurance of adhesive strength between device and board.

Melexis is contributing to global environmental conservation by promoting **lead free** solutions. For more information on qualifications of **RoHS** compliant products (RoHS = European directive on the Restriction Of the use of certain Hazardous Substances) please visit the quality page on our website: http://www.melexis.com/quality.aspx


16. ESD Precautions

Electronic semiconductor products are sensitive to Electro Static Discharge (ESD).

Always observe Electro Static Discharge control procedures whenever handling semiconductor products.




17. UA Package Information (TO92 flat)



Notes:

- 1. Mold flashes and protrusion are not included.
- 2. Gate burrs shall not exceed 0.127mm on the top side.

Hall plate location



REF

REF

Notes:

1. All dimensions are in millimeters

Marking:

1st Line: U83 - Part number (US1883)

 2^{nd} Line: yww

y - last digit of year ww - calendar week

This table in mm

MAX

REVISION 005 - 13 JUNE 2019

REF

	Α	D	E	F	J	L	L1	S	b1	b2	С	е	e1
min	2.80	3.90	1.40	0.00	2.51	14.0	1.55	0.63	0.35	0.43	0.35	2.51	1.24
max	3.20	4.30	1.60	0.20	2.72	15.0	1.75	0.84	0.44	0.52	0.44	2.57	1.30
	θ1	θ2	θ3	θ4								•	
min	5°	5°	45°	3°									



18. Contact

For the latest version of this document, go to our website at www.melexis.com.

For additional information, please contact our Direct Sales team and get help for your specific needs:

Europe, Africa	Telephone: +32 13 67 04 95
	Email: sales_europe@melexis.com
Americas	Telephone: +1 603 223 2362
	Email : sales_usa@melexis.com
Asia	Email : sales_asia@melexis.com

19. Disclaimer

The information furnished by Melexis herein ("Information") is believed to be correct and accurate. Melexis disclaims (i) any and all liability in connection with or arising out of the furnishing, performance or use of the technical data or use of the product(s) as described herein ("Product") (ii) any and all liability, including without limitation, special, consequential or incidental damages, and (iii) any and all warranties, express, statutory, implied, or by description, including warranties of fitness for particular purpose, non-infringement and merchantability. No obligation or liability shall arise or flow out of Melexis' rendering of technical or other services.

The Information is provided "as is" and Melexis reserves the right to change the Information at any time and without notice. Therefore, before placing orders and/or prior to designing the Product into a system, users or any third party should obtain the latest version of the relevant information to verify that the information being relied upon is current. Users or any third party must further determine the suitability of the Product for its application, including the level of reliability required and determine whether it is fit for a particular purpose.

The Information is proprietary and/or confidential information of Melexis and the use thereof or anything described by the Information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights.

This document as well as the Product(s) may be subject to export control regulations. Please be aware that export might require a prior authorization from competent authorities. The Product(s) are intended for use in normal commercial applications. Unless otherwise agreed upon in writing, the Product(s) are not designed, authorized or warranted to be suitable in applications requiring extended temperature range and/or unusual environmental requirements. High reliability applications, such as medical life-support or life-sustaining equipment are specifically not recommended by Melexis.

The Product(s) may not be used for the following applications subject to export control regulations: the development, production, processing, operation, maintenance, storage, recognition or proliferation of 1) chemical, biological or nuclear weapons, or for the development, production, maintenance or storage of missiles for such weapons: 2) civil firearms, including spare parts or ammunition for such arms; 3) defense related products, or other material for military use or for law enforcement; 4) any applications that, alone or in combination with other goods, substances or organisms could cause serious harm to persons or goods and that can be used as a means of violence in an armed conflict or any similar violent situation.

The Products sold by Melexis are subject to the terms and conditions as specified in the Terms of Sale, which can be found at https://www.melexis.com/en/legal/terms-and-conditions.

 $This \ document \ supersedes \ and \ replaces \ all \ prior \ information \ regarding \ the \ Product(s) \ and/or \ previous \ versions \ of \ this \ document.$

Melexis NV © - No part of this document may be reproduced without the prior written consent of Melexis. (2016)

ISO/TS 16949 and ISO14001 Certified

REVISION 005 – 13 JUNE 2019 Page 11 of 11