



## **RFANT Pb free Series – RoHS Compliance**

## MULTILAYER CERAMIC ANTENNA

## **Halogens Free Product**

## 2.4 GHz ISM Band Working Frequency

# P/N: RFANT5220110A0T

\*Contents in this sheet are subject to change without prior notice.

#### Approval sheet




#### FEATURES

- 1. Surface Mounted Devices with a small dimension of 5.2 x 2.0 x 1.1 mm<sup>3</sup> meet future miniaturization trend.
- 2. Embedded and LTCC (Low Temperature Co-fired Ceramic) technology is able to future integrate with system design as well as beautifying the housing of final product.
- 3. High Stability in Temperature / Humidity Change

#### APPLICATIONS

- 1. Bluetooth
- 2. Wireless LAN
- 3. HormRF
- 4. ISM band 2.4GHz wireless applications

### CONSTRUCTION



PIN	Connection			
1	Feeding			
2	Identification Mark			
3	Soldering terminal			

#### DIMENSIONS


Figure		Symbol	Dimension (mm)
W=2.0±0.2mm T=1	.15±0.1mm	L	5.20 ± 0.20
22 mm	22mm	W	2.00 ± 0.20
L=5.2±0.2mm A=0.4±0.25mm	A=0.4±0.25mm	Т	1.15 ± 0.10
		A	0.40 ± 0.25

## **ELECTRICAL CHARACTERISTICS**

RFANT5220110A0T	Specification
Working Frequency Range	2.4 GHz $\sim$ 2.5GHz
Gain	2 dB (Typical)
VSWR	2 max.
Polarization	Linear
Azimuth Beamwidth	Omni-directional
Impedance	50Ω
Rated Power (max.)	3 Watts
Maximum Input Power	5 Watts for 5 minutes
Operation Temperature	-40°C ~ +85°C


### Remark: The specification is defined based on the test board dimension as in below

## SOLDER LAND PATTERN DESIGN






#### Antenna on Test Board (FR4 Thickness 0.8mm)




### Antenna S11 on Test Board



## **RADIATION PATTERN**

Radiation Pattern and Gain were dependent on measurement board design. The specification of RFANT5220110A0T antenna was measured based on the PCB size and installation position as shown in the below figure Test Board



## RELIABILITY TEST

Test item	Test condition / Test method	Specification
Solderability	*Solder bath temperature : $235 \pm 5^{\circ}$ C	At least 95% of a surface of each terminal
JIS C 0050-4.6	*Immersion time $: 2 \pm 0.5$ sec	electrode must be covered by fresh solder.
JESD22-B102D	Solder:Sn3Ag0.5Cu for lead-free	
Leaching	*Solder bath temperature : $260 \pm 5^{\circ}$ C	Loss of metallization on the edges of each
(Resistance to	*Leaching immersion time $: 30 \pm 0.5$ sec	electrode shall not exceed 25%.
dissolution of	Solder : SN63A	
metallization) IEC 60068-2-58		
Resistance to soldering		
heat	*Preheating temperature : $120~150^{\circ}$ C,	No mechanical damage.
JIS C 0050-5.4	1 minute.	Electrical specification shall satisfy the
	*Solder temperature : 270±5°C	descriptions in electrical characteristics under
	*Immersion time : 10±1 sec	the operational temperature range within -40
		~ 85°C.
	Solder : Sn3Ag0.5Cu for lead-free	Loss of metallization on the edges of each
	Measurement to be made after keeping at	electrode shall not exceed 25%.
	room temperature for 24±2 hrs	
Drop Test	*Height:75 cm	No mechanical damage.
JIS C 0044		Electrical specification shall satisfy the
Customer's specification.	*Test Surface : Rigid surface of concrete or	descriptions in electrical characteristics under
	steel.	the operational temperature range within -40
	*Times: 6 surfaces for each units; 2 times for	~ 85°C.
	each side.	
Vibration	*Frequency:10Hz~55Hz~10Hz(1min)	No mechanical damage.
JIS C 0040	*Total amplitude : 1.5mm	Electrical specification shall satisfy the
	*Test times : 6hrs.(Two hrs each in three	descriptions in electrical characteristics under
	mutually perpendicular directions)	the operational temperature range within -40
		~ 85°C.
Adhesive Strength	*Droopurizing force :	
of Termination	*Pressurizing force : 5N(≦0603) ; 10N(>0603)	No remarkable damage or removal of the
JIS C 0051- 7.4.3		termination.
Bending test	*Test time : 10±1 sec	
JIS C 0051- 7.4.1	The middle part of substrate shall be	No mechanical damage.
	pressurized by means of the pressurizing rod	Electrical specification shall satisfy the
	at a rate of about 1 mm/s per second until the	descriptions in electrical characteristics under
	deflection becomes 1mm/s and then pressure	the operational temperature range within -40
	shall be maintained for 5±1 sec.	~ 85°C.
	Measurement to be made after keeping at	
	room temperature for 24±2 hours	

Г

Temperature cycle	1. 30±3 minutes at -40°C±3°C,	No mechanical damage.	
JIS C 0025		, and the second s	
	2. 10~15 minutes at room	Electrical specification shall satisfy the	
	temperature,	descriptions in electrical characteristics under	
	3. 30±3 minutes at +85°C±3°C,	the operational temperature range within -40 ~ 85℃.	
	4. 10~15 minutes at room	~ 65 C.	
	temperature,		
	Total 100 continuous cycles		
	Measurement to be made after keeping at		
	room temperature for 24±2 hrs		
High temperature	*Temperature : 85°C±2°C	No mechanical damage.	
JIS C 0021	*Test duration:1000+24/-0 hours	Electrical specification shall satisfy the	
	Measurement to be made after keeping at	descriptions in electrical characteristics under	
	room temperature for 24±2 hrs	the operational temperature range within -40	
	·	~ 85°C.	
Humidity	*Humidity ÷ 90% to 95% R.H.	No mechanical damage.	
(steady conditions)	*Temperature : 40±2°C	Electrical specification shall satisfy the	
JIS C 0022	*Time:1000+24/-0 hrs.	descriptions in electrical characteristics under the operational temperature range within -40	
	Measurement to be made after keeping		
	at room temperature for $24\pm2$ hrs	~ 85°C.	
	※ 500hrs measuring the first data then		
	1000hrs data		
Low temperature	*Temperature : -40°C±2°C	No mechanical damage.	
JIS C 0020	*Test duration : 1000+24/-0 hours	Electrical specification shall satisfy the	
	Measurement to be made after keeping at	descriptions in electrical characteristics under	
	room temperature for $24\pm2$ hrs	the operational temperature range within -40	
		~ 85°C.	

Г

### SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2





Fig 2. Infrared soldering profile

#### ORDERING CODE

RF	ANT	522011	0	Α	0	Т
Walsin	Product code	Dimension code	Unit of	Application	Specification	Packing
RF device	ANT : Antenna	Per 2 digits of	dimension	A : 2.4GHZ ISM	Design Code	T:7" Reeled
		Length, Width,	0 : 0.1 mm	Band		
		Thickness :	1 :1.0 mm			
		e.g. :				
		522011 =				
		Length 52,				
		Width 20,				
		Thickness 11				

Minimum Ordering Quantity: 2000 pcs per reel. PACKAGING




#### Plastic Tape specifications (unit :mm)

Index	Ao	Во	ΦD	Т	W
Dimension (mm)	$2.40\pm0.10$	$5.50\pm0.10$	$1.55\pm0.05$	$1.20\pm0.10$	$12.0\pm0.10$
Index	E	F	Po	P1	P2
Dimension (mm)	$1.75\pm0.10$	$5.50\pm0.10$	$4.00\pm0.10$	$4.00\pm0.10$	$2.00\pm0.10$



#### **Reel dimensions**



Index	А	В	С
Dimension (mm)	Φ178	Φ60.0	Φ13.5

Typing Quantity: 2000 pieces per 7" reel

#### CAUTION OF HANDLING

#### **Limitation of Applications**

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

#### Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection, which can be confirmed.
- (2) Storage environment condition.
  - Products should be storage in the warehouse on the following conditions.
  - Temperature : -10 to +40°C
  - Humidity : 30 to 70% relative humidity
  - Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
  - Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
  - Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
  - Products should be storage under the airtight packaged condition.