
VS-10TQ035SPbF, VS-10TQ045SPbF

Vishay Semiconductors


High Performance Schottky Rectifier, 10 A



PRODUCT SUMMARY					
Package	D ² PAK				
I _{F(AV)}	10 A				
V_{R}	35 V, 40 V, 45 V				
V _F at I _F	0.57 V				
I _{RM}	15 mA at 125 °C				
T _J max.	175 °C				
Diode variation	Single die				
E _{AS}	13 mJ				

FEATURES

- 175 °C T_J operation
- Low forward voltage drop
- · High frequency operation





- Guard ring for enhanced ruggedness and long term reliability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

DESCRIPTION

The VS-10TQ...SPbF Schottky rectifier series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS						
SYMBOL	CHARACTERISTICS	VALUES	UNITS			
I _{F(AV)}	Rectangular waveform	10	A			
V _{RRM}		35/45	V			
I _{FSM}	t _p = 5 μs sine	1050	A			
V _F	10 A _{pk} , T _J = 125 °C	0.49	V			
TJ	Range	-55 to +175	°C			

VOLTAGE RATINGS					
PARAMETER	SYMBOL	VS-10TQ035SPbF	VS-10TQ045SPbF	UNITS	
Maximum DC reverse voltage	V_{R}	35	45	V	
Maximum working peak reverse voltage	V_{RWM}	- 55	40	V	

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS VALUES UNIT			
Maximum average forward current See fig. 5	I _{F(AV)}	50 % duty cycle at T_C = 151 °C, r	10	А	
Maximum peak one cycle non-repetitive surge current	l=o	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated	1050	Α
See fig. 7	I _{FSM}	10 ms sine or 6 ms rect. pulse	V _{RRM} applied	280 A	
Non-repetitive avalanche energy	E _{AS}	$T_J = 25 ^{\circ}\text{C}, I_{AS} = 2 \text{A}, L = 6.5 \text{mH}$		13	mJ
Repetitive avalanche current	I _{AR}	Current decaying linearly to zero i Frequency limited by T _J maximum	•	2	А



VS-10TQ035SPbF, VS-10TQ045SPbF

Vishay Semiconductors

ELECTRICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST	TEST CONDITIONS		
		10 A	T _{.1} = 25 °C	0.57	V
Maximum forward voltage drop	V (1)	20 A	1j = 25 C	0.67	
See fig. 1	V _{FM} ⁽¹⁾	10 A	T 105 %C	0.49	
		20 A	T _J = 125 °C	0.61	
Maximum reverse leakage current	I _{RM} ⁽¹⁾	T _J = 25 °C	V Dated V	2	0
See fig. 2		T _J = 125 °C	V _R = Rated V _R	15	- mA
Maximum junction capacitance	C _T	V _R = 5 V _{DC} (test signal	V _R = 5 V _{DC} (test signal range 100 kHz to 1 MHz), 25 °C		pF
Typical series inductance	L _S	Measured lead to lead	8.0	nH	
Maximum voltage rate of change	dV/dt	Rated V _R		10 000	V/µs

Note

 $^{^{(1)}\,}$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER		SYMBOL	SYMBOL TEST CONDITIONS		UNITS	
Maximum junction and storage temperature range		T _J , T _{Stg}		-55 to +175	°C	
Maximum thermal resistar junction to case	nce,	R _{thJC}	DC operation See fig. 4	2.0	°C/W	
Typical thermal resistance case to heatsink) ,	R _{thCS}	Mounting surface, smooth and greased	0.50	- °C/W	
Approximate weight				2	g	
Approximate weight				0.07	OZ.	
minimu				6 (5)	kgf · cm	
Mounting torque	maximum			12 (10)	(lbf·in)	
Marking device			Case style D ² PAK	10TQ	045S	



www.vishay.com

Vishay Semiconductors




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics





www.vishay.com

Vishay Semiconductors




Fig. 5 - Maximum Allowable Case Temperature vs.
Average Forward Current




Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Maximum Non-Repetitive Surge Current





Fig. 8 - Unclamped Inductive Test Circuit

VS-10TQ035SPbF, VS-10TQ045SPbF

Vishay Semiconductors

ORDERING INFORMATION TABLE

Device code



Vishay Semiconductors product

2 - Current rating (10 A)

Circuit configuration: T = D²PAK

4 - Schottky "Q" series

035 = 35 V 045 = 45 V

6 - S = D²PAK

7 - • None = tube (50 pieces)

• TRL = tape and reel (left oriented)

• TRR = tape and reel (right oriented)

8 - PbF = lead (Pb)-free


LINKS TO RELATED DOCUMENTS				
Dimensions	www.vishay.com/doc?95014			
Part marking information	www.vishay.com/doc?95008			
Packaging information	www.vishay.com/doc?95032			



Vishay Semiconductors

D²PAK, TO-262

DIMENSIONS - D²PAK in millimeters and inches



	MILLIM	IETERS	INC	HES	
SYMBOL	MIN.	MAX.	MIN.	MAX.	NOTES
	IVIIIA.	WAA.	IVIIIV.	WAA.	
Α	4.06	4.83	0.160	0.190	
A1	0.00	0.254	0.000	0.010	
b	0.51	0.99	0.020	0.039	
b1	0.51	0.89	0.020	0.035	4
b2	1.14	1.78	0.045	0.070	
b3	1.14	1.73	0.045	0.068	4
С	0.38	0.74	0.015	0.029	
c1	0.38	0.58	0.015	0.023	4
c2	1.14	1.65	0.045	0.065	
D	8.51	9.65	0.335	0.380	2

SYMBOL	MILLIN	IETERS	INC	NOTES	
	MIN.	MAX.	MIN.	MAX.	NOTES
D1	6.86	8.00	0.270	0.315	3
E	9.65	10.67	0.380	0.420	2, 3
E1	7.90	8.80	0.311	0.346	3
е	2.54 BSC		0.100 BSC		
Н	14.61	15.88	0.575	0.625	
L	1.78	2.79	0.070	0.110	
L1	-	1.65	-	0.066	3
L2	1.27	1.78	0.050	0.070	
L3	0.25 BSC		0.010	BSC	
L4	4.78	5.28	0.188	0.208	

Notes


- (1) Dimensioning and tolerancing per ASME Y14.5 M-1994
- (2) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outmost extremes of the plastic body
- $^{(3)}\,$ Thermal pad contour optional within dimension E, L1, D1 and E1
- (4) Dimension b1 and c1 apply to base metal only
- (5) Datum A and B to be determined at datum plane H
- (6) Controlling dimension: inch


(7) Outline conforms to JEDEC outline TO-263AB



DIMENSIONS - TO-262 in millimeters and inches

Modified JEDEC outline TO-262 (Datum A) (2) (3) (3) L1 D D L2 B B B C C C C C C C C A (2) A (2) A (2) A (3) L (2)





⊕ 0.010 **M** A **M** B


Lead assignments



<u>Diodes</u>
1. - Anode (two die)/open (one die)

2., 4. - Cathode

3. - Anode



Section B - B and C - C Scale: None

SYMBOL	MILLIMETERS		INC	INCHES		
	MIN.	MAX.	MIN.	MAX.	NOTES	
Α	4.06	4.83	0.160	0.190		
A1	2.03	3.02	0.080	0.119		
b	0.51	0.99	0.020	0.039		
b1	0.51	0.89	0.020	0.035	4	
b2	1.14	1.78	0.045	0.070		
b3	1.14	1.73	0.045	0.068	4	
С	0.38	0.74	0.015	0.029		
c1	0.38	0.58	0.015	0.023	4	
c2	1.14	1.65	0.045	0.065		
D	8.51	9.65	0.335	0.380	2	
D1	6.86	8.00	0.270	0.315	3	
Е	9.65	10.67	0.380	0.420	2, 3	
E1	7.90	8.80	0.311	0.346	3	
е	2.54 BSC		0.100	BSC		
L	13.46	14.10	0.530	0.555		
L1	-	1.65	-	0.065	3	
L2	3.56	3.71	0.140	0.146		

Notes

- $^{(1)}$ Dimensioning and tolerancing as per ASME Y14.5M-1994
- (2) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outmost extremes of the plastic body
- (3) Thermal pad contour optional within dimension E, L1, D1 and E1
- (4) Dimension b1 and c1 apply to base metal only
- (5) Controlling dimension: inches

(6) Outline conform to JEDEC TO-262 except A1 (maximum), b (minimum) and D1 (minimum) where dimensions derived the actual package outline



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.