



PCB spring terminal block

Rated current: 10 A

Rated voltage: 300 V

Wire range: 28-12 AWG

Pitch: 7.5 mm/7.62 mm

Mounting: Wave soldering



### UL/CUL

Use Group	B	C	D
Rate Voltage [V]	300	-	300
Rated Current [A]	10	-	10
Wire Range [AWG]	28-12		
Dielectric Voltage-Withstand	1.6KV		

### IEC

Overvoltage Category	III	III	II
Contamination Class	3	2	2
Rated Voltage [V]	400	630	1000
Rated Current [A]	21	21	21
Impulse withstand voltage [KV]	6	6	6
Conductor cross section[solid/flexible] [mm <sup>2</sup> ]	0.2-2.5		

### Material

Insulation Material	PA66
Flame retardant rating	UL94V-0
Conductor Material	Copper alloy
Plating of conductor surface	Sn plated

**Other Data**

Pitch/Poles [mm]/[P]	7.5 , 7.62/2*2-2*24
Stripping Length [mm]	5-6
Screw/Torque(Max)[N.m]	/
Operating temperature [°C]	-40~+105
Soldering temperature	260°C/5S
Pin dimensions [mm]	0.7*0.7
PCB Hole Diameter [mm]	Ø1.3

**Dimensions**

**PCB opening diagram**

