

SPECIFICATION SHEET

SPECIFICATION SHEET NO.	Q0524-FF10M70000SA20
DATE	May 24, 2023
REVISION	A1
DESCRIPITION	SMD MHz Ceramic Filter, L3.45*W3.1*H1.4mm, 4 Pads, CF33 Series,
	A20 Type, 10.700MHz, 3dB Band Width: 330+/-50KHz,
	Insertion Loss: 3.0+/-2.0dB. Impedance: 330 ohm
	Operating Temp. Range -20°C ~+80°C,
	Packed in Tape/Reel,
	RoHS/RoHS III compliant
CUSTOMER	
CUSTOMER PART NUMBER	
CROSS REF. PART NUMBER	
ORIGINAL PART NUMBER	TGS CF33 10.7MA20 TLF
PART CODE	FF10M70000SA20

VENDOR APPROVE			
Issued/Checked/Approved	Compose Mandy Xu ToN#39	Compose Cumpos	Jack Jack
DATE: May 24, 2023			
CUSTOMER APPROVE			

DATE:

5/24/2023

1



SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

MAIN FEATURE

- SMD MHz Ceramic Filter, L3.45*W3.1*H1.4mm, 4 Pads
- Low cost & short lead time.
- Cross more competitors part SFECF Series
- RoHS/RoHS III compliant

APPLICATION

• Communication Electronics and more



100% OUALITY	ROHS



FF	10M70000	S	A20
1	2	3	4

1) FF: Part family Code for SMD MHz Ceramic Filter, L3.45*W3.1*H1.4mm, 4 Pads, CF33 series

2) 10M70000: Frequency range code for 10.70000MHz

3) S: Packed in Tape/Reel

4) A20: Specification code for original Part No. TGS CF33 10.7MA20 TLF

5/24/2023




SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

DIMENSION (Unit: mm)


Image for reference

CF33






*: QC Code








(1): Input
(2): Ground
(3) Float (Signal Line)
(4) Output

5/24/2023

NextGen Components, Inc.



SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

ELECTRICAL PARAMETERS

Parameter	r	Part No.	Units		Value	Condition	
		Symbol		Min.	Typical	Max.	_
Original M	lanufacturer	TGS	TGS Crystals				
Holder Typ	be	CF33		SMD MHz C .45*W3.1*H			
Center Fre	quency (f0)	10.7M	MHz		10.7000		@+/-30KHz
Bandwidth	n	A20	kHz	280	330	380	@3 dB
Bandwidt	n		kHz	-		700	@20 dB
Ripple			dB			1.0	within 3dB bandwidth
Insertion I	.OSS		dB	1.0	3.0	5.0	@Min.loss point
Temp. Cha	aracteristic		%			±0.5	@-20°C ~ +80°C
Spurious Response			dB	30			@9.0 ~ 12.0MHz
Input/Out Impedance			Ω		330		
Insulation Resistance Withstand DC Voltage			MΩ	100			@ 10V 1 min.
			V			50	@ DC, 1 min
Operating Temp. Range			°C	-20		+80	
Storage Te	emp. Range		°C	-40		+85	
Package T Packed in Tape/Ree RoHS LF RoHS III compliant		Tape/Reel					
		LF	RoHS III compliant				
Others	Add Value		N/A				
Internal Control Code *			N/A				

Note: Original Part Number: TGS CF33 10.7MA20 TLF



SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

RELIABILITY

Test Items	Test Items Test Method And Conditions			
Humidity	HumidityAfter being placed in a chamber with 90-95% R.H. at 40±2°C for 96 hours and then being placed in room temperature for 1 hour, filter shall be measured.			
High Temperature	High TemperatureAfter being placed in a chamber with 85±2 °C, for 96 hours and thenbeing placed in room temperature for 1 hour, filter shall be measured.			
Low Temperature	After being placed in a chamber with -40±2 °C,for 96 hours and then being placed in room temperature for 1 hour, filter shall be measured.	lt shall fulfill Table 1.		
Temperature Cycling	After temperature cycling of blow table was performed 5 times, Filter shall be measured after being placed in natural conditions for 1h. Temp.: –20±3°C, Time: 30±3 min ; Temp.: –80±3°C, Time: 30±3 min.	It shall fulfill Table 1.		
Vibration	Subject the filter to vibration for 2h.Each in x y and z axis with the amplitude of 1.5mm, The frequency shall be varied uniformly between the limits of 10Hz-55Hz-10Hz and then filter shall be measured.	It shall fulfill Table 1.		
Mechanical Shock	Filter shall be measured after 3 times random dropping from the height of 1m on the wooden plate.	No visible damage. it shall fulfill Table 1		
Soldering Test	Passed through the reflow oven under the following condition, and left at room temp. for 24 hours before measurement.	It shall fulfill Table 1.		
Solderability	Dipped in 235°C±5°C solder bath for 3s±0.5s with rosin flux (25wt% ethanol solution.)	The terminals shall be at least 95% covered by solder.		
Board Bending	Mount on a glass-epoxy board(width =50mm, thickness=1.6mm),then bend it to 1mm displacement(velocity= 1mm/s) and keep it for 5s.	Mechanical damage such as break shall not occur		

5/24/2023


NextGen Components, Inc.




SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

Table 1

Test Items	Characteristics after test	
Center Frequency Drift	±30 kHz Max.	
Insertion Loss Drift	±2.0 dB Max.	
3dB Bandwidth Drift	±25 kHz Max.	
20dB Bandwidth Drift	±60 kHz Max.	
Note: The limits in the above table are referenced to the initial measurements.		








Board Bending


5/24/2023

NextGen Components, Inc.



SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

TEST CIRCUIT (For Reference Only)



R1=280 Ω (1±5%,) R2= 330 Ω (1±5%,) Rg=50 Ω C2=10pF(Including stray capacitance and input capacitance of RF voltmeter), S.S.G: Output Voltmeter (1): Input (2): Ground (3): Float (4): Output


Note:

Parts shall be tested under the condition (Temp.: 20±15°C,Humidity 65±20% R.H.) unless the standard condition(Temp.: 25±3 °C, Humidity : 65±10% R.H.)is regulated to measure.




SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

RECOMMENDED REFLOW SOLDERING STANDARD CONDITION



RECOMMENDED LAND PATTERN




- (1): Input(2): Ground(3) Float (Signal Line)
- (4) Output





SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

TPAE/REEL DIMENSIONS (mm)




фА	фВ	W T Pieces per reel		Carrier tape size	
180±3	60min	12.4min	19.4max	1000 typ.	12





5/24/2023



SMD MHZ CERAMIC FILTER CF33 SERIES A20 TYPE

NOTES

- Don't apply excess mechanical stress to the component and terminals at soldering. Do not use this product with bend.
- Do not clean or wash the component for it is not hermetically sealed.
- Do not use strong acidity flux, more than 0.2wt% chlorine content, in flow soldering.
- Don't be close to fire.
- This specification mentions the quality of the component as a single unit. Please insure the component is thoroughly evaluated in your application circuit
- Expire date (Shelf life) of the products is 12 months after delivery under the conditions of a sealed and an unopened package. Please use the products within 12 months after delivery. If you store the products for a long time (more than 12 months), use carefully because the products may be degraded in the solder-ability or rusty. Please confirm solder-ability and characteristics for the products regularly.
- Exposure components under soldering condition that is exceeding our recommendation will increase the failure dangerous.
- Please contact us before using the product as automobile electronic component.
- Please return one of these specifications after your signature of acceptance.
- When something gets doubtful with this specifications, we shall jointly work to get an agreement.
- For questions on technology, prices and delivery, please contact our sales offices or e-mail: sales@NextGenComponent.com .

DISCLAIMER

NextGen Components, Inc. reserves the right to make changes to the product(s) and or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent

accompany the sale of any such product(s) or information 5/24/2023