

#### Is Now Part of



# ON Semiconductor®

# To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to Fairchild <a href="general-regarding-numbers-n

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



September 2014

# FPF2495 IntelliMAX™ 28 V, Over-Voltage, Over-Current Protection Load Switch with Adjustable Current-Limit Control

#### **Features**

- V<sub>IN</sub>: 2.5 V~5.5 V
- 28 V Absolute Ratings at V<sub>OUT</sub>
- Current Capability: 2 A
- Adjustable Current Limit: 0.05 A ~ 2 A (Typ.)
  - 0.1 A~2 A with 10% Accuracy
  - < 0.1A with 15% Accuracy</li>
- R<sub>ON</sub>: Maximum 100 mΩ at 5 V<sub>IN</sub> and 1 A I<sub>OUT</sub>
- Output OVP: Min.=5.6 V, Typ.=5.8 V, Max.=6 V
- No Output Discharge During Off State
- Open-Drain OCP on FLAGB
- Thermal Shutdown
- Under-Voltage Lockout (UVLO)
- True Reverse-Current Blocking (TRCB)
- Logic CMOS IO Meets JESD76 Standard for GPIO Interface and Related Power Supply Requirements
- ESD Protected:
  - Human Body Model: >2 kV
  - Charged Device Model: >2.5 kV
  - IEC 61000-4-2 Air Discharge: >15 kV
  - IEC 61000-4-2 Contact Discharge: >8 kV

#### Description

The FPF2495 advanced load-management switch targets applications requiring a highly integrated solution. It disconnects loads powered from the DC power rail (<6 V) with stringent off-state current targets and high load capacitances (<100  $\mu F$ ). The FPF2495 consists of a slew-rate controlled low-impedance MOSFET switch (100 m $\Omega$  maximum) and integrated analog features. The slew-rate controlled turn-on characteristic prevents inrush current and the resulting excessive voltage droop on power rails. FPF2495 has over-voltage protection and over-temperature protection.

The FPF2495 has a True Reverse-Current Blocking (TRCB) function that obstructs unwanted reverse current from  $V_{\text{OUT}}$  to  $V_{\text{IN}}$  during ON and OFF states. The exceptionally low off-state current drain (<2  $\mu\text{A}$  maximum) facilitates compliance with standby power requirements. The input voltage range operates from 2.5 V to 5.5  $V_{\text{DC}}$  to support a wide range of applications in consumer, optical, medical, storage, portable, and industrial-device power management. Switch control is managed by a logic input (active HIGH) capable of interfacing directly with low-voltage control signal / General-Purpose Input / Output (GPIO) without an external pull-down resistor.

The device is packaged in advanced, fully "green" compliant, 1.21 mm x 1.21 mm, Wafer-Level Chip-Scale Package (WLCSP).

# **Applications**

- Smart Phones, Tablet PCs
- Storage, DSLR, and Portable Devices

# **Ordering Information**

Part Number	Operating Temperature Range	Package	Packing Method	Top Mark
FPF2495UCX	-40 to 85°C	1.21 mm x 1.21 mm, Wafer-Level Chip-Scale Package (WLCSP)	Tape & Reel	TH

# **Application Diagram**




Figure 1. Typical Application

#### Note:

1. C<sub>IN</sub> and C<sub>OUT</sub> capacitors recommended for improvement of device stability.

# **Functional Block Diagram**




Figure 2. Functional Block Diagram

# **Pin Configurations**




Figure 3. Pin Assignments (Top View)




Figure 4. Pin Assignments (Bottom View)

# **Pin Description**

Pin#	Name	Description				
A3, B3	V <sub>OUT</sub>	Switch Output				
A1, B1	V <sub>IN</sub>	Supply Input: Input to the power switch				
A2	GND	Ground (true device ground)				
B2	GND	Ground (true device ground)				
C3	ON	ON/OFF Control Input: Active HIGH - GPIO compatible	Logic HIGH	Switch Enable		
CS	ON	ONOFF Control input. Active mon - GF10 compatible	Logic LOW	Switch Disable		
C1	OC <sub>FLAGB</sub>	<b>Fault Output</b> : Active LOW, open-drain output that indicates an input over current. External pull-up resistor to $V_{CC}$ is required.				
C2	I <sub>SET</sub>	Current Limit Set Input: A resistor from ISET to ground s	urrent Limit Set Input: A resistor from ISET to ground sets the current limit for the switch.			

# **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol		Min.	Max.	Unit	
V	V <sub>OUT</sub> to GND, V <sub>OUT</sub> to V <sub>IN</sub>		-0.3	28.0	V
$V_{PIN}$	ON, V <sub>IN</sub> , FLAGB, I <sub>SET</sub> to GND			6.0	V
I <sub>SW</sub>	Maximum Continuous S	laximum Continuous Switch Current <sup>(4)</sup>			Α
t <sub>PD</sub>	Total Power Dissipation at T <sub>A</sub> =25°C			1.0	W
TJ	Operating Junction Tem	perature	-40	+150	°C
T <sub>STG</sub>	Storage Junction Tempe	erature	-65	+150	°C
0	Thermal Resistance, Jui	action-to-Ambient		95 <sup>(2)</sup>	°C/W
$\Theta_{JA}$	(1-inch Square Pad of 2	oz. Copper)		110 <sup>(3)</sup>	C/VV
	Electrostatic Discharge	Human Body Model, JESD22-A114	2.0		
ESD	Capability Charged Device Model, JESD22-C101		2.5		kV
E9D	IEC61000-4-2 System	Air Discharge (V <sub>IN</sub> , V <sub>ON</sub> , V <sub>OUT</sub> to GND)	15.0		٨V
	Level	Contact Discharge (V <sub>IN,</sub> V <sub>ON,</sub> V <sub>OUT</sub> to GND)	8.0		

#### Notes:

- 2. Measured using 2S2P JEDEC std. PCB.
- 3. Measured using 2S2P JEDEC PCB cold plate method.
- 4. Maximum Junction Temperature = 85°C.

# **Recommended Operating Conditions**

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameters	Min.	Max.	Unit
V <sub>IN</sub>	Supply Voltage	2.5	5.5	V
$T_A$	Ambient Operating Temperature	-40	85	°C

#### **Electrical Characteristics**

Unless otherwise noted;  $V_{IN}$ =2.5 to 5.5 V,  $T_A$ =-40 to +85°C; typical values are at  $V_{IN}$ =5 V and  $T_A$ =25°C.

Symbol	Parameters	Condition	Min.	Тур.	Max.	Uni
Basic Oper	ation				l	
$V_{IN}$	Input Voltage		2.5		5.5	V
I <sub>Q(OFF)</sub>	Off Supply Current	V <sub>ON</sub> =GND, V <sub>OUT</sub> =Open		1	2	μΑ
I <sub>SD(OFF)</sub>	Shutdown Current	V <sub>IN</sub> =5.5 V, V <sub>OUT</sub> =0 V, V <sub>ON</sub> =GND		0.1	4.0	μΑ
IQ	Quiescent Current	I <sub>OUT</sub> =0 mA		65	100	μA
_	0 0 11	V <sub>IN</sub> =5.0 V, I <sub>OUT</sub> =1 A		70	100	•
Ron	On Resistance	V <sub>IN</sub> =3.7 V, I <sub>OUT</sub> =1 A		75	105	mΩ
R <sub>ON</sub>	On Resistance <sup>(6)</sup>	V <sub>IN</sub> =5.0 V, I <sub>OUT</sub> =1.5 A		70		mΩ
V <sub>IH</sub>	ON Input Logic HIGH Voltage	V <sub>IN</sub> =2.5 V to 5.5 V	1.15			V
V <sub>IL</sub>	ON Input Logic LOW Voltage	V <sub>IN</sub> =2.5 V to 5.5 V			0.65	V
.,	FLAGB Output Logic	V <sub>IN</sub> =5 V, I <sub>SINK</sub> =10 mA		0.1	0.2	
$V_{IL\_FLAG}$	LOW Voltage	V <sub>IN</sub> =2.5 V, I <sub>SINK</sub> =10 mA		0.15	0.30	V
I <sub>FLAGB_LK</sub>	FLAGB Output HIGH Leakage Current	V <sub>IN</sub> =5 V, Switch On			1	μA
I <sub>ON</sub>	On Input Leakage	V <sub>ON</sub> =0 V to V <sub>IN</sub>			1.0	μΑ
R <sub>ON_PD</sub>	Pull-Down Resistance at ON Pin	V <sub>IN</sub> =2.5~5.5 V, V <sub>ON</sub> =HIGH, T <sub>A</sub> =-40 to 85°C		14		MΩ
Over-Voltaç	ge Protection				L	
		V <sub>OUT</sub> Rising Threshold	5.50	5.80	6.00	
$V_{OV\_TRIP}$	Output OVP Lockout	V <sub>OUT</sub> Falling Threshold		5.50		V
OUT <sub>HYS</sub>	Output OVP Hysteresis	V <sub>OUT</sub> Falling Threshold		0.3		V
t <sub>OVP</sub>	OVP Response Time <sup>(6)</sup>	$I_{OUT}{=}0.5$ A, $C_L{=}1~\mu\text{F},~T_A{=}25^{\circ}\text{C},~V_{OUT}$ from $5.5~V$ to $6.0~V$	1		4 <sup>(6)</sup>	μs
Over-Curre	nt Protection				7	
7		V <sub>IN</sub> =5 V, R <sub>SET</sub> =20000 Ω,	40	50	58	
		V <sub>OUT</sub> =1.68 to 5 V with 15% Accuracy <sup>(5)</sup>	42	30		
I <sub>LIM</sub>	Current Limit	V <sub>OUT</sub> =1.68 to 5 V with 15% Accuracy <sup>(5)</sup> V <sub>IN</sub> =5 V, R <sub>SET</sub> =2100 Ω, V <sub>OUT</sub> =1.68 to 5 V with 10% Accuracy <sup>(5)</sup>	450	500	550	mA
I <sub>LIM</sub>	Current Limit	V <sub>IN</sub> =5 V, R <sub>SET</sub> =2100 Ω,				mA
		$V_{IN}$ =5 V, R <sub>SET</sub> =2100 Ω, $V_{OUT}$ =1.68 to 5 V with 10% Accuracy <sup>(5)</sup> $V_{IN}$ =5 V, R <sub>SET</sub> =1070 Ω,	450	500	550	R
I <sub>LIM</sub>	Current Limit  Under-Voltage Lockout	$V_{\text{IN}}$ =5 V, R <sub>SET</sub> =2100 Ω, $V_{\text{OUT}}$ =1.68 to 5 V with 10% Accuracy <sup>(5)</sup> $V_{\text{IN}}$ =5 V, R <sub>SET</sub> =1070 Ω, $V_{\text{OUT}}$ =1.68 to 5 V with 10% Accuracy <sup>(5)</sup>	450	500	550	mA V
V <sub>UVLO</sub>		$\begin{array}{c} V_{\text{IN}} \!\!=\!\! 5 \text{ V, R}_{\text{SET}} \!\!=\!\! 2100 \; \Omega, \\ V_{\text{OUT}} \!\!=\!\! 1.68 \text{ to 5 V with 10\% Accuracy}^{(5)} \\ V_{\text{IN}} \!\!=\!\! 5 \text{ V, R}_{\text{SET}} \!\!=\!\! 1070 \; \Omega, \\ V_{\text{OUT}} \!\!=\!\! 1.68 \text{ to 5 V with 10\% Accuracy}^{(5)} \\ V_{\text{IN}} \text{ Increasing} \end{array}$	450	500 1000 2.4	550	V
	Under-Voltage Lockout	$\begin{array}{c} V_{\text{IN}} \!\!=\!\! 5 \text{ V, R}_{\text{SET}} \!\!=\!\! 2100 \; \Omega, \\ V_{\text{OUT}} \!\!=\!\! 1.68 \text{ to 5 V with 10\% Accuracy}^{(5)} \\ V_{\text{IN}} \!\!=\!\! 5 \text{ V, R}_{\text{SET}} \!\!=\!\! 1070 \; \Omega, \\ V_{\text{OUT}} \!\!=\!\! 1.68 \text{ to 5 V with 10\% Accuracy}^{(5)} \\ V_{\text{IN}} \text{ Increasing} \end{array}$	450	500 1000 2.4 2.2	550	R

Continued on the following page...

# **Electrical Characteristics** (Continued)

Unless otherwise noted;  $V_{IN}$ =2.5 to 5.5 V,  $T_A$ =-40 to +85°C; typical values are at  $V_{IN}$ =5 V and  $T_A$ =25°C.

Symbol	Parameters	Conditions	Min.	Тур.	Max.	Unit	
V <sub>RCB_HYS</sub>	RCB Hysteresis			100		mV	
t <sub>RCB</sub>	Default RCB Response Time	V <sub>IN</sub> =5 V, V <sub>ON</sub> =High/Low		2		μs	
I <sub>RCB</sub>	RCB Current	V <sub>ON</sub> =0 V, V <sub>OUT</sub> =5.5 V,		7		μΑ	
thocp	Hard Over-Current Response Time	Moderate Over-Current Condition, I <sub>OUT</sub> ≥ I <sub>LIM</sub> , V <sub>OUT</sub> =0 V		6		μs	
t <sub>OCP</sub>	Over-Current Response Time	Moderate Over-Current Condition, $I_{OUT} \ge I_{LIM} V_{OUT} \le V_{IN}$		7		μs	
toc_flag	Over-Current Flag Response Time	ent Flag When Over-Current Occurs to Flag		8		ms	
		Shutdown Threshold		150			
TSD	Thermal Shutdown	Return from Shutdown		130		°C	
		Hysteresis	lysteresis 20				
Dynamic C	haracteristics						
t <sub>DON</sub>	Turn-On Delay <sup>(6,7)</sup>			0.67		ms	
t <sub>R</sub>	V <sub>OUT</sub> Rise Time <sup>(6,7)</sup>			0.69		ms	
t <sub>ON</sub>	Turn-On Time <sup>(6,8)</sup>	$V_{IN}$ =5 V, R <sub>L</sub> =100 $\Omega$ , C <sub>L</sub> =1 $\mu$ F,		1.36		ms	
t <sub>DOFF</sub>	Turn-Off Delay <sup>(7,6)</sup>	$T_A$ =25°C, $R_{SET}$ =2040 $\Omega$		0.01		ms	
t <sub>F</sub>	V <sub>OUT</sub> Fall Time <sup>(7,6)</sup>			0.22		ms	
t <sub>OFF</sub>	Turn-Off Time <sup>(9,6)</sup>			0.23		ms	
t <sub>DON</sub>	Turn-On Delay <sup>(7,10)</sup>			0.65	0.78	ms	
t <sub>R</sub>	V <sub>OUT</sub> Rise Time <sup>(7,10)</sup>			0.65	0.82	ms	
ton	Turn-On Time <sup>(8,10)</sup>	V <sub>IN</sub> =5 V, R <sub>L</sub> =3.8 Ω, C <sub>L</sub> =10 μF, T <sub>A</sub> =-		1.3	1.6	ms	
t <sub>DOFF</sub>	Turn-Off Delay <sup>(7,10)</sup>	40 to 85°C, $R_{SET}$ =634 $\Omega$		4	10	μs	
t <sub>F</sub>	V <sub>OUT</sub> Fall Time <sup>(7,10)</sup>			76	120	μs	
t <sub>OFF</sub>	Turn-Off Time <sup>(9,10)</sup>			80	130	μs	

#### Notes:

- 5. Characterization based on 1% tolerance resistor.
- 6. This parameter is guaranteed by design and characterization; not production tested.
- 7.  $t_{DON}/t_{DOFF}/t_R/t_F$  are defined in Figure 5 below.
- 8.  $t_{ON}=t_R+t_{DON}$ .
- 9.  $t_{OFF}=t_F+t_{DOFF}$ .
- 10. This parameter is guaranteed by design.

#### **Timing Diagram**




Figure 5. Timing Diagram

#### where:

$$\begin{split} &t_{DON} = \text{Delay On Time} \\ &t_R = V_{OUT} \text{ Rise Time} \\ &t_{ON} = \text{Turn-On Time} \\ &t_{DOFF} = \text{Delay Off Time} \\ &t_F = V_{OUT} \text{ Fall Time} \\ &t_{OFF} = \text{Turn Off Time} \end{split}$$

# **Operation and Application Description**

#### **Input Capacitor**

To limit the voltage drop on the input supply caused by transient inrush current when the switch turns on into discharge load capacitor; a capacitor must be placed in between the  $V_{\text{IN}}$  and GND pins. A high-value capacitor on  $C_{\text{IN}}$  can be used to reduce the voltage drop in high-current applications.

#### **Output Capacitor**

An output capacitor should be placed between the  $V_{\text{OUT}}$  and GND pins. This capacitor prevents parasitic board inductance from forcing  $V_{\text{OUT}}$  below GND when the switch is on. This capacitor also prevents reverse inrush current from creating a voltage spike that could damage the device in the case of a  $V_{\text{OUT}}$  short.

#### **Fault Reporting**

Upon the detection of an over-current, OC\_FLAGB signal the fault by activating LOW.

#### **Current Limiting**

The current limit ensures that the current through the switch does not exceed the maximum set value, while not limiting the minimum value. The current at which the part's limit is adjustable through the selection of the external resistor connected to the ISET pin. Information for selecting the resistor is found in the section below. The device acts as a constant-current source when the load draws more than the maximum value set by the device until thermal shutdown occurs. The device recovers if the die temperature drops below the threshold temperature.

#### **Under-Voltage Lockout (UVLO)**

The under-voltage lockout turns the switch off if the input voltage drops below the lockout threshold. With the ON pin active, the input voltage rising above the UVLO threshold releases the lockout and enables the switch.

#### True Reverse-Current Blocking

The true reverse-current blocking feature protects the input source against current flow from output to input regardless of whether the load switch is on or off.

#### **Thermal Shutdown**

The thermal shutdown protects the die from internally or externally generated excessive temperature. During an over-temperature condition, the switch is turned off. The switch automatically turns on again if the temperature of the die drops below the threshold temperature.

# **Setting Current Limit**

The current limit is set with an external resistor connected between the  $I_{\text{SET}}$  and GND pins. The resistor is selected using Table 1. Resistor tolerance of 1% or less is recommended.

Table 1. Current Limit Settings by R<sub>SET</sub> (11)

Table I.	Current Limit Settings by K <sub>SET</sub>		
$R_{SET}\Omega$	Min. Current Limit (mA)	Typ. Current Limit (mA)	Max. Current Limit (mA)
528	1800	2000	2200
604	1570	1750	1920
680	1350	1500	1650
866	1125	1250	1375
1070	900	1000	1100
1200	810	900	990
1330	720	800	880
1500	630	700	770
1740	540	600	660
2100	450	500	550
2320	405	450	495
2550	360	400	440
2940	315	350	385
3400	370	300	330
4020	225	250	275
4990	180	200	220
6490	135	150	165
9530	90	100	110
20000	42	50	58

#### Note:

- 11. Table values based on 1% tolerance resistor.
- 12. For 50 mA setting, tolerance is ±15% with 1%.

### **Board Layout**

For best performance, all traces should be as short as possible. To be most effective, the input and output capacitors should be placed close to the device to minimize the effect that parasitic trace inductance may have on normal and short-circuit operation. Using wide traces for VIN, VOUT, GND helps minimize parasitic electrical effects along with minimizing the case-to-ambient thermal impedance.

# **Typical Performance Characteristics**

T<sub>A</sub>=25°C.



Figure 6. toN Response



Figure 8. OC\_FLAGB Response Time (Toggle R<sub>LOAD</sub> from High to Low Resistance)



Figure 10. t<sub>OCP</sub> Response Time



Figure 7. OVP Response (Increase V<sub>OUT</sub> to OVP Trip Point)






Figure 9. t<sub>OFF</sub> Response

# **Product-Specific Dimensions**

D	E	X	Y
1210 μm ±30 μm	1210 μm ±30 μm	205 μm	205 μm


		REVISIONS		
	REV	DESCRIPTION	DATE	BY/SITE
1		INITIAL DRAWING RELEASE.	2-15-2008	L. ENGLAND/FSME
	2	Updated land pattem to individual solder mask openings. Removed solder alloy note. Other misc updates for standardization.	4-9-2010	L. ENGLAND/FSME







**TOP VIEW** 

LAND PATTERN RECOMMENDATION (NSMD PAD TYPE)







**BOTTOM VIEW** 

#### NOTES:

- A. NO JEDEC REGISTRATION APPLIES.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCE PER ASMEY14.5M, 1994.

DATUM C IS DEFINED BY THE SPHERICAL CROWNS OF THE BALLS.

EN PACKAGE NOMINAL HEIGHT IS 586 MICRONS ±39 MICRONS (547-625 MICRONS).

FOR DIMENSIONS D, E, X, AND Y SEE PRODUCT DATASHEET.

G. DRAWING FILNAME: MKT-UC009ABrev2

APPROVALS	DATE	FAIR		D		
L. England	4-9-10	SEMICO				
ргта. снк. H. Allen	4-9-10	0	DALI	MI CCD		
ENGR. CHK.		9 BALL WLCSP, 3X3 ARRAY 0.4MM PITCH, 250UM BALL				
		Ĭ	171171	1 11011, 2	OOOW BALL	
PROJECTIO	N	SCALE	SIZE	DRAWING NUMBER		REV
		N/A	N/A	MKT-U	JC009AB	2
INCH [MM]	DO NO	Γ SCALE I	DRAWING	SHEET 1 of	1	

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and h

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative